



P/N LEGEND

A1500 WV-S-XP XXX				
①	②	③	④	⑤
① Series No.				
② Connector type: WV=Vertical				
③ Mounting type: S=SMT				
④ No. of circuits				
⑤ Option code:				
D01=With Cap				
Contacts/Gold-flash and Solder tabs/Gold-flash				
D10=Without Cap				
Contacts/Gold-flash and Solder tabs/Gold-flash				

SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 100V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 500MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Brass
 Solder Tabs: Brass
 Wafer: Nylon 6T,UL94V-0
 Cap: Nylon 6T,UL94V-0,Natural(Beige)
 Color: Natural(Beige)

Circuit No.	Dimensions		
	A	B	C
02P	1.50	6.00	3.60
03P	3.00	7.50	5.10
04P	4.50	9.00	6.60
05P	6.00	10.50	8.10
06P	7.50	12.00	9.60
07P	9.00	13.50	11.10
08P	10.50	15.00	12.60
09P	12.00	16.50	14.10
10P	13.50	18.00	15.60
11P	15.00	19.50	17.10
12P	16.50	21.00	18.60
13P	18.00	22.50	20.10



燦達電子工業股份有限公司
 JOINT TECH ELECTRONIC IND. CO., LTD.

REV.	DESCRIPTION	DATE	NAME	UNIT	SCALE	SHEET
A5	EN1505200001	2015.05.20	黃樸有	mm	1:1	1 of 2
A4	EN1501060001	2014.10.24	黃培軍			
A3	EN1106240218	2011.06.24	陳敏			
A2	EN1102160030	2011.04.19	陳錦展			
REV.	DESCRIPTION	DATE	NAME			

DRAWN BY	APPROVED BY
李勤	董正一
2006.07.07	2006.07.07
GENERAL TOLERANCE	
X. X±0.25	ANGLE±
X. XX±0.15	
X. XXX±0.05	

TITLE:	
1.50mm PITCH	
180° WAFER-SMT TYPE	
DRAW NO.:	REV.
A1500WV-S-XP	A5