High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT















Height: 10.0mm Max

Footprint: 16.8mm x 15.8mm MaxCurrent Rating: up to 30Arms

Inductance Range: 4.7uH to 33.0uH

@ High current, low DCR, and high efficiency

High reliability

Minimized acoustic noise and minimized leakage flux noise

Available in Commercial (PA2247) and Automotive (PM2247) grades

Electrical Specifications @ 25°C, Operating Temperature Range -55°C to +155°C											
Part Number			Rated³ Current	DC Resistance		Saturation Current ² (25°C)	K Factor for				
Commerical	Automotive ⁶	TOOKITE, OHT	Carrent	TYP.	MAX.	TYP.	Core Loss				
		uH±20%	A	mΩ	mΩ	A					
PA2247.472NLT	PM2247.472NLT	4.7	30	3.4	3.8	39	10.9				
PA2247.562NLT	PM2247.562NLT	5.6	28	3.82	4.2	34	9.6				
PA2247.682NLT	PM2247.682NLT	6.8	26	4.18	4.6	31	9.6				
PA2247.822NLT	PM2247.822NLT	8.2	25	6.0	7.2	28	8.6				
PA2247.103NLT	PM2247.103NLT	10.0	24	7.1	8.6	26	7.2				
PA2247.153NLT	PM2247.153NLT	15.0	18	9.2	11.5	20	6.1				
PA2247.223NLT	PM2247.223NLT	22.0	16	13.2	15.8	18	5.0				
PA2247.333NLT	PM2247.333NLT	33.0	13	18.7	20.0	16.7	3.9				

Notes:

- 1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- The saturation current is the current at which the initial inductance is guaranteed to drop by no more than 40%. The typical inductance at a specified current can be found on the typical performance curves.
- 3. The rated current is the DC current required to raise the component temperature by approximately 40 ° C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- 4. The part temperature (ambient+temp rise) should not exceed the upper operating temperature range under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- The PMxxxx.XXXNLT part numbers are AEC-Q200 and IATF16949 certified. The
 inductance and mechanical dimensions are 100% tested in production but do not
 necessarily meet a product capability index (Cpk) >1.33 and therefore may not strictly
 conform to PPAP.

6. Special Characteristics 🔘

Power.PulseElectronics.com P864. D (09/20)

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT




Mechanical

PA2247.XXXNLT and PM2247.XXXNLT D F XXXNL В D/C FINAL LAYOUT SUGGESTED PAD LAYOUT Series PA2247/PM2247 15.0(REF) 6.0 (REF) 15.0(REF 10.4±0.3 16.5±0.3 15.5±0.3 9.7±0.3 13.2±0.5 3.2±0.2

All Dimensions in mm.

2




SURFACE MOUNTING TYPE, REEL/TAPE LIST										
Corios	REEL SIZE (mm)		TA	QTY						
Series	А	G	P ₁	W	$K_{_{0}}$	PCS/REEL				
PA2247/PM2247	Ø330	32.4	24	32	10.5	150				

Power.PulseElectronics.com P864. D (09/20)


High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT





Typical Performance Curves
















Power.PulseElectronics.com


P864. D (09/20)

High Current Composite Inductor - PA2247XXXNLT and PM2247.XXXNLT





CORE LOSS vs FLUX DENSITY



For More Information:

Americas - prodinfo_power@pulseelectronics.com | Europe - power-apps-europe@pulseelectronics.com | Asia - power-apps-asia@pulseelectronics.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. Pulse Electronics, Inc. All rights reserved.

