
18



SMD CRYSTAL OSCILLATOR



• D3SX Series 3.2*2.5 OSC



FEATURES

- 3.2X2.5X1.2 Miniature Package
- Tri-State Enable/Disable
- TTL/HCMOS compatible
- Home security devices, power saving application, and low frequency specification circuit design looking for a smaller package
- 5.0V, 3.3V, 2.8V(2.5V), 1.8V option


Electrical Specifications

Parameter		Condition	D3SX				
Frequency Range	F0		1~54MHz	1~125MHz			
Frequency Stability*		All Condition	± 25 ppm, ± 50 ppm, ± 100 ppm				
Operating Temperature Range	Topr		-20°C~+70°C(-40°C~+85°C option)				
Storage Temperature Range	Tstg		-55°C∼+125°C				
Power supply Voltage	V_{DD}		5.0V+/-10%	3.3V+/-10%	2.8V+/-10%	1.8V+/-10%	
Supply Current	Idd	1MHz to 9.999MHz	15mA Max	8mA Max	7mA Max	6mA Max	
		10MHz to 34.999MHz	20mA Max	10mA Max	8mA Max	7mA Max	
		35MHz to 49.999MHz	35mA Max	25mA Max	20mA Max	15mA Max	
		50MHz to 54.000MHz	40mA Max	35mA Max	30mA Max	25mA Max	
Output Symmetry	Sym	At 1/2V _{DD}	40/60%(45/55% Option)				
Rise time	$T_{\rm r}$	$10\%\mathrm{V}_{\mathrm{DD}}\!\!\sim\!\!90\%\mathrm{V}_{\mathrm{DD}}$	5 nS Max	5 nS Max	6 nS Max	7 nS Max	
Fall Time	T_{f}	$90\%V_{DD}\sim10\%V_{DD}$	5 nS Max	5 nS Max	6 nS Max	7 nS Max	
Output Voltage	V_{OH}		90% V _{DD} Min				
	V_{OL}		10% Vdd Max				
Output Load HCMOS Load	i		15pF Typ.				
Start Time	Ts		10mS Max				
Stand-by Function			Yes				
Aging(First Year)		25℃±3℃	±2ppm Max				
Pin 1,tri-state function			Pin 1=H or openOutput active at pin 3				
Till Till State Tulletion			Pin 1=Lhigh impedance at pin 3				
Packing Unit			3000pcs/reel				

^{*}Include: 25°C tolerance, operating temperature range, input voltage change, aging, load change, shock and vibration

Mechanical Dimensions(mm)







Recommended Solder Pattern

1.20	1.00	1.20	1
			0.95
			0.80
			0.95 0
			0

^{**}Note: A 0.01uF bypass capacitor should be placed between Vdd(Pin4) and GND(Pin2) to Minimize power supply line noise

TAIWAN:

HOSONIC ELECTRONIC CO., LTD. 23-1 LANE 84. CHUN YING ST. SHULIN CHEN. TAIPEI 23804. TAIWAN WEB SITE:http://www.hosonic.com



CHINA: HANGZHOU HOSONIC ELECTRONIC CO., LTD. NO.242 LIANGBO ROAD. LIANGZHU TOWN. YUHANG DISTRICT, HANGZHOU, ZHEJIANG, CHINA

1: 86-571-88778189 **:** 86-571-88778857