






REV.	DATE	ECN NO.	MODIFICATION	APPROVER
A0	2018.01.06	/	精加工	JASON




PCB LAYOUT

极数	尺寸				ATOM料号
	A	B	C	D	
2	1.50	3.60	2.80	6.00	WF150**-01***
3	3.00	5.10	4.30	7.50	
4	4.50	6.60	5.80	9.00	WF15004-01202
5	6.00	8.10	7.30	10.50	
6	7.50	9.60	8.80	12.00	WF15006-01202
7	9.00	11.10	10.30	13.50	
8	10.50	12.60	11.80	15.00	
9	12.00	14.10	13.30	16.50	
10	13.50	15.60	14.80	18.00	
11	15.00	17.10	16.30	19.50	
12	16.50	18.60	17.80	21.00	
13	18.00	20.10	19.30	22.50	WF15013-01201
14	19.50	21.60	20.80	24.00	
15	21.00	23.10	22.30	25.50	

规格:

Specifications:

- 额定电流: 1A AC/DC (使用AWG#26时)
Current rating: 1A AC/DC (AWG#26)
- 额定电压: 125V AC/DC
Voltage rating: 125V AV/DC
- 使用温度范围: -25°C~+85°C (含通电时温度上升)
Temperature range: -25°C~+85°C (including temperature rise in applying electrical current)
- 接触电阻: 初期 / 20 mΩ 以下
环境试验后/30 mΩ 以下
Contact resistance: Initial value/10mΩ max
After environmental tests/20 mΩ max
- 绝缘电阻: 初期/500MΩ 以上
Insulation resistance: 500 MΩ min
- 耐电压: AC 800V/1分钟
Withstanding voltage: 500VAC/minute
- 适用电线范围: AWG#32~#26
Applicable wire: AWG#32 to #26
- 适合的印刷电路板厚度: 0.6mm、1.2mm、1.6mm
Applicable PC board thickness: 0.6mm、1.2mm、1.6mm
- 主体材料: Thermoplastic, UL94-V0, 天然色
Housing material: Thermoplastic, UL94-V0, natural
- 端子材料: 黄铜, 镀锡
Terminal material: brass, plating Tin



GENERAL TOLERANCE			UNITS	mm	NAME (INTENDED USE)		ATOM 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO., LTD.		
SELECT	✓		MAT'L	FINISH	WAFER 1.5 PITCH SMT		TITLE:		
TOL. ON:	1	2			3	PART NO. (INTENDED USE)		WAFER 1.5MM XP SMT 卧贴	
X.XXX	±0.15	±0.05	±0.15	Q'TY	WF150**-01***		DWG NO.:		
X.XX	±0.25	±0.13	±0.25		APPD:		ATOM-A03814		
X.X	±0.30	±0.25	±0.50		CHKD:		SCALE SHEET REV.		
X.	±0.38	±0.38	±1.00	DR: TOM		1:1 1/1 A0			
ANGLE	±5°								