

TJ11系列

● Feature 特性

- ◆ 电阻焊接 Resistance weiding
- ◆ 低功耗 Low power
- ◆ 高可靠性 High stability
- ◆ 频率范围宽 Wide frequency range
- ◆ 表面装贴 回流焊 IR R-flow




● Electrical specifications 电气参数

型号	Holder Type	TJ11 SMD1612
频率范围	Frequency Toleranc (ΔF) at25°C	30MHz~60.0MHz (Fund)
温度频差	Frequency rift	±10ppm~±20ppm
工作温度范围	Operating Temperature Range	-20°C~+70°C to -40°C~+85°C
储存温度范围	Storage Temperature Range	-20°C~+60°C to -55°C~+125°C
老化	Aging 25°C	±3ppm/year Maximum
静电容	Shunt Capacitance (C0)	7pf Maxmum
激励功率	Drive Level	10uw~50uw Typical
绝缘阻抗	Insulaton Resistance	500Mohms at DC 100V
负载电容	Load Capacitance (CL)	Suggested by customer

Ph Free

RoHS Compliant
Directive 2002/95/EC


● Mechanical Dimensions 外型尺寸



● Equivalent Series Resistance and Mode of Operation


等效电阻和振荡模式

Frequency Range 频率范围	ESR (ohm) 等效阻抗	Mode 振荡模式
30.000-40.000 MHz	80Max	Fundamental
40.000-60.000 MHz	60Max	Fundamental



Top View Suggested Layout

● Reflow condition 回流焊条件



● Frequency VS. Temperature Curne

