

H1 SERIES | H16WD

PANEL MOUNT



Features

- Ratings from 25A to 90A @ 48-690 VAC
- 1600 Volts Blocking
- SCR output for heavy industrial loads
- Zero Voltage or instantaneous turn-on outputs
- UL/CSA/VDE Approved, CE Compliant to EN60950-1

75A

H16WD4875

90A

H16WD4890

- Improved SEMS screw and washer
- Redesigned housing with anti-rotation barriers
- DC control

25A

H16WD4825

- Direct bond copper substrate
- EMC Compliant to Level 3
- Direct power lead frame

50A

H16WD4850

• Epoxy free design

For Generation 3 datasheet click here

PRODUCT SELECTION

Control Voltage

4-32 VDC

H1	_	SWD -	60	_	25	– к	_	G	_	Н	_	-10	
Serires —	_		Ť		Ť	Т		T		Τ		T	
H1													
Transient Overvoltage													
6WD : 1600 Vpk													
Operating Voltage -													
60 : 48-690 VAC													
Rated Load Current													
25 : 25 Amps 50 : 50 Amps	75 : 75 Amps 90 : 90 Amps												
Termination ——													
Blank: Screw F: Quick Connect (Up K: Hex standoffs (2)	to 50 Amps or	ıly) (1)											
nput Status LED —													
Blank: Not Included G: Included													
Thermal Pad ——													
Blank: Not Included H: Included													
Switching Type —													

Note: Not all part number combinations are available.

Contact Crydom Technical support for information on

the availability of a specific part number.

Page 1

Blank: Zero Voltage Turn-On

-10: Instantaneous Turn-On (3)

Required for valid part number

required for valid part number

For options only and not

OUTPUT SPECIFICATIONS (4)

Description	25A	50A	75A	90A
Operating Voltage (47-440Hz) [Vrms]	48-690	48-690	48-690	48-690
Transient Overvoltage [Vpk]	1600	1600	1600	1600
Rated Load Current [Arms] (5)(2)	25	50	75	90
Rated Load Current (UL508 Motor Controller) [Arms] (5)	10	20	30	45
Minimum Load Current [mArms]	150	150	150	150
Maximum Off-State Leakage Current @ Rated Voltage [mArms]	1.0	1.0	1.0	1.0
Minimum Off-State dv/dt @ Maximum Rated Voltage [V/µsec]	500	500	500	500
Maximum 1 Cycle Surge Current (50/60Hz) [Apk]	239/250	597/625	954/1000	1145/1200
Maximum I ² t for Fusing (50/60Hz) [A ² sec]	285/259	1779/1621	4555/4150	6560/5976
Thermal Resistance Junction to Case (Rjc) [°C/W]	0.8	0.45	0.3	0.27
Maximum On-State Voltage Drop @ Rated Current [Vrms]	1.3	1.3	1.2	1.2
HP rating UL 508/IEC60947[HP (KW)]: 240 VAC	1.5 (1.1)	3 (2.2)	5 (3.7)	7.5 (5.6)
HP rating UL 508/IEC60947[HP (KW)]: 380 VAC	2 (1.5)	5 (3.7)	7.5 (5.6)	15 (11.2)
HP rating UL 508/IEC60947[HP (KW)]: 480 VAC	3 (2.2)	5 (3.7)	10 (7.4)	20 (14.9)
HP rating UL 508/IEC60947[HP (KW)]: 600 VAC	3 (2.2)	10 (7.4)	15 (11.2)	25 (18.6)
Minimum Power Factor (at Maximum Load)	0.5	0.5	0.5	0.5

INPUT SPECIFICATIONS (4)


Description	DC Control
Control Voltage Range	4-32 VDC
Minimum Turn-On Voltage (6)	4.0 VDC
Must Turn-Off Voltage	1.0 VDC
Maximum Reverse Voltage	-32 VDC
Minimum Input Current @ Minimum Voltage (for on-state)	7mA
Maximum Input Current @ Maximum Voltage	12mA
Nominal Input Impedance	Current Regulated
Maximum Turn-On Time [msec] (7)	1/2 Cycle
Maximum Turn-Off Time [msec]	1/2 Cycle




GENERAL SPECIFICATIONS (4)

Description	Parameters				
Dielectric Strength, Input/Output/Base (50/60Hz)	4000 Vrms				
Minimum Insulation Resistance (@ 500 VDC)	10° Ohm				
Maximum Capacitance, Input/Output	8 pF				
Ambient Operating Temperature Range	-30 to 80 °C				
Ambient Storage Temperature Range	-40 to 125 °C				
Weight (typical)	2.6 oz (74.9 g)				
Housing Material	UL 94 V-0				
SSR Mounting Torque Range [in lbs/Nm]	18-20 (2-2.2)				
Baseplate Material	Aluminum				
Input Terminal Screw Torque Range [in-lb/Nm]	13-15 / 1.5-1.7				
Output Terminal Screw Torque Range [in lb/Nm]	18-20 (2-2.2)				
SSR Mounting Screw Torque Range [in-lb/Nm]	18-20 / 2.0-2.2				
Input/Load Terminal Screw Torque Range [in-lb/Nm] (2)	w/"K" option 8-10 / 0.9-1.13				
Input/Output Terminal Screw Thread Size	#6-32 UNC / #8-32 UNC				
Humidity per IEC60068-2-78	93% non-condensing				
	w/"G" option (green)				
MTBF (Mean Time Between Failures) at 40°C ambient temperature (8)	11,641,553 hours (1,328 years)				
MTBF (Mean Time Between Failures) at 60°C ambient temperature (8)	7,210,376 hours (823 years)				

WIRING DIAGRAM




Recommended Wire Sizes						
Terminals	Wire Size (Solid / Stranded)	Wire Pull-Out Strength (lb)[N]				
Input	24 AWG (0.2 mm²) / 0.2 [minimum]	10 [44.5]				
input	2 x 12 AWG (3.3 mm²) / 3.3 [maximum]	90 [400]				
	20 AWG (0.5 mm²) / 0.518 [minimum]	30 [133]				
Output	2 x 10 AWG (5.3 mm ²) / 5.3	110 [490]				
	2 x 8 AWG (8.4 mm ²) / 8.4 [maximum]	90 [400]				



Page 2


EQUIVALENT CIRCUIT BLOCK DIAGRAM




MECHANICAL SPECIFICATIONS (4)

Tolerances: ±0.02 in / 0.5 mm All dimensions are in: inches [millimeters]


Screw Termination




Hex Standoff Termination ("K" Option) (2)




Quick Connect Termination ("F" Option) - Up to 25 Amp (1)





Quick Connect Termination ("F" Option) - Up to 50 Amp (1)




SURGE CURRENT INFORMATION













Non repetitive peak surge current at Tj initial 40°C.

THERMAL DERATE INFORMATION











Designed in accordance with the requirements of IEC 62314

IEC 61000-4-2: Electrostatic Discharge – Level 3 IEC 61000-4-4: Electrically Fast Transients - Level 3

IEC 61000-4-5: Electrical Surges - Level 3

IEC 600068-2-6: Vibration 0.33mm and 0.75mm Amplitude over 10-55 Hz

IEC 600068-2-27: Shock Resistance 15g/11ms









Protective Cover & Hardware Kits

Protective Cover Part number: KS101



Clear plastic cover compatible with all new S1 designs. Safety covers provide added protection from electric shock when installing or checking equipment.

Hardware Kit Part number: HK4



Bag with 2 square brass accessories and 2 screw 8-32 x 5/8 for output. Used to mount TMR1 lug terminals.

Recommended Accessories									

Cover	Hardware Kit	Heat Sink Part No.	Thermal Resistance [°C/W]	Lug Terminal	Thermal Pad				
KS101	HK1	HS501DR	5.0	TRM1	HSP-1				
	HK4	HS301 / HS301DR	3.0	TRM6	HSP-2				
		HS251	2.5						
		HS202 / HS202DR	2.0						
		HS201 / HS201DR	2.0						
		HS172	1.7						
		HS151 / HS151DR	1.5						
		HS122 / HS122DR	1.2						
		HS103 / HS103DR	1.0						
		HS101	1.0						
		HS073	0.7						
		HS072	0.7						
		HS053	0.5						
		HS033	0.36						
		HS023	0.25						

GENERAL NOTES

- (1) Single pair (up to 25A) Double pair* (50A model only). *Caution: User must connect to both pairs.
- (2) Option "K" is designed and tested for use with printed circuit boards or ring/fork terminals having a thickness between 0.031 and 0.093 inches (0.79 to 2.36 mm), and loads rated up to 50 Amps. For higher load currents, the "K" standoff temperature must not exceed 105°C. For additional application assistance please contact Crydom Technical Support.
- (3) Instantaneous turn-on version is not recomended for capacitive loads. Use zero turn-on only.
- (4) All parameters at 25°C unless otherwise specified.
- (5) Heat sinking required, see derating curves.
- (6) Increase minimum voltage by 1V for operations from -20 to -30°C.
- (7) Turn-on time for Instantaneous turn-on versions is 0.02 msec.
- (8) All parameters at 50% power rating and 100% duty cycle (contact Crydom tech support for detailed report)
- (9) Load can be wired to either SSR output terminal 1 or 2.
- (10) Elective Input Status LED, "G" option.
- (11) Mechanical dimensions vary from G3 models.

For additional information or specific questions, contact Crydom Technical Support.







RISK OF MATERIAL DAMAGE AND HOT ENCLOSURE

- The product's side panels may be hot, allow the product to cool before touching
- Follow proper mounting instructions including torque values
- Do not allow liquids or foreign objects to enter this product

Failure to follow these instructions can result in serious injury, or equipment damage.



HAZARD OF ELECTRIC SHOCK, EXPLOSION OR ARC FLASH

- Disconnect all power before installing or working with this equipment
- Verify all connections and replace all covers before turning on nower

Failure to follow these instructions will result in death or serious injury

Page 6

Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

Americas

+1 (877) 502 5500 — Option 2 sales.crydom@sensata.com

Europe, Middle East & Africa

+44 (1202) 416170 ssr-info.eu@sensata.com

Asia Pacific

sales.isasia@list.sensata.com China +86 (21) 2306 1500 Japan +81 (45) 277 7117 Korea +82 (31) 601 2004 India +91 (80) 67920890 Rest of Asia +886 (2) 27602006 ext 2808