

## FEATURES


- Low current.(max.100mA).
- Low voltage..

## APPLICATIONS

- General purpose switching and amplification.

## ORDERING INFORMATION

Type No.	Marking	Package Code
BC856A/B	3A/3B	SOT-23
BC857A/B/C	3E/3F/3G	SOT-23
BC858A/B/C	3J/3K/3L	SOT-23



SOT-23		
Dim	Min	Max
A	2.70	3.10
B	1.10	1.50
C	1.0 Typical	
D	0.4 Typical	
E	0.35	0.48
G	1.80	2.00
H	0.02	0.1
J	0.1 Typical	
K	2.20	2.60


All Dimensions in mm

MAXIMUM RATING @  $T_a=25^\circ\text{C}$  unless otherwise specified

Symbol	Parameter	Value	Units
$V_{CBO}$	Collector-Base Voltage	BC856 -80	V
		BC857 -50	
		BC858 -30	
$V_{CEO}$	Collector-Emitter Voltage	BC856 -65	V
		BC857 -45	
		BC858 -30	
$V_{EBO}$	Emitter-Base Voltage	-5	V
$I_C$	Collector Current -Continuous	-0.1	A
$P_C$	Collector Dissipation	250	mW
$T_j, T_{stg}$	Junction and Storage Temperature	-65 to +150	°C


ELECTRICAL CHARACTERISTICS @  $T_a=25^\circ\text{C}$  unless otherwise specified

Parameter	Symbol	Test conditions	MIN	TYP	MAX	UNIT
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C=-10\mu\text{A}, I_E=0$	-80			V
			-50			
			-30			
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C=-10\text{mA}, I_B=0$	-65			V
			-45			
			-30			
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E=-1\mu\text{A}, I_C=0$	-5			V
Collector cut-off current	$I_{CBO}$	$V_{CB}=-30\text{V}, I_E=0$		-1	-15	nA
Emitter cut-off current	$I_{EBO}$	$V_{EB}=-5\text{V}, I_C=0$			-0.1	μA
DC current gain	BC856A,857A,858A BC856B,857B,858B BC857C,858C		$h_{FE}$	$V_{CE}=-5\text{V}, I_C=-2\text{mA}$	125 220 420	250 475 800
Collector-emitter saturation voltage	$V_{CE(\text{sat})}$	$I_C=-100\text{mA}, I_B=-5\text{mA}$ $I_C=-10\text{mA}, I_B=-0.5\text{mA}$			-0.65 -0.3	V
Base-emitter saturation voltage	$V_{BE(\text{sat})}$	$I_C=-10\text{mA}, I_B=-0.5\text{mA}$ $I_C=-100\text{mA}, I_B=-5\text{mA}$		-0.7 -0.85		V
Base-emitter voltage	$V_{BE(\text{on})}$	$I_C=-2\text{mA}, V_{CE}=-5\text{V}$ $I_C=-10\text{mA}, V_{CE}=-5\text{V}$	-0.6	-0.65	-0.75 -0.82	V
collector capacitance	$C_c$	$V_{CB}=-10\text{V}, I_e=I_e=0$ $f=1\text{MHz}$		4.5		pF
Transition frequency	F	$I_C=-200\mu\text{A}, V_{CE}=-5\text{V}$ , $R_S=2\text{k}\Omega, f=1\text{kHz}$ , $B=200\text{Hz}$		2	10	dB
Transition frequency	$f_T$	$V_{CE}=-5\text{V}, I_C= -10\text{mA}$ $f=100\text{MHz}$	100			MHz

TYPICAL CHARACTERISTICS @  $T_a=25^\circ\text{C}$  unless otherwise specified

BC857A;  $V_{CE} = -5 \text{ V}$ .


- (1)
- $T_{\text{amb}} = 150 \text{ }^\circ\text{C}$
- .
- 
- (2)
- $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$
- .
- 
- (3)
- $T_{\text{amb}} = -55 \text{ }^\circ\text{C}$
- .

Fig.1 DC current gain as a function of collector current; typical values.


BC857A;  $V_{CE} = -5 \text{ V}$ .


- (1)
- $T_{\text{amb}} = -55 \text{ }^\circ\text{C}$
- .
- 
- (2)
- $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$
- .
- 
- (3)
- $T_{\text{amb}} = 150 \text{ }^\circ\text{C}$
- .

Fig.2 Base-emitter voltage as a function of collector current; typical values.


BC857A;  $I_C/I_B = 20$ .


- (1)
- $T_{\text{amb}} = 150 \text{ }^\circ\text{C}$
- .
- 
- (2)
- $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$
- .
- 
- (3)
- $T_{\text{amb}} = -55 \text{ }^\circ\text{C}$
- .

Fig.3 Collector-emitter saturation voltage as a function of collector current; typical values.


BC857A;  $I_C/I_B = 20$ .


- (1)
- $T_{\text{amb}} = -55 \text{ }^\circ\text{C}$
- .
- 
- (2)
- $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$
- .
- 
- (3)
- $T_{\text{amb}} = 150 \text{ }^\circ\text{C}$
- .

Fig.4 Base-emitter saturation voltage as a function of collector current; typical values.




BC857B;  $V_{CE} = -5$  V.  
(1)  $T_{amb} = 150$  °C.  
(2)  $T_{amb} = 25$  °C.  
(3)  $T_{amb} = -55$  °C.

Fig.5 DC current gain as a function of collector current; typical values.




BC857B;  $V_{CE} = -5$  V.  
(1)  $T_{amb} = -55$  °C.  
(2)  $T_{amb} = 25$  °C.  
(3)  $T_{amb} = 150$  °C.

Fig.6 Base-emitter voltage as a function of collector current; typical values.




BC857B;  $I_C/I_B = 20$ .  
(1)  $T_{amb} = 150$  °C.  
(2)  $T_{amb} = 25$  °C.  
(3)  $T_{amb} = -55$  °C.

Fig.7 Collector-emitter saturation voltage as a



BC857B;  $I_C/I_B = 20$ .  
(1)  $T_{amb} = -55$  °C.  
(2)  $T_{amb} = 25$  °C.  
(3)  $T_{amb} = 150$  °C.


Fig.8 Base-emitter saturation voltage as a



BC857C;  $V_{CE} = -5$  V.

- (1)  $T_{amb} = 150$  °C.
- (2)  $T_{amb} = 25$  °C.
- (3)  $T_{amb} = -55$  °C.


Fig.9 DC current gain as a function of collector current; typical values.



BC857C;  $V_{CE} = -5$  V.

- (1)  $T_{amb} = -55$  °C.
- (2)  $T_{amb} = 25$  °C.
- (3)  $T_{amb} = 150$  °C.


Fig.10 Base-emitter voltage as a function of collector current; typical values.



BC857C;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = 150$  °C.
- (2)  $T_{amb} = 25$  °C.
- (3)  $T_{amb} = -55$  °C.

Fig.11 Collector-emitter saturation voltage as a function of collector current; typical values.



BC857C;  $I_C/I_B = 20$ .

- (1)  $T_{amb} = -55$  °C.
- (2)  $T_{amb} = 25$  °C.
- (3)  $T_{amb} = 150$  °C.

Fig.12 Base-emitter saturation voltage as a function of collector current; typical values

Device	Package	Shipping
BC856/857/858	SOT-23	3000/Tape&Reel