

RS0806A/RS0806B Series 8A TRIACs

DESCRIPTION:

High current density due to double mesa technology, SIPOS and Glass Passivation.

RS0806A/B series triacs is suitable for general purpose AC switching, They can be used as an ON/OFF function in applications such as static relays, heating regulation, induction motor stating circuits...or for phase contol operation, light dimmers, motor speed controllers.

RS0806A/B-SW -CW -BW are 3 quadrants triacs, They are specially recommended for use on inductive loads.

RS0806A are isolated in internal, they provide a 2500V RMS isolation voltage from all three terminals to external heat sink.

MAIN FEATURES

| Symbol | Value | Unit |
|-----------|-------------|------|
| IT(RMS) | 8 | Α |
| VDRM/VRRM | 600 and 800 | V |
| Vтм | 1.55 | V |

RS0806B (TO-220B non-insulated) RS0806A (TO-220A insulated) T1 (1) G (3) T2 (2)

ABSOLUTE MAXIMUM RATINGS

| Parameter | Symbol | Value | Unit | | |
|---|---|-----------|-------------|-----|--|
| Storage junction temperature range | | | -40 to +150 | °C | |
| Operrating junction temperature range | | Tj | -40 to +125 | °C | |
| Repetitive Peak Off-state Voltage | Tj=25°C | VDRM | 600and800 | | |
| Repetitive Peak Reverse Voltage | Tj=25°C | VRRM | 600and800 | V | |
| Non repetitive Surge Peak Off-state Voltage | Ion repetitive Surge Peak Off-state Voltage | | | V | |
| Non repetitive Peak Reverse Voltage | Non repetitive Peak Reverse Voltage tp=10ms,Tj=25°C | | | | |
| RMS on-state current (full sine wave) | JST08B Tc=110°C | IT(RMS) | 8 | А | |
| Nivio on-state current (tuli sine wave) | JST08A Tc=100°C | TI(RIVIS) | | | |
| Non repetitive surge peak on-state current | f = 60 Hz t=16.7ms | ITSM | 84 | А | |
| (full cycle,Tj=25°C) | f = 50 Hz t=20ms | 115101 | 80 | | |
| I²t Value for fusing | tp=10ms | l²t | 36 | A²s | |
| Critical rate of rise of on-state current (IG=2×IGT,tr≤100 ns,f=120Hz,Tj=125°C) | dI /dt | 50 | A/µs | | |
| Peak gate current (tp=20us,Tj=125°C) | | | 4 | Α | |
| Peak Gate Power Dissipation (tp=20us,Tj=125°C) | | | 10 | W | |
| Average gate power dissipation (Tj=125°C) | | | 1 | W | |



ELECTRICAL CHARACTERISTICS (Tj=25°C unless otherwise specified)

3 Quadrants

| Symbol | Test Condition | Quadrant | | RS0806A/RS0806B | | | | Unit |
|----------------------|------------------------------|----------|------|-----------------|----|-----|------|-------|
| Cymbol | rest condition | Quadrant | | TW | SW | CW | BW | Offic |
| lgт | Vp=12V Br=22O | 1-11-111 | MAX. | 5 | 10 | 35 | 50 | mA |
| VD=12V RL=33Ω VGT | | 1-11-111 | MAX. | 1.3 | | | | V |
| VGD | VD=VDRM RL=3.3KΩ Tj =125℃ | 1-11-111 | MIN. | 0.2 | | | V | |
| lL | IG=1.2IGT | I-III | MAX. | 15 | 20 | 50 | 70 | mA |
| | | MAX. | 25 | 35 | 60 | 80 | mA | |
| Iн | IT =100mA | | MAX. | 10 | 15 | 40 | 60 | mA |
| dV/dt | VD=67%VDRM gate open Tj=125℃ | | MIN. | 20 | 40 | 400 | 1000 | V/µs |
| (dV/dt)c | (dl/dt)c=3.5A/ms Tj=125℃ | | | 0.5 | 1 | 10 | 25 | V/µs |

4 Quadrants

| Symbol | Test Condition | Quadrant | | RS0806A/RS0806B | | Unit |
|----------|-----------------------------|----------------|------|-----------------|-----------|------|
| Cyrribol | rest Condition | Quadrant | | С | В | |
| lgт | Vp=12V Br=22O | I-II-III IV | MAX. | 25 50 | 50 100 | mA |
| VGT | - VD=12V RL=33Ω | ALL | MAX. | 1.3 | | V |
| VGD | VD=VDRM RL=3.3KΩ Tj =125℃ | ALL | MIN. | 0. | 0.2 | |
| IL | L- 4 0L- | I-III-IV | MAX. | 35 | 50 | mA |
| | IG=1.2IGT | | MAX. | 60 | 80 | mA |
| lн | IT =100mA | MAX. | 25 | 50 | mA | |
| dV/dt | VD=67%VDRM gate open Tj=125 | MIN. | 200 | 400 | V/µs | |
| (dV/dt)c | (dl/dt)c=3.5A/ms Tj=125℃ | MIN. | 5 | 10 | V/µs | |


STATIC CHARACTERISTICS

| Symbol | Parameter | | Value(MAX.) | Unit |
|----------------------|------------------|---------|-------------|------|
| Vтм | Ітм=11A,tp=380µs | Tj=25℃ | 1.55 | V |
| IDRM VD=VDRM VR=VRRM | | Tj=25℃ | 5 | μА |
| IRRM | VD-VDKW VK-VKKM | Tj=125℃ | 1 | mA |

THERMAL RESISTANCES


| Symbol | Param | Value | Unit | | |
|---------------------------------------|----------------------|--------|------|--------------|--|
| Rth(J -C) Junction to Case(AC) | Junction to Case(AC) | JST08B | 1.6 | °C // A / | |
| | Junction to Case(AC) | JST08A | 2.5 | - °C/W | |
| Rth(j-a) Junction to ambient (S=1cm²) | JST08A | 60 | °C/W | | |
| | (S=1cm²) | JST08B | 60 | C/ VV | |

ORDERING INFORMATION



PACKAGE MECHANICAL DATA

TO-220A insulated package and TO-220B non-insulated package



| | Dimensions | | | | | |
|------|-------------|------|------|--------|-------|-------|
| Ref. | Millimeters | | | Inches | | |
| | Min. | Тур. | Max. | Min. | Тур. | Max. |
| Α | 4.4 | | 4.6 | 0.173 | | 1.181 |
| В | 0.61 | | 0.88 | 0.024 | | 0.034 |
| С | 0.46 | | 0.70 | 0.018 | | 0.027 |
| C2 | 1.23 | | 1.32 | 0.048 | | 0.051 |
| C3 | 2.4 | | 2.72 | 0.094 | | 0.107 |
| D | 8.6 | | 9.7 | 0.338 | | 0.382 |
| Е | 9.8 | | 10.4 | 0.386 | | 0.409 |
| F | 6.2 | | 6.6 | 0.244 | | 0.259 |
| G | 4.8 | | 5.4 | 0.189 | | 0.213 |
| Н | 28.0 | | 29.8 | 11.0 | | 11.7 |
| L1 | | 3.75 | | | 0.147 | |
| L2 | 1.14 | | 1.7 | 0.044 | | 0.066 |
| L3 | 2.65 | | 2.95 | 0.104 | | 0.116 |
| V1 | | 40° | | | 40° | |

Marking:




FIG.1:Maximum power dissipation versus RMS on-state current(full cycle)




FIG.3:On-state characteristics (maximum

values).




FIG.5:Non-repetitive surge peak on-state current for a sinusoidal pulse with width tp<10ms,and corresponding value of l²t.




FIG.2:RMS on-state current versus case temperature(full cycle)




FIG.4:Surge peak on-state current versus number of cycles.




FIG.6:Relative variations of gate trigger current, holding current and latching current versus junction temperature(typical values)

