

Multilayer Chip Ferrite Bead



◆ Features

- 1、 Internal silver printed layers and magnetic shielded structures to minimize crosstalk
- 2、 It has sharp impedance characteristics at desirable frequency and does not affect the signal frequency
- 3、 SMD Type & suitable for reflow and wave soldering
- 4、 Four types material and wide range of impedance values for various applications
- 5、 Excellent solderability and heat resistance
- 6、 RoHS Compliant.



◆ Application

Filtering between analog and digital circuitry, clock Generation circuitry, I/O interconnects, isolation between RF noisy circuits and logic devices susceptible to functional degradation, power supply filtering to prevent conducted RF energy from corrupting the power generation circuitry, high frequency EMI prevention of computer, printers, VCRs, TVs and portable telephones.


◆ Dimensions Unit: mm

Size(EIA)	0603 (0201)	1005 (0402)	1608 (0603)	2012 (0805)
L	0.60±0.03	1.00±0.10	1.60±0.150	2.00±0.20
W	0.30±0.03	0.50±0.10	0.80±0.150	1.25±0.20
T	0.30±0.03	0.50±0.10	0.80±0.150	0.90±0.20
E	0.15±0.05	0.25±0.10	0.30±0.20	0.50±0.30

◆ PRODUCT IDENTIFICATION

SBM 1608 K 601 A S P
(1) (2) (3) (4) (5) (6) (7)

- (1) Series Type
- (2) Chip Size (mm) :Length X Width
- (3) Material Code
- (4) Nominal Impedance:601=600Ω;
102=1000Ω
- (5) Rated Curren: A=50mA; B=100mA;C=150mA;
D=200mA;E=300mA;F=400mA;
G=500mA;H=600mA;I=700mA;
J=800mA;K=900mA;L=1000mA.
- (6) Company Code
- (7) Packaging: E- Embossed plastic tape, 7" reel
P – Embossed paper tape, 7" reel



◆ Specification

Part Number	Impedance (Ω)	Test Frequency (MHz)	DCR Max. (Ω)	Rated Current (mA)
SBM0603 Series				
SBM0603G100DSP	10±25%	100	0.25	200
SBM0603G220DSP	22±25%	100	0.45	200
SBM0603G600DSP	60±25%	100	0.70	200
SBM0603G800DSP	80±25%	100	0.90	200
SBM0603G121DSP	120±25%	100	1.00	200
SBM0603G601DSP	600±25%	100	1.70	200
SBM1005 Series				
SBM1005G050HSP	0~15	100	0.15	600
SBM1005G470HSP	47±25%	100	0.15	600
SBM1005G600HSP	60±25%	100	0.20	600
SBM1005G750GSP	75±25%	100	0.30	500
SBM1005G101GSP	100±25%	100	0.35	500
SBM1005G121GSP	120±25%	100	0.40	500
SBM1005G221GSP	220±25%	100	0.70	500
SBM1005K301GSP	300±25%	100	0.80	500
SBM1005K601GSP	600±25%	100	1.00	500
SBM1005K102ESP	1000±25%	100	1.20	300
SBM1005B152BSP	1500±25%	100	1.40	100
SBM1005B182ASP	1800±25%	100	1.80	50
SBM1608 Series				
SBM1608G050JSP	0~15	100	0.05	800
SBM1608G300JSP	30±25%	100	0.05	800
SBM1608G600HSP	60±25%	100	0.10	600
SBM1608G900HSP	90±25%	100	0.15	600
SBM1608G121HSP	120±25%	100	0.20	600
SBM1608G221GSP	220±25%	100	0.30	500
SBM1608G331GSP	330±25%	100	0.35	500
SBM1608G471GSP	470±25%	100	0.45	500
SBM1608G601GSP	600±25%	100	0.50	500
SBM1608G102ESP	1000±25%	100	0.60	300
SBM1608G152CSP	1500±25%	100	0.75	150

◆ Specification

Part Number	Impedance (Ω)	Test Frequency (MHz)	DCR Max. (Ω)	Rated Current (mA)
SBM1608 Series				
SBM1608K202BSP	2000 \pm 25%	100	1.00	100
SBM1608K222BSP	2200 \pm 25%	100	1.00	100
SBM1608K252BSP	2500 \pm 25%	100	1.20	100
SBM1608K272BSP	2700 \pm 25%	100	1.40	100
SBM2012 Series				
SBM2012G050LSP	0~15	100	0.07	1000
SBM2012G300LSP	30 \pm 25%	100	0.10	1000
SBM2012G600JSP	60 \pm 25%	100	0.20	800
SBM2012G121JSP	120 \pm 25%	100	0.22	800
SBM2012G221HSP	220 \pm 25%	100	0.25	600
SBM2012G301HSP	300 \pm 25%	100	0.30	600
SBM2012G421HSP	420 \pm 25%	100	0.30	600
SBM2012G601HSP	600 \pm 25%	100	0.35	600
SBM2012G102FSP	1000 \pm 25%	100	0.40	500
SBM2012G152DSP	1500 \pm 25%	100	0.45	200
SBM2012G222DSP	2200 \pm 25%	100	0.60	200
SBM2012G252DSP	2500 \pm 25%	100	0.70	200
SBM2012G272DSP	2700 \pm 25%	100	0.80	200


◆ General Technical Data

Operating Temperature Range	-55 $^{\circ}$ C ~ +125 $^{\circ}$ C
Storage Condition	Less than 40 $^{\circ}$ C and 70% RH
Soldering Method	Reflow or Wave Soldering


◆ Characteristics

SBM0603 TYPE


SBM0603G100DSP




SBM0603G220DSP




SBM0603G600DSP




SBM0603G800DSP



SBM0603G121DSP




SBM0603G601DSP




SBM1005 TYPE


SBM1005G050HSP



SBM1005G300HSP




SBM1005G600HSP




◆ Characteristics

SBM1005 TYPE


SBM1005K121GSP




SBM1005K221GSP




SBM1005K301GSP




SBM1005K421GSP




SBM1005K601GSP




SBM1005K102ESP



SBM1005B152BSP




SBM1005B182ASP




◆ Characteristics

SBM1608 TYPE


SBM1608G050JSP




SBM1608G100FSP




SBM1608G300JSP




SBM1608G600HSP




SBM1608G750HSP




SBM1608G900HSP




SBM1608G121HSP




SBM1608G221GSP




SBM1608G331GSP




SBM1608G471GSP



SBM1608G601GSP




SBM1608G102ESP




◆ Characteristics

SBM1608 TYPE


SBM1608G152KSP




SBM1608K202BSP




SBM1608K222BSP



SBM1608K252BSP




SBM1608K272BSP




SBM2012 TYPE


SBM2012G050LSP




SBM2012G300LSP




SBM2012G600JSP




SBM2012G121JSP



SBM2012G221HSP




SBM2012G301HSP




◆ Characteristics

SBM2012 TYPE


SBM2012G421HSP




SBM2012G601HSP




SBM2012G102FSP




SBM2012G152DSP




SBM2012G222DSP



SBM2012G252DSP



SBM2012G272DSP



◆ Package

Size EIA (EIA)	0603 (0201)	1005 (0402)	1608 (0603)	2012 (0805)
Standard Packing Quantity (pcs / reel)	15,000	10,000	4,000	4,000