Axial Lead & Cartridge Fuses PICO® II > Slo-Blo® Fuse > 473 Series

473 Series, PICO® II Slo-Blo® Fuse











Agency Approvals

Agency	Agency File Number	Ampere Range
71 °	E10480	0.375A - 7A
(f) 29862		0.375A - 7A
PS	NBK200416-JP1021	1A - 5A

Additional Information







Description

The PICO® II Slo-Blo® Fuse combines time-delay performance characteristics with the proven reliability of a PICO® Fuse.

Features

- Enhanced inrush withstand
- Small size
- Wide range of current ratings (0.375A - 7A)
- Halogen free and RoHS complaint
- Wide operating temperature range
- Low temperature rerating

Applications

- Flat-panel Display TV
- LCD monitor
- Lighting system
- Medical equipment
- Industrial equipment

Electrical Characteristics

% of Ampere Rating	Opening Time	
100%	4 Hours, Min .	
200%	1 Sec., Min. ; 60 Sec., Max.	
300%	0.2 Sec., Min. ; 3 Sec., Max.	
800%	0.002 Sec., Min. ; 0.1 Sec., Max.	

Electrical Characteristics


Ampere		Max		Nominal Cold Nominal Nom		. Nominal Cold Nominal Nom Agency App		ncy Appro	provals	
Rating (A)	Amp Code	Voltage Rating (V)	Interrupting Rating	Resistance (Ohms)	Melting I ² t (A ² sec)	Voltage Drop (mV)	<i>81</i> 7	(PS E	
0.375	.375	125		1.7550	0.085	0.840	Х	X		
0.500	.500	125		1.1370	0.210	0.775	Х	X		
0.750	.750	125		0.4900	0.760	0.429	Х	X		
1.00	001.	125		0.3000	2.010	0.353	Х	Х	Х	
1.50	01.5	125		0.1170	3.940	0.208	Х	X	Х	
2.00	002.	125		0.0720	7.600	0.180	Х	X	Х	
2.25	2.25	125	50A@125VAC/DC	0.0640	9.280	0.164	Х	X	X	
2.50	02.5	125		0.0520	13.00	0.153	X	X	Х	
3.00	003.	125		0.0380	21.00	0.140	Х	X	X	
3.50	03.5	125		0.0240	26.80	0.094	Х	X	X	
4.00	004.	125		0.0200	35.00	0.086	Х	Х	Х	
5.00	005.	125		0.0133	54.80	0.074	Х	Х	X	
7.00	007.	125		0.0092	105.00	0.070	Х	Х		

Axial Lead & Cartridge Fuses

PICO® II > Slo-Blo® Fuse > 473 Series



Temperature Re-rating Curve



Note:

Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation

Soldering Parameters

Recommended Process Parameters:


Wave Parameter	Lead-Free Recommendation	
Preheat:	(Typical Industry Recommendation)	
(Depends on Flux Activation Temperature) Temperature Minimum:	100°C	
Temperature Maximum:	150°C	
Preheat Time:	60-180 seconds	
Solder Pot Temperature:	260°C Maximum	
Solder Dwell Time:	2-5 seconds	

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or **Convection Reflow process.**

Average Time Current Curves




Axial Lead & Cartridge Fuses PICO® || > Slo-Blo® Fuse > 473 Series

Product Characteristics


Materials	Encapsulated, Epoxy-Coated Body; Solder Coated Copper wire leads; RoHS compliant Product: Pure Tin-coated Copper wire leads		
Solderability	MIL-STD-202, Method 208		
Lead Pull Force	MIL-STD-202, Method 211, Test Condition A (will withstand 7 lbs. axial pull test)		
Operating Temperature	-60°C to +125°C (Consider re-rating)		
Shock	MIL-STD-202, Method 213, Test Condition I (100 G's peak for 6 milliseconds)		

Vibration	MIL-STD-202, Method 201 (10–55 Hz); MIL-STD-202, Method 204, Test Condition C (55–2000 Hz at 10 G's Peak)		
Salt Spray	MIL-STD-202, Method 101, Test Condition B		
Insulation Resistance (After Opening):	MIL-STD-202, Method 302, (10,000 ohms minimum at 100 volts)		
Resistance to Soldering Heat	MIL-STD-202, Method 210, Test Condition C (20 sec at 260°C)		
Thermal Shock	MIL-STD-202, Method 107, Test Condition B (–65°C to 125°C)		
Moisture Resistance	MIL-STD-202, Method 106 (90–98% RH), Heat (65°C)		

Dimensions



Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity & Packaging Code		
*T1: 52.4mm (2.062") Tape and Reel	EIA 296	Please refer to available quantities above in "Part Numbering System"		

Notes: * T1 dimension is defined as the length of the component between the two tapes. The full component length is 62.7mm (2.468").

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse. Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.