INDUCTORS

Inductors for power circuits Thin-film metal magnetic material TFM-ALVA series (for automotive)

AEC-Q200

TFM252012ALVA type



FEATURES

- O By using metal magnetic material with high Saturation magnetic flux density the excellent DC bias characteristics needed for inductors for power circuits can be achieved.
- With the same product shape and terminal structure as general chip parts it has excellent mounting stability characteristics and can also be mounted to general-purpose land patterns.
- O By using a closed magnetic circuit structure leakage flux is minimized.
- The rated voltage of 40V is realized by design that emphasizes voltage resistance.
- Operating temperature range: –55 to +150°C (including self-temperature rise)

O Compliant with AEC-Q200

APPLICATION

O For automotive (headlights, electronic power steering, meter cluster, ADAS ECU, other)

PART NUMBER CONSTRUCTION

TFM	252012	ALV	A	4R7	М	Т	AA
Series name	L×W×H dimensions 2.5×2.0×1.2 mm	Characteristic type	Automotive use	Inductance (μH)	Inductance tolerance	Packaging style	Internal code

CHARACTERISTICS SPECIFICATION TABLE

L		L measuring frequency	DC resistar	Rated cu	Rated current*			Rated voltage	Part No.	
(µH)	Tolerance	(MHz)	$(\mathbf{m}\Omega)$ max.	(mΩ)typ.	lsat (A)max.	(A)typ.	ltemp (A)max.	(A)typ.	(V)max.	
1.0	±20%	1	42	35	4.2	4.7	3.7	4.1	40	TFM252012ALVA1R0MTAA
1.5	±20%	1	60	52	3.3	3.9	3.1	3.3	40	TFM252012ALVA1B5MTAA
		1		-					-	
2.2	±20%	1	84	75	2.8	3.3	2.6	2.8	40	TFM252012ALVA2R2MTAA
3.3	±20%	1	140	124	2.1	2.5	2.0	2.2	40	TFM252012ALVA3R3MTAA
4.7	±20%	1	200	180	1.9	2.2	1.6	1.8	40	TFM252012ALVA4R7MTAA

* Rated current: smaller value of either Isat or Itemp.

Isat: When based on the inductance change rate (30% below the initial L value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

Please contact us for the rated current vs. temperature characteristics (derating) at a product temperature of 85°C or higher.

Measurement equipment

Product No.	Manufacturer	
4294A	Keysight Technologies	
Digital Milliohm Meter		
4285A+42841A+42842C	Keysight Technologies	
	4294A Digital Milliohm Meter	4294A Keysight Technologies Digital Milliohm Meter

* Equivalent measurement equipment may be used.

TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range*	Storage temperature range**	Individual weight		
–55 to +150 °C	–55 to +150 °C	35 mg		
* Operating temperature range includes self-temperature rise.				

** The storage temperature range is for after the assembly.




⊗TD

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (1/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

20200823


TFM252012ALVA type

L FREQUENCY CHARACTERISTICS



Product No.	Manufacturer		
4294A	Keysight Technologies		
* Equivalent measurement equipment may be used			

■ INDUCTANCE VS. DC BIAS CHARACTERISTICS




* Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (2/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

INDUCTORS

TFM252012ALVA type


SHAPE & DIMENSIONS



Dimensions in mm


PACKAGING STYLE

REEL DIMENSIONS




Dimensions in mm

TAPE DIMENSIONS



Dimensions in mm

Туре	А	В	К
TFM252012ALVA	2.2	2.7	1.3




Dimensions in mm


PACKAGE QUANTITY

Package quantity	3000 pcs/reel
------------------	---------------

RECOMMENDED LAND PATTERN



Dimensions in mm



A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/4)

20200823

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

A RE	MINDERS
less).	torage conditions (temperature: 5 to 40°C, humidity: 20 to 75% RH o
If the storage period elapses, the soldering of the terminal elect	-
O Do not use or store in locations where there are conditions such	h as gas corrosion (salt, acid, alkali, etc.).
 Before soldering, be sure to preheat components. The preheating temperature should be set so that the temperators does not exceed 150°C. 	ature difference between the solder temperature and chip temperatur
 Soldering corrections after mounting should be within the range If overheated, a short circuit, performance deterioration, or lifes 	-
When embedding a printed circuit board where a chip is moun the overall distortion of the printed circuit board and partial distortion	ted to a set, be sure that residual stress is not given to the chip due to ortion such as at screw tightening portions.
 Self heating (temperature increase) occurs when the power is design. 	s turned ON, so the tolerance should be sufficient for the set therm
Carefully lay out the coil for the circuit board design of the non- A malfunction may occur due to magnetic interference.	magnetic shield type.
\bigcirc Use a wrist band to discharge static electricity in your body thro	bugh the grounding wire.
O Do not expose the products to magnets or magnetic fields.	
\bigcirc Do not use for a purpose outside of the contents regulated in th	e delivery specifications.
telecommunications equipment, home appliances, amusement ment, measurement equipment, industrial robots) and to be use is mounted in a vehicle) or standard applications as general el as general electronic equipment in automotive applications in a while the said automotive or general electronic equipment inclu usage methods, respectively. Other than automotive or automotive the applications listed below, whose performance and/or quality malfunction or defect could cause serious damage to society, p Please understand that we are not responsible for any damage below or for any other use exceeding the range or conditions set	ge or liability caused by use of the products in any of the application
set forth in this specification, please contact us.	
(1) Aerospace/aviation equipment(2) Transportation equipment (electric trains, ships, etc.)	(8) Public information-processing equipment(9) Military equipment
(3) Medical equipment	(10) Electric heating apparatus, burning equipment
(4) Power-generation control equipment(5) Atomic energy-related equipment	(11) Disaster prevention/crime prevention equipment(12) Safety equipment
CD AIONIC ENEROV-LEIZIEO EOUIDINENI	(12) Galety equipment
(6) Seabed equipment	(13) Other applications that are not considered general-purpos

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. (4/4) Please note that the contents may change without any prior notice due to reasons such as upgrading.

20200823