

Features

- Halogen Free Available Upon Request By Adding Suffix "-HF"
- Glass Passivated Chip
- Super Fast Switching For High Efficiency
- Low Reverse Leakage Current
- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix Designates Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Moisture Sensitivity Level 1

Maximum Ratings

- Operating Junction Temperature Range: -50°C to +150°C
- Storage Temperature Range: -50°C to +150°C
- Maximum Thermal Resistance: 20°C/W Junction to Lead


MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
US2AA	US2A	50V	35V	50V
US2BA	US2B	100V	70V	100V
US2CA	US2C	150V	105V	150V
US2DA	US2D	200V	140V	200V
US2GA	US2G	400V	280V	400V
US2JA	US2J	600V	420V	600V
US2KA	US2K	800V	560V	800V
US2MA	US2M	1000V	700V	1000V

Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	I _{F(AV)}	2.0A	T _L =110°C
Peak Forward Surge Current	I _{FSM}	50A	8.3ms,Half Sine
Maximum Instantaneous Forward Voltage US2AA-US2DA US2GA US2JA-US2MA	V _F	1.0V 1.4V 1.7V	I _{FM} =2.0A; T _A =25°C
Maximum DC Reverse Current At Rated DC Blocking Voltage	I _R	5.0μA 50μA	T _A =25⁰C; T _A =125⁰C
Maximum Reverse Recovery Time US2AA-US2GA US2JA-US2MA	Trr	50ns 75ns	I _F =0.5A; I _R =1.0A; Irr=0.25A
Typical Junction Capacitance	CJ	28pF	Measured at 1.0MHz, V _R =4.0V


Note :1. High Temperature Solder Exemption Applied, See EU Directive Annex Notes 7a.

2 Amp Ultra Fast Rectifier 50 to 1000 Volts



DIMENSIONS						
DIM	INCHES		MM		NOTE	
	MIN	MAX	MIN	MAX	NOTE	
A	0.075	0.096	1.90	2.44		
В	0.050	0.064	1.27	1.63		
С	0.002	0.008	0.051	0.203		
D		0.020		0.51		
E	0.030	0.060	0.76	1.52		
F	0.065	0.091	1.65	2.32		
G	0.189	0.220	4.80	5.59		
Н	0.157	0.187	4.00	4.75		
J	0.090	0.115	2.25	2.92		

SUGGESTED SOLDER PAD LAYOUT





Curve Characteristics







Fig. 3 - Typical Instantaneous Forward Characteristics











Ordering Information

Device	Packing	
Part Number-TP	Tape&Reel: 5Kpcs/Reel	

Note : Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.