





REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD


Electrical  
 Current Rating: 0.5A AC(rms)/DC  
 Voltage Rating: 50V AC(rms)/DC  
 Contact Resistance: 40 mΩ Max  
 Insulation Resistance: 500 MΩ MIN  
 Withstanding Voltage: 250V AC r.m.s  
 Temperature Range-Operating: -25°C ~ +85°C  
 Material and Plating  
 Housing: LCP( UL 94V-0)  
 Contact Pin: Phosphor Bronze  
 Plating: Gold Plated




### Ordering Information

FBB 050 01 - F XX S 1 XX 3 W5 M  
 1 2 3 4 5 6 7 8 9 10 11



1 Category FBB-Board To Board	2 Series Number 050-Pitch0.5mm	3 Distinction No. 01	4 Type F-Female	5 Circuits XX	6 Entry Angle S-180° Vertical
7 Plating 1-Gold Plated	8 Thickness of Plating 00-Gold Flash 01-1μ"	9 Material-Resin 3-LCP	10 Color-Resin W5-White	11 Packaging M-Reel	



THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 26/SEPT/13	PART NO. FBB05001-FXXS1XX3W5M	TEM NO. FBB05001-F	 Leader Of Industry
	X.±.012(0.30)	X.±5'	CHECKED BY CHERRY	DATE 26/SEPT/13	TITLE Board to Board Pitch 0.5mm 180° Vertical (SMT)		
DESIGN UNITS Inch (metric)	X.X±.008(0.20)	.X'±2'	DRAWN BY JACOB	DATE 26/SEPT/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
SCALE 5:1	SIZE A4	X.XX±.006(0.15)					
		X.XXX±.004(0.10)					

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

Circuits (n)	Part No.	Dimensions(in./mm)		
		A	B	C
10	FBB05001-F10S1XX3W5M	.220(5.60)	.138(3.50)	.079(2.00)
12	FBB05001-F12S1XX3W5M	.240(6.10)	.157(4.00)	.098(2.50)
14	FBB05001-F14S1XX3W5M	.260(6.60)	.177(4.50)	.118(3.00)
16	FBB05001-F16S1XX3W5M	.280(7.10)	.197(5.00)	.138(3.50)
20	FBB05001-F20S1XX3W5M	.319(8.10)	.236(6.00)	.177(4.50)
22	FBB05001-F22S1XX3W5M	.339(8.60)	.256(6.50)	.197(5.00)
24	FBB05001-F24S1XX3W5M	.358(9.10)	.276(7.00)	.217(5.50)
30	FBB05001-F30S1XX3W5M	.417(10.60)	.335(8.50)	.276(7.00)
34	FBB05001-F34S1XX3W5M	.457(11.60)	.374(9.50)	.315(8.00)
40	FBB05001-F40S1XX3W5M	.516(13.10)	.433(11.00)	.374(9.50)
50	FBB05001-F50S1XX3W5M	.614(15.60)	.531(13.50)	.472(12.00)

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 26/SEPT/13	PART NO. FBB05001-FXXS1XX3W5M	TEM NO. FBB05001-F	 Leader Of Industry	
	DESIGN UNITS Inch (metric)	X. $\pm$ .012(0.30)	X. $\pm$ 5'	CHECKED BY CHERRY	DATE 26/SEPT/13	TITLE Board to Board Pitch 0.5mm 180° Vertical (SMT)		REV 0
SCALE 5:1	SIZE A4	X.XX $\pm$ .006(0.15)	X.XX $\pm$ 1'	DRAWN BY JACOB	DATE 26/SEPT/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		