# Surface Mount **RFTransformer**

50Ω

## 1.5 to 500 MHz


#### **Maximum Ratings**

Operating Temperature	-40°C to 85°C
Storage Temperature	-55°C to 100°C
RF Power	0.25W
DC Current	30mA
Permanent damage may occur if any	of these limits are exceeded.

#### **Pin Connections**

PRIMARY DOT	6
PRIMARY	4
SECONDARY DOT	1
SECONDARY	3
NOT USED	2

#### Outline Drawing AT224-1








Tolerance to be within  $\pm .002$ 

#### Outline Dimensions (inch)

<b>A</b>	<b>B</b>	C	D	<b>E</b>	<b>F</b>
. <b>150</b>	.150	.160	.050	.040	.025
3.81	3.81	4.06	1.27	1.02	0.64
<b>G</b>	H	J	<b>K</b>		wt
.028	.065	. <b>190</b>	.030		grams
0.71	1.65	4.83	0.76		0.15



#### **Features**

- good return loss
- usable over 0.4-500 MHz
- excellent amplitude unbalance, 0.1 dB typ.
- and phase unbalance, 2 deg typ. in 1 dB bandwidth
- · plastic base with leads
- aqueous washable

#### **Applications**

· balanced to unbalanced transformation • push-pull amplifiers





#### CASE STYLE: AT224-1A

\*Addition of Top hat™ feature

- Benefits
- Allows faster pick-and-place Enables visual identification marking

+RoHS Compliant The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

#### **Electrical Specifications**

	FREQUENCY (MHz)	3 dB	INSERTION LOSS*	1 dB
		MHz	MHz	MHz
1	1.5-500	1.5-500	2.5-400	5-350

\* Insertion Loss is referenced to mid-band loss, 0.6 dB tvp.



FREQUENCY (MHz)

		al Performance		
	FREQUENCY (MHz)	INSERTION LOSS (dB)	INPUT R. LOSS (dB)	
	1.51	1.15	13.64	
	2.49	0.91	13.85	
	4.35 6.87	0.72 0.62	13.75 13.76	
	16.75	0.60	13.91	
	40.86	0.69	14.35	
	99.67	0.71	14.33	
	243.10	1.13	12.92	
	353.08	1.47	11.62	
	502.30	2.06	10.10	
	INSERTION LOSS		INPUT RET	URN LOSS
2.5				
0 2.0   0 1.5   0 1.5   0 0.5		(B)		
0 1.5		00 13 -		
z 1.5		 12		
2 1.0		Z <sup>12</sup>		
Y.		j 11 +		
0.5		<sup>W</sup> 10		
=		10 -		
0.0		9		

### Notes A Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document. B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuit's website at www.minicircuits.com/WCLStore/terms.jsp

REV. D M152546 TC1-1+ IG/TD/CP/AM 151015 Page 1 of 1



FREQUENCY (MHz)

#### www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

 $\frac{\text{Mini-Circuits:}}{\frac{\text{TC1-1+}}{2}}$