**CT100** March 2020



# **CT100**

#### 1D Linear Sensor

#### **Features**

- Operating Magnetic Field Range: ±50 mT
- Stable Magnetic Performance over Temperature
- Linearity Error: ±0.5% from -20 mT to +20 mT
- Differential Outputs
- Supply Voltage: 1.0 V to 5.5 V
- Operating Temperature: -40°C to +125°C
- Package Options:
  - o 6-lead SOT23
  - o 6-lead DFN,  $1.50 \times 1.50 \times 0.45$  mm

#### **Applications**

- Linear Measurements
- Proximity Sensing
- Current Sensing

#### **Product Description**

The CT100 is a 1D linear sensor in full-bridge configuration from Crocus Technology developed on its patented MLU<sup>TM</sup> technology. The total magnetic field range for the CT100 is from -50 mT to +50 mT and it achieves a linearity error of  $\pm 0.5\%$  for a range of -20 mT to +20 mT while providing XtremeSense<sup>TM</sup> performance to achieve unparalleled temperature stability. It supports a wide operating voltage range of 1.0 V to 5.5 V.

It is available in a 6-lead SOT23 package and for space critical applications, a low profile and small form factor 6-lead DFN package that is  $1.50 \times 1.50 \times 0.45$  mm in size.

## **Ordering Information**

Part Number	Operating Temperature Range	Output Type	Package	Packing Method
CT100LW-IS6-M	-40°C to +85°C	Differential	6-lead SOT23	Tape & Reel
CT100LW-HS6-M	-40°C to +125°C	Differential	2.90 x 2.80 x 1.20 mm	rape & Neel
CT100LW-ID6-M	-40°C to +85°C	Differential	6-lead DFN	Tono & Bool
CT100LW-HD6-M	-40°C to +125°C	Dinerential	1.50 x 1.50 x 0.45 mm	Tape & Reel

## **Block Diagram**




Figure 1. CT100 Functional Block Diagram for SOT23-6




Figure 2. CT100 Functional Block Diagram for DFN-6




Figure 3. CT100 Axis of Sensitivity for SOT23-6 (Top Down View)




Figure 4. CT100 Axis of Sensitivity for DFN-6 (Top Down View)

# **Pin Configuration**





Figure 5. CT100 Pin-out Diagram


### **Pin Definitions**

SOT23-6 Pin #	Pin Name	Pin Description				
1	X2	Differential Output X2				
2	N/C	lo Connect				
3	X1	Differential Output X1				
4	GND	Ground				
5	N/C	No Connect				
6	VDD	Supply Voltage				

# **Pin Configuration**



**DFN-6 – Top Down View** 



**DFN-6 – Bottoms Up View** 

Figure 6. CT100 Pin-out Diagrams

## **Pin Definitions**

DFN-6 Pin #	Pin Name	Pin Description				
1	VDD	Supply Voltage				
2	N/C	No Connect				
3	GND	Ground				
4	X1	Differential Output X1				
5	N/C	No Connect				
6	X2	Differential Output X2				

### **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the CT100 and may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter		Min.	Max.	Unit
V <sub>DD</sub>	Supply Voltage	-0.3	6.0	V	
Vouт	Analog Output Pins Maximum V	-660	+660	mV	
ECD	Electrostatic Discharge	Human Body Model (HBM) per JESD22-A114	±4.0		137
E2D	Protection Level	Charged Device Model (CDM) per JESD22-C101	±1.0		kV
Вмах	Maximum Magnetic Field @ TA		±200	mT	
Tstg	Storage Temperature	-65	+160	°C	
TL	Lead Soldering Temperature, 10		+260	°C	

## **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual operation of the CT100. Recommended operating conditions are specified to ensure optimal performance to the specifications. Crocus Technology does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Min.	Тур.	Max.	Unit	
$V_{DD}$	Supply Voltage Range	1.0	3.0	5.5	V	
V <sub>OUT</sub>	OUT Voltage Range	-605		+605	mV	
BOPERATING	Operating Magnetic Field			±50	mT	
т.	Operating Ambient Temperature	Industrial	-40	+25	+85	°C
TA	Operating Ambient Temperature	-40	+25	+125		

## **Electrical & Magnetic Specifications**

Unless otherwise specified:  $V_{DD}$  = 1.0 V to 5.5 V and  $T_A$  = -40°C to +150°C. Typical values are  $V_{DD}$  = 3.0 V and  $T_A$  = +25°C.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Units	
Magnetic	,						
BOPERATING	Operating Magnetic Field (1)				±50	mT	
Electrical							
RBRIDGE	Bridge Resistance		20		40	kΩ	
D-	D 0 "	$V_{DD} = 3.0 \text{ V},$		0.20		m\//	
P <sub>D</sub>	Power Consumption	R <sub>BRIDGE</sub> = $30 \text{ k}\Omega$	0.30			mW	
V <sub>OFFSET</sub>	Offset Voltage		-5		+5	mV/V	
S	Sensitivity (Full-bridge Gain)	BOPERATING = ±20 mT	3.8	4.5	5.2	mV/V/mT	
TCR <sub>BRDIGE</sub>	Temperature Coefficient Resistance of Bridge (1)				600	ppm/°C	
TCO	Temperature Coefficient of Offset Voltage (1)				3.0	μV/V/°C	
TCS	Temperature Coefficient of Sensitivity (1)			-250	-350	ppm/°C	
L	Linearity	$B_{OP} = \pm 20 \text{ mT}$			±0.5	%	
EHYST	Hysteresis Error	$B_{OP} = \pm 20 \text{ mT}, T_A = +25^{\circ}\text{C}$			0.05	%	
ем	Output Noise (1)	$f = 10 \text{ Hz}, V_{DD} = 1.0 \text{ V},$ $B_{OPERATING} = 0 \text{ mT}, T_A = +25^{\circ}\text{C}$			700	nV <sub>RMS</sub> /√Hz	

<sup>(1)</sup> Guaranteed by design and characterization.

#### **Electrical Characteristics**

 $V_{DD} = 1.0 \text{ V} \text{ and } T_A = +25^{\circ}\text{C}.$ 




Figure 7. Sensitivity: Output Voltage vs. Magnetic Field vs. Temperature




Figure 8. Offset Voltage vs. Temperature

# **Recommended Application Circuit**




Figure 9. CT100 (SOT23-6) Application Diagram

**Table 1. Recommended External Components** 

Component	Description	Vendor & Part Number	Parameter	Min.	Тур.	Max.	Unit
Свур	0.1 μF, X7R	Murata GRM033Z71A104KE14	С		0.1		μF
		Others					

## **SOT23-6 Package Drawing and Dimensions**





Figure 10. 6-Lead SOT23 Package Drawing

Table 2. CT100 6-Lead SOT23 Package Dimensions

Symbol	Dime	nsions in Millimeters	(mm)			
Syllibol	Min.	Тур.	Max.			
Α	1.05	1.20	1.35			
A1	0.00	0.10	0.15			
A2	1.00	1.10	1.20			
b	0.40	-	0.50			
b1	0.40	0.40	0.45			
С	0.08	•	0.22			
c1	0.08	0.13	0.20			
D	2.80	2.90	3.00			
E	2.60	2.80	3.00			
E1	1.50	1.60	1.70			
е		0.95 BSC				
e1		1.90 BSC				
L	0.35	0.43	0.60			
L1		0.60 REF				
L2		0.25 BSC				
R	0.10	•	-			
R1	0.10	-	0.25			
θ	0°	4°	8°			
θ1	5°	6° 15°				
θ2	5°	8°	15°			

Crocus Technology provides package drawings as a service to customers considering or planning to use Crocus products in their designs. Drawings may change without notice. Please note the revision and date of the data sheet and contact a Crocus Technology representative to verify or obtain the most recent version. The package specifications do not expand the terms of Crocus Technology's worldwide terms and conditions, specifically the warranty therein, which covers Crocus Technology's products.

# **SOT23 Tape & Pocket Drawing and Dimensions**





#### NOTES:

- 1. Material: Conductive Polystyrene
- 2. Dimensions in mm.
- 3. 10 sprocket hole pitch cumulative tolerance  $\pm 0.20$  mm.
- 4. Camber bot to exceed 1 mm in 100 mm.
- 5. Pocket position relative to sprocket hole measured as true position of pocket and not pocket hole.
- 6. (S.R.  $\Omega$ /sq) means surface electric resistivity of the carrier tape.

Figure 11. Tape and Pocket Drawing for SOT23 Package

## **DFN-6 Package Drawing and Dimensions**









Figure 12. DFN-6 Package Drawing

Table 3. CT100 DFN-6 Package Dimensions

Symbol	Dimensions in Millimeters (mm)						
Symbol	Min.	Тур.	Max.				
Α	0.40	0.45	0.50				
A1	0.00	0.02	0.05				
b	0.15	0.20	0.25				
С	•	0.15 REF	-				
D	1.40	1.50	1.60				
D2	1.15	1.20	1.25				
Е	1.40	1.50	1.60				
E2	0.65	0.70	0.75				
е		0.50	-				
L	0.15	0.20	0.25				
у	0.000	-	0.075				

Crocus Technology provides package drawings as a service to customers considering or planning to use Crocus products in their designs. Drawings may change without notice. Please note the revision and date of the data sheet and contact a Crocus Technology representative to verify or obtain the most recent version. The package specifications do not expand the terms of Crocus Technology's worldwide terms and conditions, specifically the warranty therein, which covers Crocus Technology's products.

## **DFN-6 Tape & Pocket Drawing and Dimensions**



#### **NOTES:**

- I. Measured from centerline of sprocket hole to centerline of pocket.
- II. Cumulative tolerance of 10 sprocket holes is  $\pm 0.20$ .
- III. Measured from centerline of sprocket hole to centerline of pocket.
- IV. Other material available.

Figure 13. Tape and Pocket Drawing for DFN-6 Package

**Table 4. DFN-6 Tape and Pocket Dimensions** 

Symbol	Dimension (mm)
Ao	$1.70 \pm 0.05$
Во	$1.70 \pm 0.05$
Ko	$0.60 \pm 0.05$
F	$3.50 \pm 0.05$
P1	4.00 ± 0.10
DW	$8.00 \pm 0.30$

### **Package Information**

**Table 5. CT100 Package Information** 

Part Number	Package Type	# of Leads	Package Quantity	Lead Finish	Eco Plan (1)	MSL Rating <sup>(2)</sup>	Operating Temperature <sup>(3)</sup>	Device Marking
CT100LW-IS6-M	SOT23	6	3,000	Sn	Green & RoHS	1	-40°C to +85°C	CT YWWS
CT100LW-HS6-M	SOT23	6	3,000	Sn	Green & RoHS	1	-40°C to +125°C	CT YWWS
CT100LW-ID6-M	DFN	6	3,000	Sn	Green & RoHS	3	-40°C to +85°C	C YZ
CT100LW-HD6-M	DFN	6	3,000	Sn	Green & RoHS	3	-40°C to +125°C	C YZ

- (1) RoHS is defined as semiconductor products that are compliant to the current EU RoHS requirements. It also will meet the requirement that RoHS substances do not exceed 0.1% by weight in homogeneous materials. Green is defined as the content of Chlorine (CI), Bromine (Br) and Antimony Trioxide based flame retardants satisfy JS709B low halogen requirements of ≤ 1,000 ppm.
- (2) MSL Rating = Moisture Sensitivity Level Rating as defined by JEDEC standard classifications.
- (3) Package will withstand ambient temperature range of -40°C to +150°C and storage temperature range of -65°C to +160°C.
- (4) Device Marking for SOT23 is defined as XZ YWWS where XZ = part number, Y = year, WW = work week and S = sequential number. DFN is defined as X where X = part number and YZ = date code information.

**Disclaimer:** The contents of this document are provided for informational purposes only. CROCUS TECHNOLOGY, INC. AND CROCUS TECHNOLOGY SA (COLLECTIVELY "CROCUS") MAKE NO REPRESENTATIONS OR WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH RESPECT TO THE ACCURACY OR COMPLETENESS OF THE CONTENTS HEREIN, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. Crocus reserves the right to make changes to the specifications and product descriptions, and/or to discontinue or make changes to its products at any time without notice. Crocus's products have not been designed, tested, or manufactured for use and should not be used in applications where the failure, malfunction or inaccuracy of the Products carries a risk of death or serious bodily injury or damage to tangible property, including, but not limited to, life support systems, nuclear facilities, military, aircraft navigation or communication, emergency systems, harsh environments, or other applications with a similar degree of potential hazard.

#### **Product Status Definition**

<b>Data Sheet Identification</b>	<b>Product Status</b>	Definition
Objective	Proposed New Product Idea or In Development	Data sheet contains design target specifications and are subject to change without notice at any time.
Preliminary	First Production	Data sheet contains preliminary specifications obtained by measurements of early samples. Follow-on data will be published at a later date as more test data is acquired. Crocus reserves the right to make changes to the data sheet at any time.
None	Full Production	Data sheet contains final specifications for all parameters. Crocus reserves the right to make changes to the data sheet at any time.
Obsolete	Not in Production	Data sheet for a product that is no longer in production at Crocus. It is for reference only.