Spec. No. JEFL243C-9108D-01 P 1/10

Wire Wound Chip Common Mode Choke Coil DLW5BTZ | | | | TQ2 | |

Murata Standard Reference Specification [AEC-Q200]

This reference specification applies to Wire Wound Chip Common Mode Choke Coil DLW5BTZ TQ Series for Automotive Electronics based on AEC-Q200 except for Power train and Safety.

2. Part Numbering

(1) Chip Common Mode Choke Coil

(2) Structure (W : Winding Type)

(3) Dimension (L×W)

(4) Type

(5) Category

(6) Impedance (Typ. at 100MHz)

(7) Circuit

(8) Features

(9) Number of Line

(10) Packaging Code L : Taping (φ 180mm/reel)

K: Taping (ϕ 330mm/reel)

B: Bulk

3.Rating

Customer Part Number	MURATA Part Number	Impedance at 10MHz, Under Standard Testing Conditions (Ω min.)	Impedance at 100MHz, Under Standard Testing Conditions (Ω Typ.)	Rated Voltage V(DC)	Withstanding Voltage V(DC)	Rated Current (A)	DC Resistance (Rdc) (Ωmax.)	Insulation Resistance (MΩ min.)	ESD Rank 2.2kV
	DLW5BTZ101TQ2L								
	DLW5BTZ101TQ2K	10	100			4	0.013		
	DLW5BTZ101TQ2B								
	DLW5BTZ251TQ2L								
	DLW5BTZ251TQ2K	20	250			3	0.020		
	DLW5BTZ251TQ2B								
	DLW5BTZ501TQ2L								
	DLW5BTZ501TQ2K	30	500	50	125	2.5	0.027	10	2
	DLW5BTZ501TQ2B								
	DLW5BTZ102TQ2L								
	DLW5BTZ102TQ2K	60	1000			2	0.034	-	
	DLW5BTZ102TQ2B								
	DLW5BTZ142TQ2L								
	DLW5BTZ142TQ2K	100	1400			1.5	0.056		
	DLW5BTZ142TQ2B								

[•] Operating Temperature : - 40 °C to + 105 °C • Storage Temperature : - 40 °C to + 105 °C

4. Standard Testing Conditions

< Unless otherwise specified >

Temperature: Ordinary Temp. 15 °C to 35 °C

Humidity: Ordinary Humidity 25 %(RH) to 85 %(RH)

< In case of doubt >

Temperature: 20 °C ± 2 °C


Humidity: 60 %(RH) to 70 %(RH)

Atmospheric pressure: 86 kPa to 106 kPa


Reference Only

Spec. No. JEFL243C-9108D-01

5. Style and Dimensions



6. Marking



7. Electrical Performance

No.	Item	Specifications	Test Method
7.1	Impedance (Z) (at 10MHz)	Meet item 3.	Measuring Equipment : KEYSIGHT 4191A or the equivalents. Measuring Frequency : 10MHz (ref. Item 9.)
7.2	Insulation Resistance (I.R.)		Measuring Equipment : R8340A or the equivalents. Measuring voltage : Rated Voltage Time : within 60 s (ref. Item 9.)
7.3	DC Resistance (Rdc)		Measuring Current: 100 mA max. (ref. Item 9.) (In case of doubt in the above mentioned standard condition, measure by 4 terminal method.)
7.4	Withstanding Voltage	Products shall not be damaged.	Test Voltage: 2.5 times for Rated Voltage Time: 1 to 5 seconds Charge Current: 1 mA max. (ref. Item 9.)



Spec. No. JEFL243C-9108D-01

8. Q200 Requirement

7-1. Performance (based on Table 13 for Ferrite EMI SUPPRESSORS/FILTERS) AEC-Q200 Rev.D issued June 1. 2010

	T	EC-Q200	Murata Specification / Deviation		ation	
No.	Stress Test Method		·			
3	High Temperature Exposure	1000hours at 105 deg C Set for 24hours at room temperature, then measured.	Meet Ta	able A after testir	ng.	
	Expodure	men medaured.	Ap	opearance	No damaged.	
			ch	npedance lange t 10MHz)	within ± 20%	
			I.F	₹.	10MΩ min.	
				ithstanding oltage	No damaged.	
4	Temperature Cycling	1000cycles -40 deg C to +105 deg C Set for 24hours at room temperature, then measured.	Meet Ta	able A after testir	ng.	
5	Destructive Physical Analysis	Per EIA469 No electrical tests	Not App	olicable		
7	Biased Humidity	1000hours at 85 deg C, 85%RH Apply max rated voltage and current.		able A after testir	ng.	
		Apply max rated voltage and current.	Apply ra	ated voltage.		(ref.item 9)
8	Operational Life	Apply 105 deg C 1000hours Set for 24hours at room temperature, then measured		able A after testir ated current.	ng.	,
9	External Visual	Visual inspection	(ref.item 9 No abnormalities			(remitering)
10	Physical Dimension	Meet ITEM 5 (Style and Dimensions)	No defects			
12	Resistance to Solvents	Per MIL-STD-202 Method 215	Not Applicable			
13	Mechanical Shock	Per MIL-STD-202 Method 213 Conditon F: 1500g's(14.7N)/0.5ms/ Half sine	Meet T	able A after te	sting.	
14	Vibration	5g's(0.049N) for 20 minutes, 12cycles each of 3 oritentations Test from 10-2000Hz. 12cycles each of 3 orientations	Meet T	able A after te	sting.	
15	Resistance to Soldering Heat	No-heating Solder temperature 260C+/-5 deg C Immersion time 10s	Pre-heating: 150 to 180C / 90±30s Meet Table A after testing.			
17	ESD	Per AEC-Q200-002	Meet Table A after testing. ESD Rank: Refer to Item 3. Rating.			
18	Solderbility	Per J-STD-002	Method b: Not Applicable 90% of the terminations is to be soldered. (except partly-exposed wire) Flux:Ethanol solution of rosin,25(wt)% includes activator equivalent to 0.06 to 0.10(wt)% chlorine			
19	Electrical Characterization	Measured : Impedance	No defe			

Spec. No. JEFL243C-9108D-01


	F	AEC-Q200	Murata Specification / Deviation	
No.	Stress	Test Method		
20	Flammability	Per UL-94	Not Applicable	
21	Board Flex	Epoxy-PCB(1.6mm) Deflection 2mm(min) 60 sec minimum holding time	Meet Table A after testing. 30 sec minimum holding time	
22	Terminal Strength	Per AEC-Q200-006 A force of 17.7N for 60sec	No defects	
30	Electrical Transient Conduction	Per ISO-7637-2	Not Applicable	

9. Terminal to be Tested When measuring and supplying the voltage, the following terminal is applied.

No.	Item	Terminal to be Tested
9.1	Impedance (Z)	
	(Measurement Terminal)	Terminal → ♦ • • Terminal
9.2	DC Resistance (Rdc)	↓•
	(Measurement Terminal)	
9.3	Insulation Resistance (I.R.)	
	(Measurement Terminal)	Terminal
9.4	Withstanding Voltage	Terminal O————————————————————————————————————
	(Measurement Terminal)	1
9.5	Biased Humidity (Supply Terminal)	Terminal O O O O
		• • • • • • • • • • • • • • • • • • • •
9.6	Operational Life (Supply Terminal)	Terminal

10. Impedance Frequency Characteristics (Typical)

DLW5BTZ_TQ series




11. P.C.B., Flux, Solder and Soldering condition

Test shall be done using P.C.B., Flux, Solder and Soldering condition which are specified in item 14 except the case of being specified special condition.

12. Specification of Packaging

12.1. Appearance and Dimensions



12.2. Specification of Taping

- (1) Packing quantity (Standard quantity) φ 180 mm reel : 700 pcs. / reel φ 330 mm reel :2500 pcs. / reel
- (2) Packing Method

Products shall be packaged in each embossed cavity of plastic tape and sealed with cover tape.

(3) Sprocket Hole

The sprocket holes are to the right as the tape is pulled toward the user.

(4) Spliced point

The cover tape have no spliced point.

(5) Missing components number


Missing components number within 0.1% of the number per reel or 1 pc., whichever is greater, and are not continuous. The specified quantity per reel is kept.

12.3. Pull Strength of Plastic Tape

Plastic Tape	5 N min.
Cover Tape	10 N min.

12.4. Peeling off force of Cover Tape


0.2N to 0.7N (minimum value is typical.) Speed of Peeling off : 300 mm / min




12.5. Dimensions of Leader-tape, Trailer and Reel

There shall be leader-tape (cover tape only and empty tape) and trailer-tape (empty tape) as follows.

« Packaging Code : L (ϕ 180mm reel) »



« Packaging Code : K (ϕ 330mm reel) »



Reference Only

12.6 Marking for reel

Spec. No. JEFL243C-9108D-01

Customer part number, MURATA part number, Inspection number(*1), RoHS marking(*2), Quantity, etc

*1) « Expression of Inspection No. »

 $\Box\Box$ 0000 $\times\times$ (3)

(1) Factory Code

(2) Date First digit : Year / Last digit of year

Second digit : Month / Jan. to Sep. \rightarrow 1 to 9, Oct. to Dec. \rightarrow O,N,D

Third, Fourth digit: Day

(3) Serial No.

*2) « Expression of RoHS marking » ROHS $-\underline{Y}$ ($\underline{\triangle}$)


(1) RoHS regulation conformity parts.

(2) MURATA classification number

12.7 Marking for Outside package

Customer name Purchasing Order Number, Customer Part Number, MURATA part number, RoHS marking (*2), Quantity, etc

12.8 Specification of Outer Case



Reel	Outer Case Dimensions (mm)			Standard Reel Quantity in Outer Case	
	W	D	Н	(Reel)	
φ 180mm	186	186	93	4	
φ330mm	340	340	85	4	

* Above Outer Case size is typical. It depends on a quantity of an order.


13. 🛆 Caution


13.1. Mounting Direction

Mount products in right direction.

Wrong direction which is 90 $^{\circ}$ rotated from right direction cause not open or short circuit but also flames

or other serious trouble.





13.2. Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property.

(1) Aircraft equipment

(6) Transportation equipment (trains, ships, etc.)

(2) Aerospace equipment

(7) Traffic signal equipment

(3) Undersea equipment

(8) Disaster prevention / crime prevention equipment

(4) Power plant control equipment

(9) Data-processing equipment

(5) Medical equipment

(10) Applications of similar complexity and / or reliability requirements to the applications listed in the above.

13.3 Caution(Rating)

Do not exceed maximum rated current of the product. Thermal stress may be transmitted to the product and short/open circuit of the product or falling off the product may be occurred.

13.4 Fail-safe

Be sure to provide an appropriate fail-safe function on your product to prevent a second damage that may be caused by the abnormal function or the failure of our product.

14.Notice

Products can only be soldered with reflow.

This product is designed for solder mounting.

Please consult us in advance for applying other mounting method such as conductive adhesive.

14.1. Flux and Solder

Flux	Use rosin-based flux,(with converting chlorine content 0.06 to 0.1(wt)%.), but not highly acidic flux (with Halogen content exceeding 0.2(wt)% conversion to chlorine).
	Do not use water-soluble flux.
Solder	Use Sn-3.0Ag-0.5Cu solder

14.2. Assembling

< Exclusive use of Reflow soldering >

Flow soldering may cause deterioration in insulation resistance.

So,reflow soldering shall be applied for this product.

< Thermal Shock >

Pre-heating should be in such a way that the temperature difference between solder and ceramic surface is limited to 100°C max. Also cooling into solvent after soldering should be in such a way that the temperature difference is limited to 100°C max.

Not enough preheating may cause deterioration in insulation resistance and / or crank or ceramic body.

14.3. Cleaning Conditions

Do not clean after soldering. If cleaning, please contact us.


14.4. Resin coating

The impedance value may change due to high cure-stress of resin to be used for coating/molding products. An open circuit issue may occur by mechanical stress caused by the resin, amount/cured shape of resin, or operating condition etc. Some resin contains some impurities or chloride possible to generate chlorine by hydrolysis under some operating condition may cause corrosion of wire of coil, leading to open circuit. So, please pay your careful attention when you select resin in case of coating/molding the products with the resin. Prior to use the coating resin, please make sure no reliability issue is observed by evaluating products mounted on your board.

14.5. Attention regarding P.C.B. bending

The following shall be considered when designing and laying out P.C.B.'s.

(1) P.C.B. shall be designed so that products are not subject to the mechanical stress due to warping the board. [Products direction]



Products shall be location the sideways direction (Length:a<b) to the mechanical stress.

P 7/10


P 8/10

(2) Components location on P.C.B. separation.

It is effective to implement the following measures, to reduce stress in separating the board.

It is best to implement all of the following three measures; however, implement as many measures as possible to reduce stress.


Contents of Measures	Stress Level
(1) Turn the mounting direction of the component parallel to the board separation surface.	A > D*1
(2) Add slits in the board separation part.	A > B
(3) Keep the mounting position of the component away from the board separation surface.	A > C



*1 A > D is valid when stress is added vertically to the perforation as with Hand Separation. If a Cutting Disc is used, stress will be diagonal to the PCB, therefore A > D is invalid.

(3) Mounting Components Near Screw Holes

When a component is mounted near a screw hole, it may be affected by the board deflection that occurs during the tightening of the screw. Mount the component in a position as far away from the screw holes as possible.



14.6. Attention Regarding P.C.B. Design

- < The Arrangement of Products >
 - •P.C.B. shall be designed so that products are far from the portion of perforation.
 - •The portion of perforation shall be designed as narrow as possible, and shall be designed so as not to be applied the stress in the case of P.C.B. separation.
 - Products shall not be arranged on the line of a series of holes when there are big holes in P.C.B.
 (Because the stress concentrate on the line of holes.)


< Products Placing >

•Support pins shall be set under P.C.B. to prevent causing a warp to P.C.B. during placing the products on the other side of P.C.B..

< P.C.B. Separation >


•P.C.B. shall not be separated with hand.

P.C.B. shall be separated with the fixture so as not to cause P.C.B. bending.



Reference Only

14.7. Standard Land Dimensions




14.8. Reflow Soldering

- (1) Standard printing pattern of solder paste
 - Standard thickness of solder paste should be 150 to 200µm.

Solderability is subject to reflow condition and thermal conductivity.

Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.


- Use the solder paste printing pattern of the right pattern.
- For the resist and copper foil pattern, use standard land dimensions.
- Use the Solder Sn-3.0Ag-0.5Cu for pattern printing.



(2) Soldering Conditions

Standard soldering profile and the limit soldering profile is as follows.

The excessive limit soldering conditions may cause leaching of the electrode and / or resulting in the deterioration of product quality.



	Standard Profile	Limit Profile
Pre-heating	150~180°C 、90s±30s	
Heating	above 220°C、30s~60s	above 230°C、60s max.
Peak temperature	250±3°C	260°C, 10s
Cycle of reflow	2 times	2 times

Spec. No. JEFL243C-9108D-01 P 10/10

14.9. Reworking with Soldering iron

The following conditions must be strictly followed when using a soldering iron after being mounted by reflow soldering.

Pre-heating: 150°C, 1 min
 Soldering iron output: 30W max.
 Tip temperature: 350°C max.
 Tip diameter: \$\phi\$3mm max.
 Soldering time: 3(+1,-0) seconds.
 Times: 2times max.


Notes: Do not touch the products directly with the soldering iron.


14.10. Handling of a substrate

After mounting products on a substrate, do not apply any stress to the product caused by bending or twisting to the substrate when cropping the substrate, inserting and removing a connector from the substrate or tightening screw to the substrate.

Excessive mechanical stress may cause cracking in the product.

Bending Twisting





14.11. Brushing of neighborhood of products

When you clean the neighborhood of products such as connector pins, bristles of cleaning brush shall not be touched to the winding portion to prevent the breaking of wire.

14.12. Operating Environment

Do not use this product under the following environmental conditions, on deterioration of the performance, such as inslation resistance may result from the use.

- (1) in corrosive gases (acidic gases, alkaline gases, chlorine, sulfur gases, organic gases and etc.)
- (2) in the atmosphere where liquid such as organic solvent, may splash on the products.

14.13. Storage condition

(1) Storage period

Use the products within 12 months after delivered.

Solderability should be checked if this period is exceeded.

- (2) Storage environment conditions
 - Products should be stored in the warehouse on the following conditions.

Temperature : -10 °C to +40 °C

Humidity : 15 % to 85% relative humidity No rapid change on temperature and humidity.

•Products should not be stored in corrosive gases, such as sulfureous, acid gases, alkaline gases, to prevent the following deterioration.

Poor solderabirity due to the oxidized electrode.

- •Products should be stored on the palette for the prevention of the influence from humidity, dust and so on.
- •Products should be stored in the warehouse without heat shock, vibration, direct sunlight and so on.
- •Products should not be stored under the air tights packaged condition.
- (3) Delivery

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

15. **△** Note

- (1)Please make sure that your product has been evaluated in view of your specifications with our product being mounted to your product.
- (2)You are requested not to use our product deviating from the reference specifications.
- (3)The contents of this reference specification are subject to change without advance notice. Please approve our product specifications or transact the approval sheet for product specifications before ordering.