Vishay Semiconductors

Small Signal Schottky Diodes, Single and Dual

FEATURES


and fast switching

MECHANICAL DATA

Weight: approx. 8.8 mg

Packaging codes/options:

Case: SOT-23



www.vishay.com

DESIGN SUPPORT TOOLS click logo to get started



Wallable					
PARTS TABLE					
PART	ORDERING CODE	CIRCUIT CONFIGURATION	TYPE MARKING	REMARKS	
BAS70-00	BAS70-00-E3-08 or BAS70-00-E3-18	Single	73		
	BAS70-00-HE3-08 or BAS70-00-HE3-18	Single			
BAS70-04	BAS70-04-E3-08 or BAS70-04-E3-18	Dual serial	74		
	BAS70-04-HE3-08 or BAS70-04-HE3-18	Duai seriai		Topo and real	
BAS70-05	BAS70-05-E3-08 or BAS70-05-E3-18	Common cathode	75	Tape and reel	
	BAS70-05-HE3-08 or BAS70-05-HE3-18	Common cathode	75		
BAS70-06	BAS70-06-E3-08 or BAS70-06-E3-18	Common anode	76		
	BAS70-06-HE3-08 or BAS70-06-HE3-18	Common anode			

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Repetitive peak reverse voltage		$V_{RRM} = V_{RRM} = V_{R}$	70	V	
Forward continuous current ⁽¹⁾		١ _F	200	mA	
Surge forward current ⁽¹⁾	t _p < 1 s	I _{FSM}	600	mA	
Power dissipation ⁽¹⁾		P _{tot}	200	mW	

Note

⁽¹⁾ Device on fiberglass substrate, see layout on next page

THERMAL CHARACTERISTICS ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Thermal resistance junction to ambient air ⁽¹⁾		R _{thJA}	500	K/W	
Junction temperature		Тj	125	°C	
Storage temperature range		T _{stg}	-65 to +150	°C	
Operating temperature range		T _{op}	-55 to +125	°C	
				•	

Note

⁽¹⁾ Device on fiberglass substrate, see layout on next page

Rev. 2.2, 13-Feb-18

Document Number: 85702

1 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



• These devices are protected by a PN junction guard ring against excessive voltage, such as electrostatic discharges

• Base P/N-E3 - RoHS-compliant, commercial grade

please see www.vishay.com/doc?99912

18/10K per 13" reel (8 mm tape), 10K/box

08/3K per 7" reel (8 mm tape), 15K/box

Base P/N-HE3 - RoHS-compliant, AEC-Q101 qualified

· Material categorization: for definitions of compliance

These diodes feature very low turn-on voltage

- AEC-Q101 gualified available
- RoHS COMPLIANT



Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Reserve beakdown voltage	$I_{\rm R}$ = 10 μ A (pulsed)	V _(BR)	70			V
Leakage current	V _R = 50 V	I _R		20	100	nA
Forward voltage	I _F = 1.0 mA	V _F			410	mV
Forward voltage ⁽¹⁾	I _F = 15 mA	V _F			1000	mV
Diode capacitance	V _R = 0 V, f = 1 MHz	CD		1.5	2	pF
Reserve recovery time	$I_{F} = I_{R} = 10 \text{ mA}, i_{R} = 1 \text{ mA}, \\ R_{L} = 100 \Omega$	t _{rr}			5	ns


Note

⁽¹⁾ Pulse test; $t_p \le 300 \ \mu s$


LAYOUT FOR R_{thJA} TEST

Thickness:

Fiberglass 1.5 mm (0.059") Copper leads 0.3 mm (0.012")



PACKAGE DIMENSIONS in millimeters (inches): SOT-23



Rev. 2.2, 13-Feb-18

Document Number: 85702

0.9 (0.035)

<u>0°to 8</u>°

0.9 (0.035)

For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.