SMT Power Inductors

High Current Molded Power Inductor - PA4341.XXXANLT Series















Height: 3.0mm Max

Prootprint: 7.4mm x 6.8mm Max **Current Rating:** up to 30.0A

Pinductance Range: 0.15uH to 22.0uH Shielded construction and compact design High current, low DCR, and high efficiency

@ Minimized acoustic noise and minimized leakage flux

Electrical Specifications @ 25°C – Operating Temperature –55°C to +155°C								
	Inductance ⁵	Rated	DC Res	Saturation				
Part	100KHz, 1V	Current	TYP.	MAX.	Current			
Number	uH±20%	A	mΩ	mΩ	A			
PA4341.151ANLT	0.15*	30	1.7	2.1	40			
PA4341.221ANLT	0.22	23	2.0	2.5	34			
PA4341.331ANLT	0.33	21	2.8	3.4	25			
PA4341.361ANLT	0.36	20	3.3	3.9	24			
PA4341.471ANLT	0.47	18	3.4	4	20			
PA4341.561ANLT	0.56	16.5	3.9	4.5	18			
PA4341.681ANLT	0.68	16	4.7	5.3	17			
PA4341.821ANLT	0.82	14	5.4	6	16			
PA4341.102ANLT	1.0	12	6.7	7.4	15			
PA4341.122ANLT	1.2	10	7.7	9.5	14			
PA4341.152ANLT	1.5	10	10.2	12.1	14			
PA4341.222ANLT	2.2	8	13.5	15	10			
PA4341.272ANLT	2.7	7.2	17.3	20	9.8			
PA4341.332ANLT	3.3	6.5	19	22	9.5			
PA4341.472ANLT	4.7	5.5	28	33	6.5			
PA4341.562ANLT	5.6	5.5	39	42	6			
PA4341.682ANLT	6.8	4.5	43	50	6			
PA4341.822ANLT	8.2	4.5	54	60	6			
PA4341.103ANLT	10	4	62	68	5.5			
PA4341.153ANLT	15	3	110	140	4.5			
PA4341.223ANLT	22	2.5	150	190	3			

SMT Power Inductors

High Current Molded Power Inductor - PA4341.XXXANLT Series





Notes:

- 1. Actual temperature of the component during system operation (ambient plus temperature rise) must be within the standard operating range.
- 2. The saturation current is the current at which the initial inductance drops approximately 30% at the stated ambient temperature. This current is determined by placing the compnent in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effect) to the component.
- 3. The rated current is the DC current required to raise the component temperature by approximately 40 °C. Take note that the components' performanc varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- 4. The part temperature (ambient+temp rise) should not exceed 155 °C under worst case operating conditions. Circuit design, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.
- 5. Inductance tolerance is ±20% for all parts except PA4341.151ANLT which is ±30%.
- 6. Parts shown in bold are standard catalog parts and are available through sample stock and distribution. Parts in lighter font are available but are not necessarily held in sample stock or distribution and lead times may be longer. Please contact Pulse for availablity.


Mechanical

PA4341.XXXNLT










Final Layout


SUGGESTED PAD LAYOUT

Series	A	Α`	В	C	D	Е	T	L	G	Н
PA4341.XXXANLT	7.1±0.3	6.4±0.3	6.6±0.2	2.8±0.2	1.6±0.3	3.0±0.2	0~0.15	8.0	3.7	3.4

All Dimensions in mm.

TAPE & REEL INFO





Direction of tape

SURFACE MOUNTING TYPE, REEL/TAPE LIST								
	REEL SIZ	ZE (mm)	TA	QTY				
	А	G	P_1	W	K ₀	PCS/REEL		
PA4341.XXXANLT	Ø330	16.4+2/-0	12.0±0.1	16±0.3	3.3±0.1	1000		

SMT Power Inductors

High Current Molded Power Inductor - PA4341.XXXANLT Series



For More Information Pulse Worldwide Headquarters 15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.	Pulse Europe Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany	Pulse China Headquarters Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057	Pulse North China Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China	Pulse South Asia 3 Fraser Street 0428 DUO Tower Singapore 189352	Pulse North Asia 1F., No.111 Xiyuan Rd Zhongli City Taoyuan City 32057 Taiwan (R.O.C)
Tel: 858 674 8100	Tel: 49 2354 777 100	Tel: 86 755 33966678	Tel: 86 21 62787060	Tel: 65 6287 8998	Tel: 886 3 4356768
Fax: 858 674 8262	Fax: 49 2354 777 168	Fax: 86 755 33966700	Fax: 86 2162786973	Fax: 65 6280 0080	Fax: 886 3 4356820

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.