Compensated High Inductance Choke, 3-phase



Description

- Current compensated choke
- 3-phase choke
- Flexible wire
- Flange for mounting onto printed circuit board
- Fully potted resign

See below: Approvals and Compliances

Applications

- Placed in front of frequency converter
- Stepper motor drives
- UPS-systems
- Inverter

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product

Technical Data			
Rated voltage	up to 540 VAC	Test Voltage	2.5 kV, 50 Hz, 2 sec, winding to winding
	up to 760 VDC	Isolation Voltage	2.5 kV eff., 50 Hz, 2 sec, winding to
Rated Current	3 - 16A @ Ta 40 °C		ambient
Rated inductance	4.0 - 50mH, Tol30% +50%	Climatic Category	25/100/21 acc. to IEC 60068-1
Power Operating Frequency	50 - 400 Hz	Allowable Operation Temp.	-25 °C to 100 °C
Terminal Type	Flexible wire		
Weight	145 - 1840g		
Material: Housing	UL 94V-0		
Sealing Compound	UL 94V-0		

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: DKLP

Approval Logo Certificates		Certification Body	Description			
c FN us	UL Approvals	UL	UL File Number: E72928			
Application standards Application standards where the product can be used						

Organization	Design	Standard	Description
IEC	Designed for applications acc.	IEC/UL 62368-1	IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.

DKLP-3


Compliances

The product complies with following Guide Lines


Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm] Case 29-3W


Case 31-3W




Case 33-3W




Impedance curves






DKLP-0333-xxxx



DKLP-0331-xxxx



All Variants

I _n [A]	L _n [mH]	R_{cu} [mΩ]	Tripped Power Dissi- pation [W]	f _{res} [MHz]	Copper ø [mm]	Weight [g]	Housings	Packing unit [pcs.]	Order Number
3	30	130	3.5	0.13	0.71	145 g	29-3W	12	DKLP-0329-0330
5	10	48	3.6	0.15	0.9	145 g	29-3W	12	DKLP-0329-0510
8	4	22	4.2	0.4	1.12	145 g	29-3W	12	DKLP-0329-0804
3	50	260	7	0.055	0.71	509 g	31-3W	2	DKLP-0331-0350
4	30	155	7.5	0.075	0.8	512 g	31-3W	2	DKLP-0331-0430
5	20	100	7.5	0.145	0.9	514g	31-3W	2	DKLP-0331-0520
8	40	110	21	0.05	1.12	1726 g	33-3W	1	DKLP-0333-0840
16	10	30	23	0.14	1.6	1840 g	33-3W	1	DKLP-0333-1610

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER