

50 A VRPower® Integrated Power Stage

(Datasheet in Brief)

DESCRIPTION

The SiC654 is a high frequency integrated power stage optimized for synchronous buck applications to offer high current, high efficiency, and high power density performance with very low shutdown current. Packaged in Vishay's proprietary 5 mm x 5 mm MLP package, SiC654 enables voltage regulator designs to deliver up to 50 A continuous current per phase.

The internal power MOSFETs utilize Vishay's latest TrenchFET® technology that delivers industry benchmark performance to significantly reduce switching and conduction losses.

The SiC654 incorporates an advanced MOSFET gate driver IC that features high current driving capability, adaptive dead-time control, an integrated bootstrap switch, and user selectable zero current detection to improve light load efficiency. The driver is also compatible with a wide range of PWM controllers, supports tri-state PWM, and 5 V and 3.3 V PWM logic.

The device also supports PS4 mode to reduce power consumption when the system is in standby state.

The SiC654 offers operating temperature monitoring, protection features, and warning flags that improve system monitoring and reliability.

FEATURES

- Highly efficient
 - Thermally enhanced PowerPAK® MLP55-31L package



- Vishay's latest TrenchFET technology and low side MOSFET with integrated Schottky diode
- Integrated, low impedance, bootstrap switch
- Power MOSFETs optimized for 19 V input stage
- Supports PS4 mode light load requirement with low shutdown supply current (5 V, 3 µA)
- Zero current detection for improved light load efficiency
- · Highly versatile
 - 5 V and 3.3 V PWM logic with tri-state and hold-off timer
- 5 V DSBL#, ZCD_EN# logic with PS4 state support
- High frequency operation up to 2 MHz
- · Robust and reliable
 - Delivers in excess of 50 A continuous current, 70 A, peak (10 ms) and 100 A, peak (10 μ s)
 - Over current protection
- Over temperature flag
- Over temperature protection
- Undervoltage lockout protection
- High side MOSFET short detection
- Effective monitoring and reporting
 - Accurate temperature reporting
- Warnings and faults reporting flag
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Multi-phase VRDs for computing, graphics card and memory
- · Intel core processor power delivery
 - V_{CORE}, V_{GRAPHICS}, V_{SYSTEM AGENT}
 - V_{CCG}
- Up to 24 V rail input DC/DC VR modules

TYPICAL APPLICATION DIAGRAM




Fig. 1 - Typical Application Diagram




Vishay Siliconix

PRODUCT SUMMARY		
Part number	SiC654	SiC654A
Description	50 A power stage plus, 2.5 V _{IN} to 24 V _{IN} , 5 V PWM with ZCD, PS4 mode	50 A power stage plus, 2.5 $\rm V_{IN}$ to 24 $\rm V_{IN}$, 3.3 V PWM with ZCD, PS4 mode
Input voltage min. (V)	2.5	2.5
Input voltage max. (V)	24	24
Continuous current rating max. (A)	50	50
Switch frequency max. (kHz)	2000	2000
Enable (yes / no)	Yes	Yes
Monitoring features	T _{MON}	T _{MON}
Protection	UVLO, OCP, OTP, HS-short	UVLO, OCP, OTP, HS-short
Light load mode	ZCD, PS4	ZCD, PS4
Pulse-width modulation (V)	5	3.3
Package type	PowerPAK MLP55-31L	PowerPAK MLP55-31L
Package size (W, L, H) (mm)	5.0 x 5.0 x 0.75	5.0 x 5.0 x 0.75
Status code	2	2
Product type	VRPower (DrMOS)	VRPower (DrMOS)
Applications	Computer, industrial, networking	Computer, industrial, networking

To request the full version of the datasheet, please contact: ICmarketing@vishay.com

Vishay Siliconix

PowerPAK® MLP55-31L Case Outline



Top view	Side view	Bottom view
----------	-----------	-------------

DIM.	MILLIMETERS			INCHES				
DIIVI.	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.		
A (8)	0.70	0.75	0.80	0.027	0.029	0.031		
A1	0.00	-	0.05	0.000	-	0.002		
A2		0.20 ref.			0.008 ref.			
b ⁽⁴⁾	0.20	0.25	0.30	0.008	0.010	0.012		
D	4.90	5.00	5.10	0.193	0.196	0.200		
е		0.50 BSC			0.019 BSC			
E	4.90	5.00	5.10	0.193	0.196	0.200		
	0.35	0.40	0.45	0.013	0.015	0.017		
N ⁽³⁾	32			32				
Nd ⁽³⁾	8			8				
Ne ⁽³⁾	8			8				
D2-1	0.98	1.03	1.08	0.039	0.041	0.043		
D2-2	0.98	1.03	1.08	0.039	0.041	0.043		
D2-3	1.87	1.92	1.97	0.074	0.076	0.078		
D2-4		0.30 BSC		0.012 BSC				
D2-5	1.00	1.05	1.10	0.039	0.039 0.041 0.04			
E2-1	1.27	1.32	1.37	0.050	0.052	0.054		
E2-2	1.93	1.98	2.03	0.076	0.078	0.080		
E2-3	3.75	3.80	3.82	0.148	0.150	0.152		
E2-4		0.45 BSC		0.018 BSC				
F1	0.20 BSC			0.008 BSC				
F2	0.20 BSC		0.008 BSC					
K1	0.67 BSC		0.026 BSC					
K2	0.22 BSC		0.008 BSC					
K3	1.25 BSC		0.049 BSC					
K4		0.05 BSC		0.002 BSC				
K5		0.38 BSC		0.015 BSC				
K6		0.12 BSC		0.005 BSC				

Revision: 24-Oct-16 Document Number: 64909



Package Information

www.vishay.com

Vishay Siliconix

DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
K7	0.40 BSC			0.016 BSC		
K8	0.40 BSC			0.016 BSC		
K9	0.40 BSC			0.016 BSC		
K10	0.85 BSC			0.033 BSC		
K11	0.40 BSC			0.016 BSC		
K12	0.40 BSC			0.016 BSC		

ECN: T16-0644-Rev. E, 24-Oct-16

DWG: 6025

Notes

- 1. Use millimeters as the primary measurement
- 2. Dimensioning and tolerances conform to ASME Y14.5M. 1994
- 3. N is the number of terminals,

Nd is the number of terminals in X-direction, and

Ne is the number of terminals in Y-direction

📐 The pin #1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body

Exact shape and size of this feature is optional


7. Package warpage max. 0.08 mm


Applied only for terminals






Recommended Land Pattern PowerPAK® MLP55-31L





All dimensions in millimeters



Revision: 18-Oct-2019 1 Document Number: 66944



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.