











ACAD GENERATED DRAWING. DON'T CHANGE BY HAND

REV	DATE	ECN NO.	MODIFICATION	APPROVER
B	2010/12/17	RD00310121701	版本升级	HYQ



SPECIFICATION


- Material:
 - Housing: Thermoplastic, UL 94V-0, COLOR:BLACK.
 - Pin MATERIAL : BRASS ALLOY
 - FINISH: TIN PLATED OVER NICKEL PLATED
- Electrical Characteristics:
 - Voltage rating: 250V AC(RMS) or DC.
 - Current rating : 2.5A(max).
 - Operating Temperature: -25°C~+85°C.
 - Insulation resistance: 1000M ohms min. at 500VDC
 - Dielectric withstanding voltage: 1000 VAC/1minute.
 - Contact resistance: 20m ohms max.
- Applicable Wire:AWG#30~#20

Pin	DIMENSION	
	A	B
02	/	6.65
04	3.00	9.65
06	6.00	12.65
08	9.00	15.65
10	12.00	18.65
12	15.00	21.65
14	18.00	24.65
16	21.00	27.65
18	24.00	30.65
20	27.00	33.65
22	30.00	36.65
24	33.00	39.65


GENERAL TOLERANCE	UNITS	NAME:		深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO.,LTD.	
	SELECT	mm	Wafer 3.0mm 2*XP		
	TOL.	MAT'L	PART NO:		
	ON.	FINISH	WF300** -08**		
	1	Q'TY	APPD: hyq		
2		CHKD: Vicky		TITLE: Wafer 3.0mm 2*XP 90° 塑胶定位柱 DWG NO. ATOM-A01469	
3		DR: Aimee			
4					
5				SCALE	
6				SHEET	
7				REV	
8				1:1	
				1/2	
				B	

ACAD GENERATED DRAWING. DON'T CHANGE BY HAND


REV	DATE	ECN NO.	MODIFICATION	APPROVER
B	2010/12/17	RD00310121701	版本升级	HYQ




18-CKT.




10-CKT.




2-CKT.




20-CKT.




12-CKT.




4-CKT.




22-CKT.




14-CKT.




6-CKT.



24-CKT.



16-CKT.



8-CKT.

2*1P--2*12P 结构对照图

GENERAL TOLERANCE			UNITS	NAME:	ATOM® 深圳市爱特姆科技有限公司 SHENZHEN ATOM TECHNOLOGY CO., LTD.			
SELECT	✓		mm	Wafer 3.0mm 2*XP	PART NO:	WF300**--08***		
ON.	TOL.	1 2 3	MAT'L		APPD:	hyq		
X.XXX	±0.10±0.05±0.15		FINISH		CHKD:	Vicky		
X.XX	±0.15±0.13±0.25		Q'TY		DR:	Aimee		
X.X	±0.20±0.25±0.5					DWG NO. ATOM-A001469		
X.	±0.30±0.35±1.00					SCALE SHEET REV		
ANGLE	±2'					1:1	2/2	B