



TIP110/112 TIP115/117

COMPLEMENTARY SILICON POWER DARLINGTON TRANSISTORS

- STMicroelectronics PREFERRED SALESTYPES
- COMPLEMENTARY PNP - NPN DEVICES
- MONOLITHIC DARLINGTON CONFIGURATION
- INTEGRATED ANTIPARALLEL COLLECTOR-EMITTER DIODE


APPLICATIONS

- LINEAR AND SWITCHING INDUSTRIAL EQUIPMENT

DESCRIPTION

The TIP110 and TIP112 are silicon Epitaxial-Base NPN transistors in monolithic Darlington configuration mounted in Jedec TO-220 plastic package. They are intended for use in medium power linear and switching applications.

The complementary PNP types are TIP115 and TIP117.



ABSOLUTE MAXIMUM RATINGS

| Symbol | Parameter | Value | | Unit | |
|-----------|--|-------|------------|------|------------|
| | | NPN | TIP110 | | TIP112 |
| | | PNP | TIP115 | | TIP117 |
| V_{CBO} | Collector-Base Voltage ($I_E = 0$) | | 60 | 100 | V |
| V_{CEO} | Collector-Emitter Voltage ($I_B = 0$) | | 60 | 100 | V |
| V_{EBO} | Emitter-Base Voltage ($I_C = 0$) | | 5 | | V |
| I_C | Collector Current | | 2 | | A |
| I_{CM} | Collector Peak Current | | 4 | | A |
| I_B | Base Current | | 50 | | mA |
| P_{tot} | Total Dissipation at $T_{case} \leq 25^\circ C$ $T_{amb} \leq 25^\circ C$ | | 50 | | W |
| | | | 2 | | W |
| T_{stg} | Storage Temperature | | -65 to 150 | | $^\circ C$ |
| T_j | Max. Operating Junction Temperature | | 150 | | $^\circ C$ |

* For PNP types voltage and current values are negative

TIP110/TIP112/TIP115/TIP117

THERMAL DATA


| | | | | |
|-----------------------|-------------------------------------|-----|------|------|
| R _{thj-case} | Thermal Resistance Junction-case | Max | 2.5 | °C/W |
| R _{thj-amb} | Thermal Resistance Junction-ambient | Max | 62.5 | °C/W |

ELECTRICAL CHARACTERISTICS (T_{case} = 25 °C unless otherwise specified)


| Symbol | Parameter | Test Conditions | Min. | Typ. | Max. | Unit |
|------------------------|---|--|-------------|------|------|--------|
| I _{CEO} | Collector Cut-off Current (I _B = 0) | V _{CE} = Half Rated V _{CEO} | | | 2 | mA |
| I _{CBO} | Collector Cut-off Current (I _E = 0) | V _{CB} = Rated V _{CBO} | | | 1 | mA |
| I _{EBO} | Emitter Cut-off Current (I _C = 0) | V _{EB} = 5 V | | | 2 | mA |
| V _{CEO(sus)*} | Collector-Emitter Sustaining Voltage (I _B = 0) | I _C = 30 mA for TIP110/115 for TIP112/117 | 60 100 | | | V V |
| V _{CE(sat)*} | Collector-Emitter Saturation Voltage | I _C = 2 A I _B = 8 mA | | | 2.5 | V |
| V _{BE*} | Base-Emitter Voltage | I _C = 2 A V _{CE} = 4 V | | | 2.8 | V |
| h _{FE*} | DC Current Gain | I _C = 1 A V _{CE} = 4 V I _C = 2 A V _{CE} = 4 V | 1000 500 | | | |

* Pulsed: Pulse duration = 300 μs, duty cycle 1.5 %
For PNP types voltage and current values are negative.


Safe Operating Areas




Derating Curve




DC Current Gain (NPN type)




DC Current Gain (PNP type)




Collector-Emitter Saturation Voltage (NPN type)




Collector-Emitter Saturation Voltage (PNP type)




Base-Emitter Saturation Voltage (NPN type)




Base-Emitter Saturation Voltage (PNP type)




Base-Emitter On Voltage (NPN type)




Base-Emitter On Voltage (PNP type)



Freewheel Diode Forward Voltage (NPN types)




Freewheel Diode Forward Voltage (PNP types)



TO-220 MECHANICAL DATA

| DIM. | mm | | | inch | | |
|------|-------|------|-------|-------|-------|-------|
| | MIN. | TYP. | MAX. | MIN. | TYP. | MAX. |
| A | 4.40 | | 4.60 | 0.173 | | 0.181 |
| C | 1.23 | | 1.32 | 0.048 | | 0.051 |
| D | 2.40 | | 2.72 | 0.094 | | 0.107 |
| D1 | | 1.27 | | | 0.050 | |
| E | 0.49 | | 0.70 | 0.019 | | 0.027 |
| F | 0.61 | | 0.88 | 0.024 | | 0.034 |
| F1 | 1.14 | | 1.70 | 0.044 | | 0.067 |
| F2 | 1.14 | | 1.70 | 0.044 | | 0.067 |
| G | 4.95 | | 5.15 | 0.194 | | 0.203 |
| G1 | 2.4 | | 2.7 | 0.094 | | 0.106 |
| H2 | 10.0 | | 10.40 | 0.393 | | 0.409 |
| L2 | | 16.4 | | | 0.645 | |
| L4 | 13.0 | | 14.0 | 0.511 | | 0.551 |
| L5 | 2.65 | | 2.95 | 0.104 | | 0.116 |
| L6 | 15.25 | | 15.75 | 0.600 | | 0.620 |
| L7 | 6.2 | | 6.6 | 0.244 | | 0.260 |
| L9 | 3.5 | | 3.93 | 0.137 | | 0.154 |
| DIA. | 3.75 | | 3.85 | 0.147 | | 0.151 |



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specification mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a trademark of STMicroelectronics

© 1999 STMicroelectronics – Printed in Italy – All Rights Reserved

STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - France - Germany - Italy - Japan - Korea - Malaysia - Malta - Mexico - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A.

<http://www.st.com>