



Surface Mount Schottky Barrier Rectifier
Reverse Voltage - 20 to 200V
Forward Current - 2.0A

FEATURES


- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications

MECHANICAL DATA

- Case : SMB
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight : 0.095g / 0.003oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SS22B	SS24B	SS26B	SS28B	SS210B	SS212B	SS215B	SS220B	Units		
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	20	40	60	80	100	120	150	200	V		
Maximum RMS voltage	V_{RMS}	14	28	42	56	70	84	105	140	V		
Maximum DC Blocking Voltage	V_{DC}	20	40	60	80	100	120	150	200	V		
Maximum Average Forward Rectified Current	$I_{F(AV)}$	2.0								A		
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	55					45				A	
Max Instantaneous Forward Voltage at 2 A	V_F	0.55		0.70		0.85		0.95		V		
Maximum DC Reverse Current $T_a = 25^{\circ}C$ at Rated DC Reverse Voltage $T_a = 100^{\circ}C$	I_R	0.5			0.3					5	3	mA
Typical Junction Capacitance ⁽¹⁾	C_j	220				110				pF		
Typical Thermal Resistance ⁽²⁾	$R_{\theta JA}$	60								$^{\circ}C/W$		
Operating Junction Temperature Range	T_j	-55 ~ +125								$^{\circ}C$		
Storage Temperature Range	T_{stg}	-55 ~ +150								$^{\circ}C$		

(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C
(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristic




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current





Fig.6- Typical Transient Thermal Impedance







PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMB



The recommended mounting pad size



Marking

Type number	Marking code
SS22B	SS22
SS24B	SS24
SS26B	SS26
SS28B	SS28
SS210B	SS210
SS212B	SS212
SS215B	SS215
SS220B	SS220