Melf Metal Film Resistors

High Power Type Ultra Miniature Style [MMP Series]

FEATURE

Power Rating	I W, 2W
Resistance Tolerance	±1%, ±2%, ±5%
T.C.R.	±50ppm/°C,±100ppm/°C

DERATING CURVE

For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with the curve below.

20 40



60 80 100 120 140 160

Ambient Temperature (°C)

DIMENSIONS



STYLE	DIMENSION	DIMENSION			
Ultra Miniature	L	D	C Min.		
MMP100	5.9±0.2	2.2±0.1	0.5		
MMP200	8.5±0.2	3.2±0.2	0.5		

INTRODUCTION

The MMP Series Melf Metal Film High Power Resistors are manufactured using a vacuum sputtering system to deposit multiple layers of mixed metal alloys and passivative materials onto a carefully treated high grade ceramic substrate. SMD enabled structure and high power in small packages.

Unit: mm

Note:			

ELECTRICAL CHARACTERISTICS

STYLE	MMPI00	MMP200	
Power Rating at 70°C	IW	2W	
Maximum Working Voltage	350V		
Maximum Overload Voltage	700V		
Voltage Proof on Insulation	500V		
Resistance Range	I Ω - I MΩ & 0Ω for E24 & E96 series value		
Operating Temp. Range	-55°C to +155°C		
Temperature Coefficient	±50ppm/°C, ±100ppm/°C		

Note: Special value is available on request

ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD		APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec. (Not more than maximum Overload Voltage)	±0.5%+0.05Ω
Voltage Proof on Insulation	IEC 60115-14.7	In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-14.8	Between -55°C to +155°C	By type
Insulation Resistance	IEC 60115-14.6	in V-block for 60 Sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5 ± 0.5 Min. with ultrasonic	No deterioration of coatings and markings
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±2.0%+0.1Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr.on, 0.5Hr. Off)	±2.0%+0.1Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C ⇔ Room Temp. ⇔ +155°C ⇔ Room Temp. (5 cycles)	±0.75%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	$260\pm3^{\circ}$ C for 10 ± 1 Sec., immersed to a point 3 ± 0.5 mm from the body	±0.5%+0.05Ω

Note: RCWV(Rated Continuous Working Voltage) = $\sqrt{Power Rating \times Resistance Value}$ or Max. working voltage listed above, whichever less.

23