



Description

The SMCJ Series are designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events.

Unidirectional



Bidirectional




Feature

- Halogen-Free
- RoHS compliant
- For surface mounted application to optimize board space
- Low profile package
- Built-in strain relief
- Typical maximum temperature coefficient
 $\Delta V_{BR} = 0.1\% \times V_{BR@25^\circ C} \times \Delta T$
- Glass passivated chip junction
- 1500W peak pulse power capability at 10×1000μs waveform, repetition rate(duty cycles):0.01%
- Fast response time: typically less than 1.0ps from 0V to V_R min
- Excellent clamping capability
- Low incremental surge resistance
- High temperature soldering guaranteed:260°C/40 seconds at terminals

Applications

TVS device are ideal for the protection of I/O interfaces, V_{CC} bus and other vulnerable circuits used in telecom, computer industrial and consumer electronic application



SMCJ/DO-214AB

Maximum Ratings and Thermal Characteristics($T_A=25^\circ C$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Pulse Power Dissipation at $T_A=25^\circ C$ by 10*1000μs waveform(Fig.1) (Note 1),(Note 2)	P_{PPM}	1500	W
Power Dissipation on infinite heat sink at $T_A=50^\circ C$	$P_{M(AV)}$	6.5	W
Peak Forward Surge Current,8.3ms Single Half Sine Wave (Note 3)	I_{FSM}	200	A
Maximum Instantaneous Forward Voltage at 100A for Unidirectional only (Note 4)	V_F	3.5/5.0	V
Operation Junction and Storage Temperature Range	T_J, T_{STG}	-65 to 150	°C
Typical Thermal Resistance Junction to Lead	$R_{\theta JL}$	15	°C/W
Typical Thermal Resistance Junction to Ambient	$R_{\theta JA}$	75	°C/W

Notes:

1. Non-repetitive current pulse , per Fig. 3 and derated above $T_A=50^\circ C$ per Fig. 2.
2. Mounted on copper pad area of 0.31*0.33" (8.0*8.0mm) to each terminal.
3. Measured on 8.3ms single half sine wace or equivalent square wave for unidirectional device only, duty cycle=4 per minute maximum.
4. $V_F < 3.5V$ for $V_{BR} \leq 200V$ and $V_F < 5.0V$ for $V_{BR} \geq 201V$.

Electrical characteristics

Part Number (Uni)	Part Number (Bi)	Reverse Stand off Voltage V_R (V)	Breakdown Voltage $V_{BR} @ I_T$ (V)		Test Current I_T (mA)	Maximum Clamping Voltage $V_C @ I_{PP}$ (V)	Maximum Peak Pulse Current I_{PP} (A)	Maximum Reverse Leakage $I_R @ V_R$ (μ A)
			MIN	MAX				
SMCJ5.0A	SMCJ5.0CA	5.0	6.40	7.00	10	9.2	163.0	800
SMCJ6.0A	SMCJ6.0CA	6.0	6.67	7.37	10	10.3	145.7	800
SMCJ6.5A	SMCJ6.5CA	6.5	7.22	7.98	10	11.2	134.0	500
SMCJ7.0A	SMCJ7.0CA	7.0	7.78	8.60	10	12.0	125.0	200
SMCJ7.5A	SMCJ7.5CA	7.5	8.33	9.21	1	12.9	116.3	100
SMCJ8.0A	SMCJ8.0CA	8.0	8.89	9.83	1	13.6	110.3	50
SMCJ8.5A	SMCJ8.5CA	8.5	9.44	10.40	1	14.4	104.2	20
SMCJ9.0A	SMCJ9.0CA	9.0	10.00	11.10	1	15.4	97.4	10
SMCJ10A	SMCJ10CA	10.0	11.10	12.30	1	17.0	88.3	5
SMCJ11A	SMCJ11CA	11.0	12.20	13.50	1	18.2	82.5	1
SMCJ12A	SMCJ12CA	12.0	13.30	14.70	1	19.9	75.4	5
SMCJ13A	SMCJ13CA	13.0	14.40	15.90	1	21.5	69.8	1
SMCJ14A	SMCJ14CA	14.0	15.60	17.20	1	23.2	64.7	1
SMCJ15A	SMCJ15CA	15.0	16.70	18.50	1	24.4	61.5	1
SMCJ16A	SMCJ16CA	16.0	17.80	19.70	1	26.0	57.7	1
SMCJ17A	SMCJ17CA	17.0	18.90	20.90	1	27.6	54.4	1
SMCJ18A	SMCJ18CA	18.0	20.00	22.10	1	29.2	51.4	1
SMCJ20A	SMCJ20CA	20.0	22.20	24.50	1	32.4	46.3	1
SMCJ22A	SMCJ22CA	22.0	24.40	26.90	1	35.5	42.3	1
SMCJ24A	SMCJ24CA	24.0	26.70	29.50	1	38.9	38.6	1
SMCJ26A	SMCJ26CA	26.0	28.90	31.90	1	42.1	35.7	1
SMCJ28A	SMCJ28CA	28.0	31.10	34.40	1	45.4	33.1	1
SMCJ30A	SMCJ30CA	30.0	33.30	36.80	1	48.4	31.0	1
SMCJ33A	SMCJ33CA	33.0	36.70	40.60	1	53.3	28.2	1
SMCJ36A	SMCJ36CA	36.0	40.00	44.20	1	58.1	25.9	1
SMCJ40A	SMCJ40CA	40.0	44.40	49.10	1	64.5	23.3	1
SMCJ43A	SMCJ43CA	43.0	47.80	52.80	1	69.40	21.7	1
SMCJ45A	SMCJ45CA	45.0	50.00	55.30	1	72.7	20.6	1

Part Number (Uni)	Part Number (Bi)	Reverse Stand off Voltage V_R (V)	Breakdown Voltage $V_{BR} @ I_T$ (V)		Test Current I_T (mA)	Maximum Clamping Voltage $V_C @ I_{PP}$ (V)	Maximum Peak Pulse Current I_{PP} (A)	Maximum Reverse Leakage $I_R @ V_R$ (μ A)
			MIN	MAX				
SMCJ48A	SMCJ48CA	48.0	53.30	58.90	1	77.4	19.4	1
SMCJ51A	SMCJ51CA	51.0	56.70	62.70	1	82.4	18.2	1
SMCJ54A	SMCJ54CA	54.0	60.00	66.30	1	87.1	17.3	1
SMCJ58A	SMCJ58CA	58.0	64.40	71.20	1	93.6	16.1	1
SMCJ60A	SMCJ60CA	60.0	66.70	73.70	1	96.8	15.5	1
SMCJ64A	SMCJ64CA	64.0	71.10	78.60	1	103.0	14.6	1
SMCJ70A	SMCJ70CA	70.0	77.80	86.00	1	113.0	13.3	1
SMCJ75A	SMCJ75CA	75.0	83.30	92.10	1	121.0	12.4	1
SMCJ78A	SMCJ78CA	78.0	86.70	95.80	1	126.0	11.9	1
SMCJ85A	SMCJ85CA	85.0	94.40	104.00	1	137.0	11.0	1
SMCJ90A	SMCJ90CA	90.0	100.00	111.00	1	146.0	10.3	1
SMCJ100A	SMCJ100CA	100.0	111.00	123.00	1	162.0	9.3	1
SMCJ110A	SMCJ110CA	110.0	122.00	135.00	1	177.0	8.5	1
SMCJ120A	SMCJ120CA	120.0	133.00	147.00	1	193.0	7.8	1
SMCJ130A	SMCJ130CA	130.0	144.00	159.00	1	209.0	7.2	1
SMCJ150A	SMCJ150CA	150.0	167.00	185.00	1	243.0	6.2	1
SMCJ160A	SMCJ160CA	160.0	178.00	197.00	1	259.0	5.8	1
SMCJ170A	SMCJ170CA	170.0	189.00	209.00	1	275.0	5.5	1
SMCJ180A	SMCJ180CA	180.0	201.00	222.00	1	292.0	5.1	1
SMCJ200A	SMCJ200CA	200.0	224.00	247.00	1	324.0	4.6	1
SMCJ220A	SMCJ220A	220.0	246.00	272.00	1	356.0	4.2	1
SMCJ250A	SMCJ250CA	250.0	279.00	309.00	1	405.0	3.7	1
SMCJ300A	SMCJ300CA	300.0	335.00	371.00	1	486.0	3.1	1
SMCJ350A	SMCJ350CA	350.0	391.00	432.00	1	567.0	2.6	1
SMCJ400A	SMCJ400CA	400.0	447.00	494.00	1	648.0	2.3	1
SMCJ440A	SMCJ440CA	440.0	492.00	543.00	1	713.0	2.1	1

For bidirectional type having V_R of 10 volts and less, the I_R limit is double.

For parts without A, the V_{BR} is $\pm 10\%$ and V_C is 5% higher than with A parts.

Ratings and Characteristic Curves $T_A=25^\circ\text{C}$ unless otherwise noted




Figure 1-Peak Pulse Power Rating




Figure 2-Pulse Derating Curve




Figure 3-Pulse Waveform




Figure 4-Typical Junction Capacitance




Figure 5-Steady State Power Dissipation Derating Curve






Figure 6-Maximum Non-Repetitive Peak Forward Surge Current Uni-Directional Only

Solder Reflow Recommendation

Peak Temp=257°C, Ramp Rate=0.802deg. °C/sec



Product dimension(SMC)




DIMENSIONS ARE : $\frac{\text{INCHES}}{\text{(Millimeters)}}$

Dimension	Inches		Millimeters	
	MIN	MAX	MIN	MAX
A	0.220	0.245	5.590	6.220
B	0.305	0.320	7.750	8.130
C	0.114	0.126	2.900	3.200
D	0.260	0.280	6.600	7.110
E	0.030	0.060	0.760	1.520
F	0.079	0.103	2.060	2.620
G	-	0.008	-	0.203
H	0.079	0.103	2.060	2.620
J	0.030	0.060	0.760	1.520
K	-	0.008	-	0.203

Ordering information

Device	Package	Shipping
SMCJ Series	SMC (Pb-Free)	500 / Tape & Reel

IMPORTANT NOTICE

 and **Prisemi**[®] are registered trademarks of **Prisemi Electronics Co., Ltd (Prisemi)** ,Prisemi reserves the right to make changes without further notice to any products herein. Prisemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Prisemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. “Typical” parameters which may be provided in Prisemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including “Typicals” must be validated for each customer application by customer’s technical experts. Prisemi does not convey any license under its patent rights nor the rights of others. The products listed in this document are designed to be used with ordinary electronic equipment or devices, Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Website: <http://www.prisemi.com>

For additional information, please contact your local Sales Representative.

©Copyright 2009, Prisemi Electronics

 **Prisemi**[®] is a registered trademark of Prisemi Electronics.

All rights are reserved.