



1 2 3 4 5 6 7 8


REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD
1	△	Add dimensions	19/DEC/19	KATE	CHERRY

Electrical
 Current Rating: 2.5A AC(rms)/DC
 Voltage Rating: 250V AC(rms)/DC
 Contact Resistance: 20 mΩ Max
 Insulation Resistance: 1000 MΩ MIN
 Withstanding Voltage: 1000V AC r.m.s
 Temperature Range—Operating: -25°C~+85°C

Material and Plating
 Housing: PA66(UL 94V-2)
 Contact Pin: Brass
 Plating: Tin Plated




Type-A




Ordering Information

FWF 254 02 — S XX B 2 2 W1 B — A
 1 2 3 4 5 6 7 8 9 10 11

1	Category FWF—Wafer	2	Series Number 254—Pitch 2.54mm	3	Distinction No. 02	4	Row Option S—Single Row	5	Circuits XX	6	Entry Angle B—90° Angle
7	Plating 2—Tin Plated	8	Material—Resin 2—PA66	9	Color—Resin W1—White	10	Packaging B—PE Bag	11	Type A—Type A		



Recommended P.C.Board Layout

THIRD ANGLE PROJECTION		GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY	DATE	PART NO.	ITEM NO.	 Leader Of Industry
		X.±.012(0.30)	X.±5°	FRANK	8/JUL/13	FWF25402-SXXB22W1B-A	FWF25402	
DESIGN UNITS Inch (metric)		X.X±.008(0.20)	.X'±2°	CHECKED BY	DATE	TITLE		REV 1
SCALE	SIZE	X.XX±.006(0.15)	.XX'±1°	JACOB	8/JUL/13	Wire to Board (Wafer) Pitch 2.54mm 90° Angled (DIP)		SHEET NO. 1/2
5:1	A4	X.XXX±.004(0.10)	.XXX'±0.5°	DRAWN BY	DATE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
				CHERRY	8/JUL/13			

1 2 3 4 5 6 7 8

1 2 3 4 5 6 7 8

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

A

A

B

B

C

C

D

D



E

E

F

F

Circuits (n)	Part No.	Dimensions(in/mm)	
		A	B
2	FWF25402-S02B22W1B-A	.100(2.54)	.200(5.08)
3	FWF25402-S03B22W1B-A	.200(5.08)	.300(7.62)
4	FWF25402-S04B22W1B-A	.300(7.62)	.400(10.16)
5	FWF25402-S05B22W1B-A	.400(10.16)	.500(12.70)
6	FWF25402-S06B22W1B-A	.500(12.70)	.600(15.24)
7	FWF25402-S07B22W1B-A	.600(15.24)	.700(17.78)
8	FWF25402-S08B22W1B-A	.700(17.78)	.800(20.32)
9	FWF25402-S09B22W1B-A	.800(20.32)	.900(22.86)
10	FWF25402-S10B22W1B-A	.900(22.86)	1.000(25.40)
11	FWF25402-S11B22W1B-A	1.000(25.40)	1.100(27.94)
12	FWF25402-S12B22W1B-A	1.100(27.94)	1.200(30.48)
13	FWF25402-S13B22W1B-A	1.200(30.48)	1.300(33.02)
14	FWF25402-S14B22W1B-A	1.300(33.02)	1.400(35.56)

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 8/JUL/13	PART NO. FWF25402-SXXB22W1B-A	ITEM NO. FWF25402	 Leader Of Industry	
	X.±.012(0.30)	X.±5°	CHECKED BY JACOB	DATE 8/JUL/13	TITLE Wire to Board (Wafer) Pitch 2.54mm 90° Angled (DIP)			REV 1
	DESIGN UNITS Inch (metric)	X.X±.008(0.20)	.X±2°	DRAWN BY CHERRY	DATE 8/JUL/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
	SCALE 5:1	SIZE A4	X.XX±.006(0.15)	.XX±1°	X.XXX±.004(0.10)	.XXX±0.5°		

1 2 3 4 5 6 7 8


REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD
1	△	Size changes	14/MAY/21	KATE	CHERRY

Electrical


Current Rating: 2.5A AC(rms)/DC
Voltage Rating: 250V AC(rms)/DC
Contact Resistance: 20 mΩ Max
Insulation Resistance: 1000 MΩ MIN
Withstanding Voltage: 1000V AC r.m.s
Temperature Range—Operating: -25°C~+85°C

Material and Plating

Housing: PA66(UL 94V-2)
Contact Pin: Brass
Plating: Tin Plated




Type-A




Ordering Information

FWF 254 02 — S XX B 2 2 W5 B — A
1 2 3 4 5 6 7 8 9 10 11

1	Category FWF-Wafer	2	Series Number 254-Pitch2.54mm	3	Distinction No. 02	4	Row Option S-Single Row	5	Circuits XX	6	Entry Angle B-90° Angle
7	Plating 2-Tin Plated	8	Material-Resin 2-PA66	9	Color-Resin W5-Natural	10	Packaging B-PE Bag	11	Type A-Type A		



Recommended P.C.Board Layout

THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 8/JUL/13	PART NO. FWF25402-SXXB22W5B-A	ITEM NO. FWF25402	 Leader Of Industry	
	DESIGN UNITS Inch (metric)	X.±.012(0.30) X.X±.008(0.20) X.XX±.006(0.15) X.XXX±.004(0.10)	X.±5° .X'±2° .XX'±1° .XXX'±0.5°	CHECKED BY JACOB	DATE 8/JUL/13	TITLE Wire to Board (Wafer) Pitch 2.54mm 90° Angled (DIP)		REV 1
SCALE 5:1	SIZE A4	DRAWN BY CHERRY		DATE 8/JUL/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

1 2 3 4 5 6 7 8

REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

A

A

B

B

C

C

D

D



E

E

F

F

Circuits (n)	Part No.	Dimensions(in/mm)	
		A	B Δ
2	FWF25402-S02B22W5B-A	.100(2.54)	.202(5.14)
3	FWF25402-S03B22W5B-A	.200(5.08)	.302(7.68)
4	FWF25402-S04B22W5B-A	.300(7.62)	.403(10.22)
5	FWF25402-S05B22W5B-A	.400(10.16)	.502(12.76)
6	FWF25402-S06B22W5B-A	.500(12.70)	.602(15.30)
7	FWF25402-S07B22W5B-A	.600(15.24)	.702(17.84)
8	FWF25402-S08B22W5B-A	.700(17.78)	.802(20.38)
9	FWF25402-S09B22W5B-A	.800(20.32)	.902(22.92)
10	FWF25402-S10B22W5B-A	.900(22.86)	1.002(25.46)
11	FWF25402-S11B22W5B-A	1.000(25.40)	1.102(28.00)
12	FWF25402-S12B22W5B-A	1.100(27.94)	1.202(30.54)

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 8/JUL/13	PART NO. FWF25402-SXXB22W5B-A	ITEM NO. FWF25402	 Leader Of Industry
	DESIGN UNITS Inch (metric)	X. \pm .012(0.30)	X. \pm 5°	CHECKED BY JACOB	DATE 8/JUL/13	TITLE Wire to Board (Wafer) Pitch 2.54mm 90° Angled (DIP)	
SCALE 5:1	SIZE A4	X.XX \pm .006(0.15)	.XX \pm 1°	DRAWN BY CHERRY	DATE 8/JUL/13	REV 1	SHEET NO. 2/2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

1 2 3 4 5 6 7 8