







RoHS



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED: ±0.05mm

MAPX	MODIFICATION	DRW	DATE

NOTES:

- MATERIAL:
 - 1. MATERIAL: MOLDING: LCP UL94 V-0
 - CONTACT: COPPER ALLOY.
 - GOLD PLATED Min ON CONTACT AREA: 100u"²
 - Min TIN (LEAD FREE) ON SOLDER AREA, SHELL: COPPER ALLOY C2680J=0.30±0.03mm
 - 50u" NICKEL PLATING OVER ALL.
- MECHANICAL:
 - INSERTION: 5~20N.
 - EXTRACTION: 6~20N AFTER TEST.
 - DURABILITY: 1500 CYCLES
- ELECTRICAL:
 - CURRENT: 3A FOR VBUS, 1.25A FOR GND PIN, 0.25A FOR OTHER.
 - VOLTAGE: 20 V MAX
 - WITHSTANDING VOLTAGE: 100V AC R.M.S.
 - CONTACT RESISTANCE: 40mΩ MAX.
 - INSULATION RESISTANCE: 100MΩ MIN.
- ENVIRONMENTAL
 - TEMPERATURE RANGE -25°C ~ +85°C
- 尺寸标注事项: 者为首样全检, 重点管控尺寸
- 图例有标注
- 产品符合RoHS标准

TABLE 1:

NO.	PART NAME	QTY	MATERIAL	DESCRIPTION	REMARK
②	Shell	1	SUS 201	INI PLATING	T=0.20mm
③	Terminal	6	C2620/C2680	Au 1u" PLATING	T=0.15mm
①	Housing	3	LCP 1301		

产品图
PRODUCT CHART DWG

公差一览表	公差	公差	公差
TOLERANCE UNLESS OTHERWISE	±0.25	X	±5.°
X	±0.20	X	±2.°
XX	±0.15	XX	±1.°
.XXX	±0.10	.XXX	±0.5°

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED: ±0.05mm

单位: MM
比例: 1:1
日期: 2016-09-09

制图: 林属升
审核: 郭治富
核准: 黄园荣

制图料号: 918-4128202Y40007
产品名称: TP93 C3.1 母座直立式侧插板10.5/8.95 95 插板无弹 8P1M
PRODUCT NO: TP93 C3.1 母座直立式侧插板10.5/8.95 95 插板无弹 8P1M

角法: 版本: A0

RoHS