

## P-Channel 12-V (D-S) MOSFET

PRODUCT SUMMARY				
V <sub>DS</sub> (V)	$R_{DS(on)}\left(\Omega\right)$	I <sub>D</sub> (A)		
	0.0050 at $V_{GS} = -4.5 \text{ V}$	- 16		
- 12	0.0065 at V <sub>GS</sub> = - 2.5 V	- 15		
	0.0100 at V <sub>GS</sub> = - 1.8 V	- 13		

SO-8

#### **FEATURES**

- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET® Power MOSFET
- Compliant to RoHS Directive 2002/95/EC

# COMPLIANT HALOGEN FREE

Unit ٧


Α

W

°C

#### **APPLICATIONS**

- · Load Switch
- Battery Switch



SFET

- 50

- 55 to 150

- 8

- 1.36

1.5

0.95

- 11.5

- 2.7

3.0

1.9

	G 4 5 D			D Chan	O D
_					IIIEI WOSFET
	ABSOLUTE MAXIMUM RATINGS $\top$	$_{A}$ = 25 °C, unles	ss otherwise n	oted	
	Parameter		Symbol	10 s	Steady State
	Drain-Source Voltage	$V_{DS}$	- 12		
	Gate-Source Voltage		$V_{GS}$	±	8
	Continuous Drain Current (T <sub>.J</sub> = 150 °C) <sup>a</sup>	T <sub>A</sub> = 25 °C	I <sub>D</sub>	- 16	- 10
	Continuous Diam Current (1) = 130 C)	T 70 °C	טי	11 5	0

 $T_A = 70 \, ^{\circ}C$ 

 $T_A = 25$  °C

T<sub>A</sub> = 70 °C

THERMAL RESISTANCE RATINGS							
Parameter		Symbol	Typical	Maximum	Unit		
Maximum Junction-to-Ambient <sup>a</sup>	t ≤ 10 s	- R <sub>thJA</sub>	33	42	°C/W		
	Steady State		70	84			
Maximum Junction-to-Foot (Drain)	Steady State		16	21			

 $\overline{I}_{DM}$ 

 $I_S$ 

 $\mathsf{P}_\mathsf{D}$ 

 $T_J$ ,  $T_{stg}$ 

Notes:

a. Surface Mounted on 1" x 1" FR4 board.

Continuous Source Current (Diode Conduction)<sup>a</sup>

Operating Junction and Storage Temperature Range

服务热线:400-655-8788

Pulsed Drain Current

Maximum Power Dissipation<sup>a</sup>




Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit	
Static							
Gate Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_{D} = -600 \mu A$	- 0.5	-	1.0	V	
Gate-Body Leakage	I <sub>GSS</sub>	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 8 \text{ V}$			± 100	nA	
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> = - 12 V, V <sub>GS</sub> = 0 V			- 1	uА	
		$V_{DS} = -12 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 70 ^{\circ}\text{C}$			- 10		
On-State Drain Current <sup>a</sup>	I <sub>D(on)</sub>	V <sub>DS</sub> = - 5 V, V <sub>GS</sub> = - 4.5 V	- 30			Α	
Drain-Source On-State Resistance <sup>a</sup>	R <sub>DS(on)</sub>	V <sub>GS</sub> = - 4.5 V, I <sub>D</sub> = - 14 A		0.0050		Ω	
		V <sub>GS</sub> = - 2.5 V, I <sub>D</sub> = - 13 A		0.0065			
		V <sub>GS</sub> = - 1.8 V, I <sub>D</sub> = - 12 A		0.0100			
Forward Transconductance <sup>a</sup>	9 <sub>fs</sub>	V <sub>DS</sub> = - 6 V, I <sub>D</sub> = - 14 A		80		S	
Diode Forward Voltage <sup>a</sup>	$V_{SD}$	I <sub>S</sub> = - 2.7 A, V <sub>GS</sub> = 0 V		- 0.6	- 1.1	V	
Dynamic <sup>b</sup>							
Total Gate Charge	$Q_g$			110	165		
Gate-Source Charge	$Q_{gs}$	$V_{DS} = -6 \text{ V}, V_{GS} = -5 \text{ V}, I_{D} = -14 \text{ A}$		15		nC	
Gate-Drain Charge	$Q_{gd}$			27.5			
Turn-On Delay Time	t <sub>d(on)</sub>			110	170		
Rise Time	t <sub>r</sub>	$V_{DD}$ = - 6 V, $R_L$ = 6 $\Omega$ $I_D \cong$ - 1 A, $V_{GEN}$ = - 4.5 V, $R_g$ = 6 $\Omega$		235	350	- ns	
Turn-Off Delay Time	t <sub>d(off)</sub>			410	620		
Fall Time	t <sub>f</sub>			285	430		
Gate Resistance	$R_{g}$			3.6		Ω	
Source-Drain Reverse Recovery Time	t <sub>rr</sub>	I <sub>F</sub> = - 2.1 A, dl/dt = 100 A/μs		180	270	ns	


#### Notes:

- a. Pulse test; pulse width  $\leq 300~\mu s,$  duty cycle  $\leq 2~\%.$
- b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### TYPICAL CHARACTERISTICS 25 °C unless otherwise noted







服务热线:400-655-8788



### TYPICAL CHARACTERISTICS 25 °C unless otherwise noted



On-Resistance vs. Drain Current



T<sub>J</sub> = 150 °C

T<sub>J</sub> = 150 °C

T<sub>J</sub> = 25 °C

T<sub>J</sub> = 25 °C

V<sub>SD</sub> - Source-to-Drain Voltage (V)

Source-Drain Diode Forward Voltage

12000 10000 C - Capacitance (pF) 8000 6000 Coss 4000  $\mathsf{C}_{\mathsf{rss}}$ 2000 0 0 2 4 6 8 10 12 V<sub>DS</sub> - Drain-to-Source Voltage (V)

Capacitance

1.6
V<sub>GS</sub> = 4.5 V
I<sub>D</sub> = 14 A

1.4

(Nouralized)

1.0

0.8

0.6

- 50 - 25

0


T<sub>J</sub> - Junction Temperature (°C)

On-Resistance vs. Junction Temperature

75

100

125





On-Resistance vs. Gate-to-Source Voltage

30





#### TYPICAL CHARACTERISTICS 25 °C unless otherwise noted






Single Pulse Power, Junction-to-Ambient








Normalized Thermal Transient Impedance, Junction-to-Ambient

服务热线:400-655-8788



### TYPICAL CHARACTERISTICS 25 °C unless otherwise noted



Normalized Thermal Transient Impedance, Junction-to-Foot

服务热线:400-655-8788



## **Disclaimer**

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

### **Material Category Policy**

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be oHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.