



N-Channel 60-V (D-S) MOSFET

PRODUCT SUMMARY				
V _{DS} (V)	$R_{DS(on)}$ (Ω)	I _D (mA)		
60	2.8 at V _{GS} = 10 V	250		





N-Channel MOSFET

FEATURES

- Halogen-free According to IEC 61249-2-21 Definition
- Low Threshold: 2 V (typ.)
- Low Input Capacitance: 25 pF
- Fast Switching Speed: 25 ns
- Low Input and Output Leakage
- TrenchFET® Power MOSFET
- 1200V ESD Protection
- Compliant to RoHS Directive 2002/95/EC



- · Low Offset Voltage
- Low-Voltage Operation
- Easily Driven Without Buffer
- **High-Speed Circuits**
- Low Error Voltage

APPLICATIONS

- Direct Logic-Level Interface: TTL/CMOS
- Drivers: Relays, Solenoids, Lamps, Hammers, Display, Memories, Transistors, etc.
- **Battery Operated Systems**
- Solid-State Relays

ABSOLUTE MAXIMUM RATINGS $T_A = 25 ^{\circ}C$, unless otherwise noted					
Parameter	Symbol	Limit	Unit		
Drain-Source Voltage		V_{DS}	60	V	
Gate-Source Voltage	urce Voltage		± 20	V	
Continuous Drain Current (T _{.I} = 150 °C) ^b	T _A = 25 °C	- I _D	250	mA	
Continuous Drain Current (1) = 150 °C)	T _A = 100 °C		150		
Pulsed Drain Current ^a		I _{DM}	800		
Davies Discinstiant	T _A = 25 °C	P _D	0.30	W	
Power Dissipation ^b	T _A = 100 °C	T _A = 100 °C		VV	
Maximum Junction-to-Ambient ^b		R _{thJA}	350	°C/W	
Operating Junction and Storage Temperature Range		T _{J,} T _{stg}	- 55 to 150	°C	

- a. Pulse width limited by maximum junction temperature.
- b. Surface Mounted on FR4 board.

服务热线:400-655-8788

FREE

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply.



			Limits				
Parameter	Symbol	Test Conditions	Min.	Typ. ^a	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 10 \mu\text{A}$	60			V	
Gate-Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}$, $I_D = 250 \mu A$	1		2.5	V	
		$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 10	± 10	
		$V_{DS} = 0 \text{ V}, V_{GS} = \pm 15 \text{ V}$			1 µA		
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 10 \text{ V}$			± 150	nA	
		$V_{DS} = 0 \text{ V}, V_{GS} = \pm 10 \text{ V}, T_{J} = 85 \text{ °C}$		± 1000			
		$V_{DS} = 0 \text{ V}, V_{GS} = \pm 5 \text{ V}$			± 100		
7 0		$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$	1		1		
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 60 V, V _{GS} = 0 V , T _J = 125 °C			500	μA	
On-State Drain Current ^a	I _{D(on)}	V _{GS} = 10 V, V _{DS} = 7.5 V	500				
		V _{GS} = 4.5 V, V _{DS} = 10 V	300			mA	
Drain-Source On-Resistance ^a	-	V _{GS} = 10 V, I _D = 200 mA		2.8	1		
	R _{DS(on)}	$V_{GS} = 4.5 \text{ V}, I_D = 150 \text{ mA}$		3.1		Ω	
Forward Transconductance ^a	9 _{fs}	V _{DS} = 10 V, I _D = 100 mA	100			mS	
Diode Forward Voltage	V_{SD}	I _S = 100 mA, V _{GS} = 0 V			1.3	V	
Dynamic ^a			1			ı	
Total Gate Charge	Qg	$V_{DS} = 10 \text{ V}, V_{GS} = 4.5 \text{ V}$ $I_{D} \cong 150 \text{ mA}$		0.4	0.6	nC	
Input Capacitance	C _{iss}			25		pF	
Output Capacitance	C _{oss}	$V_{DS} = 25 \text{ V}, V_{GS} = 0 \text{ V}$		5			
Reverse Transfer Capacitance	C _{rss}	f = 1 MHz		2.0			
Switching ^{a, b, c}							
Turn-On Time	t _{d(on)}	$V_{DD} = 30 \text{ V}, R_1 = 150 \Omega$			20	ns	
Turn-Off Time	t _{d(off)}	$I_{D} \cong 200 \text{ mA}, V_{GEN} = 10 \text{ V}, R_{G} = 10 \Omega$			30		

Notes:


- a. For DESIGN AID ONLY, not subject to production testing.
- b. Pulse test: PW \leq 300 μ s duty cycle \leq 2 %.
- c. Switching time is essentially independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




3


TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted







TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted







Source-Drain Diode Forward Voltage










Threshold Voltage Variance Over Temperature


Single Pulse Power, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Ambient



THERMAL RATINGS (T_A = 25 °C, unless otherwise noted)




Normalized Thermal Transient Impedance, Junction-to-Foot


Note


- · The characteristics shown in the two graphs
 - Normalized Transient Thermal Impedance Junction-to-Ambient (25 °C)
 - Normalized Transient Thermal Impedance Junction-to-Foot (25 °C) are given for general guidelines only to enable the user to get a "ball park" indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions.



SOT-23 (TO-236): 3-LEAD








Dim	MILLIMETERS		INCHES		
	Min	Max	Min	Max	
Α	0.89	1.12	0.035	0.044	
A ₁	0.01	0.10	0.0004	0.004	
A ₂	0.88	1.02	0.0346	0.040	
b	0.35	0.50	0.014	0.020	
С	0.085	0.18	0.003	0.007	
D	2.80	3.04	0.110	0.120	
E	2.10	2.64	0.083	0.104	
E ₁	1.20	1.40	0.047	0.055	
е	0.95 BSC		0.0374 Ref		
e ₁	1.90 BSC		0.0748 Ref		
L	0.40	0.60	0.016	0.024	
L ₁	0.64 Ref		0.025 Ref		
S	0.50 Ref		0.020 Ref		
q	3°	8°	3°	8°	
ECN: S-03946-Rev. K. 09-	Jul-01	•	<u> </u>		

DWG: 5479



RECOMMENDED MINIMUM PADS FOR SOT-23



Recommended Minimum Pads Dimensions in Inches/(mm)

服务热线:400-655-8788 7



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.