

P-Channel 60 V (D-S) MOSFET

PRODUCT SUMMARY						
V _{DS} (V)	$R_{DS(on)}(\Omega)$	I _D (A) ^d	Q _g (Typ)			
- 60	0.053 at V _{GS} = - 10 V	- 25	26			
- 60	0.062 at V _{GS} = - 4.5 V	- 20	20			


FEATURES

- Halogen-free According to IEC 61249-2-21 Definition
- TrenchFET[®] Power MOSFET
- 100 % UIS Tested
- Compliant to RoHS Directive 2002/95/EC



APPLICATIONS

- High Side Switch for Full Bridge Converter
- DC/DC Converter for LCD Display



P-Channel MOSFET

	1	О	-2	51		
	c			_		7
		(\supset)		
_	\prod		П		П	_
	G		D		S	
	Т	ор	٧	iew	/	

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise note)					
Parameter	Symbol	Limit	Unit		
Drain-Source Voltage	V _{DS}	- 60	V		
Gate-Source Voltage	V _{GS}	± 20			
Continuous Drain Current (T _{.I} = 150 °C)	T _C = 25 °C	I-	- 25		
Continuous Drain Current (1) = 130 °C)	T _C = 125 °C	l _D	- 20		
Pulsed Drain Current		I _{DM}	- 100	A	
Avalanche Current, Single Pulse L = 0.1 mH		I _{AS}	I _{AS} - 22		
Repetitive Avalanche Energy, Single Pulse ^a		E _{AS}	24.2	mJ	
Dower Dissingtion	T _C = 25 °C	P _D	38.5 ^c	w	
Power Dissipation	T _A = 25 °C	1 'D	2.3 ^{b, c}] vv	
Operating Junction and Storage Temperature Range	T _J , T _{stg}	- 55 to 150	°C		

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
Marian and Landing to Ambient	t ≤ 10 s	R _{thJA}	17	21	
Maximum Junction-to-Ambient ^b	Steady State	' 'thJA	45	55	°C/W
Maximum Junction-to-Case		R _{thJC}	2.7	3.25	

Notes:

- a. Duty cycle \leq 1 %.
- b. When mounted on 1" square PCB (FR-4 material).
- c. See SOA curve for voltage derating.
- d. Based up on T_C = 25 °C.

服务热线:400-655-8788

1



Parameter	Symbol	Test Conditions	Min .	Тур.	Max.	Unit	
Static							
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = -250 \mu\text{A}$	- 60			V	
Gate Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_{D} = -250 \mu A$	- 1		- 3	V	
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA	
		V _{DS} = - 60 V, V _{GS} = 0 V		- 1			
Zero Gate Voltage Drain Current	I _{DSS}	$V_{DS} = -60 \text{ V}, V_{GS} = 0 \text{ V}, T_{J} = 125 ^{\circ}\text{C}$			- 50	μΑ	
		V _{DS} = - 60 V, V _{GS} = 0 V, T _J = 150 ° C			- 125		
On-State Drain Current ^a	I _{D(on)}	$V_{DS} = -5 \text{ V}, V_{GS} = -10 \text{ V}$	- 30			Α	
		V _{GS} = - 10 V, I _D = - 10 A		0.053			
Drain Course On State Besistance	Book	$V_{GS} = -10 \text{ V}, I_D = -10 \text{ A}, T_J = 125 \text{ °C}$	0.102] _	
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = - 10 V, I _D = - 10 A, T _J = 150 °C		0.120		Ω	
		$V_{GS} = -4.5 \text{ V}, I_D = -5 \text{ A}$		0.062			
Forward Transconductance ^a	9 _{fs}	V _{DS} = - 15 V, I _D = - 10 A		22		S	
Dynamic ^b							
Input Capacitance	C _{iss}			1140	1710	pF	
Output Capacitance	C _{oss}	$V_{GS} = 0 \text{ V}, V_{DS} = -25 \text{ V}, f = 1 \text{ MHz}$		130			
Reverse Transfer Capacitance	C _{rss}			90			
Total Gate Charge ^c	Qg			26	40		
Gate-Source Charge ^c	Q _{gs}	$V_{DS} = -30 \text{ V}, V_{GS} = -10 \text{ V}, I_{D} = -10 \text{ A}$		4.5		nC	
Gate-Drain Charge ^c	Q _{gd}			7			
Gate Resistance	R _g	f = 1 MHz		7		Ω	
Turn-On Delay Time ^c	t _{d(on)}			8	15		
Rise Time ^c	t _r	$V_{DD} = -30 \text{ V, R}_{L} = 3 \Omega$		9	15	ns	
Turn-Off Delay Time ^c	t _{d(off)}	$I_D \cong -19 \text{ A}, V_{GEN} = -10 \text{ V}, R_g = 2.5 \Omega$		65	100		
Fall Time ^c	t _f			30	45		
Drain-Source Body Diode and Charact	eristics (T _C = 2	5 °C) ^b					
Continuous Current	I _S				- 30		
Pulsed Current	I _{SM}				- 30	Α	
Forward Voltage ^a	V _{SD}	I _F = - 19 A, V _{GS} = 0 V		- 1	- 1.5	V	
Reverse Recovery Time	t _{rr}	I _F = - 19 A, di/dt = 100 A/μs		41	61	ns	

Notes:


- a. Pulse test; pulse width $\leq 300~\mu s,$ duty cycle $\leq 2~\%.$
- b. Guaranteed by design, not subject to production testing.
- c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


服务热线:400-655-8788




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Output Characteristics




Transconductance




Capacitance

30 25 I_D - Drain Current (A) 20 15 10 T_C = 125 °C 5 25 °C 55 °C 0 0.0 0.5 1.0 1.5 2.0 2.5 3.0 3.5 4.0 V_{GS} - Gate-to-Source Voltage (V)

Transfer Characteristics



On-Resistance vs. Drain Current




ag Total date offarge (110)


Gate Charge



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




On-Resistance vs. Junction Temperature




Source-Drain Diode Forward Voltage


THERMAL RATINGS



Maximum Drain Current vs. Case Temperature




* V_{GS} > minimum V_{GS} at which r_{DS(on)} is specified **Safe Operating Area**



Normalized Thermal Transient Impedance, Junction-to-Ambient



THERMAL RATINGS




Normalized Thermal Transient Impedance, Junction-to-Case

服务热线:400-655-8788



TO-251AA



Note: Dimension L3 is for reference only.

	MILLIM	IETERS	INCHES			
Dim	Min	Max	Min	Max		
Α	2.21	2.38	0.087	0.094		
A 1	0.89	1.14	0.035	0.045		
b	0.71	0.89	0.028	0.035		
b1	0.76	1.14	0.030	0.045		
b2	5.23	5.43	0.206	0.214		
С	0.46	0.58	0.018	0.023		
с1	0.46	0.58	0.018	0.023		
D	5.97	6.22	0.235	0.245		
Е	6.48	6.73	0.255	0.265		
е	2.28	BSC	0.090 BSC			
L	3.89	9.53	0.153	0.375		
L1	1.91	2.28	0.075	0.090		
L2	0.89	1.27	0.035	0.050		
L3	1.15	1.52	0.045	0.060		
ECN: S-03946—Rev. E, 09-Jul-01 DWG: 5346						

服务热线:400-655-8788



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be oHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.