

**Vishay Semiconductors** 

# Low Capacitance, Single-Line ESD-Protection Diode in SOD-323

# 2



20503

**MARKING** (example only)



XYZ = type code (see table below) bar = pin 1

## LINKS TO ADDITIONAL RESOURCES



## **FEATURES**

- For LIN-Bus applications
- Small SOD-323 package
- 1-line ESD-protection
- Working range: ± 26.5 V
- Low leakage current I<sub>R</sub> < 0.05 μA</li>
- Low load capacitance C<sub>D</sub> < 16 pF</li>
- ESD-protection acc. IEC 61000-4-2 ± 30 kV contact discharge ± 30 kV air discharge
- ESD capability according to AEC-Q101: human body model: class H3B: > 8 kV
- e3 pins plated with tin (Sn)
- AEC-Q101 gualified available
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

ORDERING INFORMATION								
PART NUMBER (EXAMPLE)	ENVIRONMENTAL AND QUALITY CODE				PACKAG	ING CODE		
	AEC-Q101 QUALIFIED	RoHS-COMPLIANT + LEAD (Pb)-FREE TERMINATIONS		TIN PLATED	3K PER 7" REEL (8 mm TAPE)	10K PER 13" REEL (8 mm TAPE)	ORDERING CODE (EXAMPLE)	
		STANDARD	GREEN	PLATED	15K/BOX = MOQ	10K/BOX = MOQ		
VLIN2626-02G	-	E	-	3	-08	-	VLIN2626-02G-E3-08	
VLIN2626-02G	Н	E	-	3	-08	-	VLIN2626-02GHE3-08	
VLIN2626-02G	-	E	-	3	-	-18	VLIN2626-02G-E3-18	
VLIN2626-02G	Н	E	-	3	-	-18	VLIN2626-02GHE3-18	

PACKAGE DATA							
DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS	
VLIN2626-02G	SOD-323	262	4.30 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C	

ABSOLUTE MAXIMUM RATINGS						
PARAMETER	ARAMETER TEST CONDITIONS		VALUE	UNIT		
Peak pulse current	$T_A = 25$ °C; acc. IEC 61000-4-5; $t_p = 8/20 \ \mu s$ ; single shot	I <sub>PPM</sub>	4	А		
Peak pulse power	$T_A = 25$ °C; acc. IEC 61000-4-5; $t_p = 8/20 \ \mu s$ ; single shot	P <sub>PP</sub>	200	W		
ESD immunity	Contact discharge acc. IEC 61000-4-2; C = 150 pF, R = 330 $\Omega,$ T <sub>A</sub> = 25 °C	V	± 30	kV		
	Air discharge acc. IEC 61000-4-2; C = 150 pF, R = 330 $\Omega,$ T <sub>A</sub> = 25 °C	V <sub>ESD</sub>	± 30	kV		
ESD immunity	Contact discharge acc. ISO 10605; C = 330 pF, R = 330 $\Omega$ , T <sub>A</sub> = 25 °C	V	± 30	kV		
	Air discharge acc. ISO 10605; C = 330 pF, R = 330 $\Omega$ , T <sub>A</sub> = 25 °C	V <sub>ESD</sub>	± 30	kV		
Operating temperature	Junction temperature	TJ	-55 to +150	°C		
Storage temperature		T <sub>STG</sub>	-55 to +150	°C		



COMPLIANT

# VLIN2626-02G



**Vishay Semiconductors** 

<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)								
PARAMETER	TEST CONDITIONS / REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT		
Protection paths	Number of lines which can be protected	N <sub>channel</sub>	-	-	1	lines		
Reverse stand-off voltage	Max. reverse working voltage	V <sub>RWM</sub>	-	-	26.5	V		
Reverse voltage	At I <sub>R</sub> = 0.05 μA	V <sub>R</sub>	26.5	-	-	V		
Reverse current	At V <sub>RWM</sub> = 26.5 V	I <sub>R</sub>	-	-	0.05	μA		
Reverse breakdown voltage	At I <sub>R</sub> = 1 mA	V <sub>BR</sub>	28	30	32	V		
	At I <sub>PP</sub> 1 A; t <sub>p</sub> = 8/20 μs	V <sub>C</sub>	-	32	40	V		
Reverse clamping voltage	At $I_{PP} = I_{PPM} = 4 \text{ A}$ ; $t_p = 8/20 \mu\text{s}$	V <sub>C</sub>	-	39	50	V		
Capacitance	At $V_R = 0 V$ , f = 1 MHz	CD	-	13.5	16	pF		

TYPICAL CHARACTERISTICS (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - ESD Discharge Current Wave Form acc. IEC 61000-4-2 (330  $\Omega$  / 150 pF)




Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance  $C_D$  vs. Reverse Voltage  $V_R$ 




Fig. 4 - Typical Reverse Voltage  $V_R$  vs. Reverse Current  $I_R$ 

2

For technical questions, contact: <u>ESDprotection@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

## **Vishay Semiconductors**






Fig. 5 - Typical Peak Clamping Voltage  $V_C$  vs. Peak Pulse Current I<sub>PP</sub>







Fig. 6 - Typical Clamping Voltage V<sub>C-TLP</sub> vs. Pulse Current I<sub>TLP</sub>


#### PACKAGE DIMENSIONS in millimeters (inches) SOD-323







Footprint recommendation:




Document no.: S8-V-3910.02-001 (4) Created - Date: 24.August.2004 Rev. 6 - Date: 23.Sept.2016 22771

Rev. 1.3, 25-Jan-2021

3


Document Number: 85915

For technical questions, contact: <u>ESDprotection@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





## CARRIER TAPE SOD-323




**B-B** Section



Document no.: S8-V-3717.07-002 (4) Created - Date: 09. Feb. 2010 22824

## **ORIENTATION IN CARRIER TAPE SOD-323**



4



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.