

N-Channel Super Junction Power MOSFET III

General Description

The series of devices use advanced trench gate super junction technology and design to provide excellent R_{DS(ON)} with low gate charge. This super junction MOSFET fits the industry's AC-DC SMPS requirements for PFC, AC/DC power conversion, and industrial power applications.


Features

- New technology for high voltage device
- Low on-resistance and low conduction losses
- small package
- Ultra Low Gate Charge cause lower driving requirements
- 100% Avalanche Tested
- ROHS compliant

Application

- Power factor correction (PFC)
- Switched mode power supplies(SMPS)
- Uninterruptible Power Supply (UPS)

V _{DS}	650	V
R _{DS(ON)TYP}	290	mΩ
I _D	11.5	A




Schematic diagram

Package Marking And Ordering Information

Device	Device Package	Marking
NCE65T360D	TO-263	NCE65T360D
NCE65T360	TO-220	NCE65T360
NCE65T360F	TO-220F	NCE65T360F







TO-263

TO-220

TO-220F

v1.1

Table 1. Absolute Maximum Ratings (T_c=25℃)

Parameter	Symbol	NCE65T360D NCE65T360	NCE65T360F	Unit
Drain-Source Voltage (VGS=0V)	V _{DS}	65	50	V
Gate-Source Voltage (VDS=0V), AC(f>1HZ)	V _G S	土	30	V
Continuous Drain Current at T _C =25°C	I _{D (DC)}	11.5	11.5*	Α
Continuous Drain Current at T _C =100°C	I _{D (DC)}	7 7*		Α
Pulsed drain current (Note 1)	I _{DM (pluse)}	46	46*	Α
Maximum Power Dissipation(T _C =25℃)	P _D	101 32.6		W
Derate above 25°C		0.81	0.26	W/°C
Single pulse avalanche energy (Note2)	Eas	144		mJ
Avalanche current ^(Note 1)	I _{AR}	6		Α
Repetitive Avalanche energy , t_{AR} limited by T_{jmax} (Note 1)	E _{AR}	0.5		mJ



Parameter	Symbol	NCE65T360D NCE65T360	NCE65T360F	Unit
Drain Source voltage slope, V _{DS} ≤480 V,	dv/dt	50		V/ns
Reverse diode dv/dt, $V_{DS} \leq 480 \text{ V,I}_{SD} < I_{D}$	dv/dt	15		V/ns
Operating Junction and Storage Temperature Range	T_{J} , T_{STG}	-55	+150	°C

^{*} limited by maximum junction temperature

Table 2. Thermal Characteristic

Parameter	Symbol	NCE65T360D NCE65T360	NCE65T360F	Unit
Thermal Resistance, Junction-to-Case (Maximum)	R _{thJC}	1.24	3.83	°C /W
Thermal Resistance, Junction-to-Ambient (Maximum)	R _{thJA}	62	80	°C /W

Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)

Table 3. Electrical Characteristics	istics (TA=25 Cuniess otherwise noted)						
Parameter	Symbol	Condition	Min	Тур	Max	Unit	
On/off states							
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	650			V	
Zero Gate Voltage Drain Current(Tc=25℃)	I _{DSS}	V _{DS} =650V,V _{GS} =0V		0.05	1	μA	
Zero Gate Voltage Drain Current(Tc=125℃)	I _{DSS}	V _{DS} =650V,V _{GS} =0V			100	μA	
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V			±100	nA	
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} ,I _D =250μA	3	3.5	4	V	
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =7A		300	360	mΩ	
Dynamic Characteristics							
Input Capacitance	C _{Iss}	\/ -50\/\/ -0\/		870		pF	
Output Capacitance	Coss	V_{DS} =50V, V_{GS} =0V, F=1.0MHz		54		pF	
Reverse Transfer Capacitance	C _{rss}	F=1.UMHZ		1.8		pF	
Total Gate Charge	Q_g	\/ 400\/ 44.54		19		nC	
Gate-Source Charge	Q _{gs}	V _{DS} =480V,I _D =11.5A, V _{GS} =10V		6		nC	
Gate-Drain Charge	Q_{gd}	V _{GS} =10V		6.5		nC	
Switching times							
Turn-on Delay Time	t _{d(on)}			11		nS	
Turn-on Rise Time	t _r	V_{DD} =380V, I_{D} =5.5A,		8		nS	
Turn-Off Delay Time	$t_{d(off)}$	$R_G=3\Omega,V_{GS}=10V$		58	70	nS	
Turn-Off Fall Time	t _f			9	14	nS	
Source- Drain Diode Characteristics							
Source-drain current(Body Diode)	I _{SD}	T -05°C			11.5	Α	
Pulsed Source-drain current(Body Diode)	I _{SDM}	T _C =25°C			46	Α	
Forward on voltage	V _{SD}	Tj=25°C,I _{SD} =11.5A,V _{GS} =0V		0.9	1.2	V	
Reverse Recovery Time	t _{rr}	T:-05°C 5.04		220		nS	
Reverse Recovery Charge	Q _{rr}	Tj=25°C,I _F =5.8A,		2.2		uC	
Peak Reverse Recovery Current	I _{rrm}	di/dt=100A/µs		19		Α	
-							

Notes: 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2. Tj=25°C,VDD=50V,VG=10V, R_G=25 Ω

v1.1



TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (curves)

Figure 1. Safe operating area




Figure 2. Safe operating area for TO-220F




Figure 3. Source-Drain Diode Forward Voltage




Figure 4. Output characteristics




Figure 5. Transfer characteristics





Figure 6. Static drain-source on resistance



v1.1



Figure 7. R_{DS(ON)} vs Junction Temperature




Figure8. BV_{DSS} vs Junction Temperature




Figure 9. Maximum ID vs Junction Temperature




Figure 10. Gate charge waveforms




Figure 11. Capacitance





Figure 12. Transient Thermal Impedance






Wuxi NCE Power Co., Ltd

NCE65T360D,NCE65T360,NCE65T360F


Figure 13. Transient Thermal Impedance for TO-220F







Test circuit


1) Gate charge test circuit & Waveform







2) Switch Time Test Circuit:





3) Unclamped Inductive Switching Test Circuit & Waveforms








Wuxi NCE Power Co., Ltd

NCE65T360D,NCE65T360,NCE65T360F


TO-263-3L Package Information



Symphol .	Dimensions	In Millimeters	Dimension	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.		
А	4.32	4.57	0.170	0.180		
A1	-	0.25		0.010		
b	0.71	0.94	0.028	0.037		
b2	1.15	1.40	0.045	0.055		
С	0.46	0.61	0.018	0.024		
c2	1.22	1.40	0.048	0.055		
D	8.89	9.40	0.350	0.370		
D1	8.01	8.23	0.315	0.324		
Е	10.04	10.28	0.395	0.405		
E1	7.88	8.08	0.310	0.318		
е	2.54	BSC	0.100	BSC		
L	14.73	15.75	0.580	0.620		
L1	2.29	2.79	0.090	0.110		
L2	1.15	1.39	0.045	0.055		
L3	1.27	1.77	0.050	0.070		




TO-220-3L-C Package Information




0h - l	Dimensions	In Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
А	4.400	4.600	0.173	0.181
A1	2.250	2.550	0.089	0.100
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
С	0.330	0.650	0.013	0.026
c1	1.200	1.400	0.047	0.055
D	9.910	10.250	0.390	0.404
E	8.9500	9.750	0.352	0.384
E1	12.650	12.950	0.498	0.510
е	2.540 TYP.		0.100	TYP.
e1	4.980	5.180	0.196	0.204
F	2.650	2.950	0.104	0.116
Н	7.900	8.100	0.311	0.319
h	0.000	0.300	0.000	0.012
L	12.900	13.400	0.508	0.528
L1	2.850	3.250	0.112	0.128
V	7.500	REF.	0.295	REF.
Ф	3.400	3.800	0.134	0.150




TO-220F Package Information



Wuxi NCE Power Co., Ltd





Symbol	Dimensions	In Millimeters	Dimensions In Inches		
	Min.	Max.	Min.	Max.	
Α	4.500	4.900	0.177	0.193	
A1	2.340	2.740	0.092	0.108	
A2	2.560	2.960	0.101	0.117	
b1	0.700	0.900	0.028	0.035	
b2	1.180	1.580	0.046	0.062	
С	0.400	0.600	0.016	0.024	
D	9.960	10.360	0.392	0.408	
E	15.670	15.970	0.617	0.629	
E1	6.500	6.900	0.256	0.272	
E2	15.500	16.100	0.610	0.634	
е	2.54	0 TYP	0.100	TYP	
Ф	3.080	3.280	0.121	0.129	
L	12.640	13.240	0.498	0.521	
L1	3.030	3.430	0.119	0.135	



ATTENTION:

- Any and all NCE products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE representative nearest you before using any NCE products described or contained herein in such applications.
- NCE assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE products described or contained herein.
- Specifications of any and all NCE products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE Power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE Power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE product that you intend to use.
- This catalog provides information as of Mar. 2010. Specifications and information herein are subject to change without notice.