




1. FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1004H-XXA-NOHF

XXXXXT-PXX-AXXXX-LXXX-TX
① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 剥皮镀锡 (Peeled tin plated) T(可定制剥皮长度镀锡)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	
Circuit2	黄色	
Circuit3	黄色	
Circuit4	黑色	

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1004H-04A-NO HF	1PCS		
2	X1004T-PV01	4PCS		
3	UL1007/28AWG. 红. 黑. 黄色	红黑各 1PCS/ 黄2PCS	200MM	
总量				

DSND		SCALE: N/A	DRAWING NO. X1004T-PV01-A28RYB-L200-T3		
DWN		VIEW:	PART NO.:		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED				1/1	A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5
REVISIONS					
www.helloxb.com www.helloxb.cn www.xk-dg.cn					

