Messrs.

DRAFT



revised)

Delivery Specifications

Product No : Quartz Crystal Unit VT-200-F

Item code : Q-VT20N0327605C50B

Product form : $32.768 \text{kHz} \pm 5 \times 10^{-6} / 12.5 \text{ pF}$

The number of copies : 1 copy

Date of Registrantion : 21 Jun. / '16



Receipt Column	Note

NOTICE

- 1. Advance agreement will be needed before changing any contents of the specification herein.
- 2. Provided that the information herein is subject to change, only revised pages shall be reissued.
- 3. When the product described herein includes Regulated Products subject The Wassenaar Arrangement etc, they may not be exported without authorization from the appropriate governmental authorities.
- 4. The contents of this specification including all figures and illustrations are proprietary information (copyright or know-how) of Seiko Instruments Inc. It is strictly prohibited to copy all or part of these specifications to third parties without permission.
- 5. In the case that the products described herein are used as part of any devices or equipment which might influence any one of the human body, human life and property, such as physical exercise equipment, medical equipment or vehicles, please let us know that.

Dept. of Issue
Sales Section
Dept. of Control
Quality Assurance Section
Guanty / (33aranoc ocodon

1.Scope

These specifications apply to QUARTZ CRYSTAL RESONATORS (hereinafter referred to as RESONATORS) to be manufactured by Seiko Instruments Inc. (hereinafter referred to as SII) to Nansons

2.Designation

RESONATORS are designated "VT-200-F" (32.768kHz).

3. Shape and dimensions

As per the VT-200-F drawing shown on page 5.

4. Electrical characteristics

Specified on page 2 through 3.

5. Shipment and packaging

5.1 (10,000) pcs are the standard lot size to which the lot number shall be allotted 5.2 The packaging shall conform to the resonator packaging standards.

6.Outgoing inspection

- 6.1 When mutually agreed, the outgoing inspection shall be conducted as per the standard on page 4.
- 6.2 The outgoing inspection slip is not basically affixed to each packaging.

7.Warranty

In the event that any defective RESONATORS or defective lot is found at incoming inspection at (CUSTOMER) and that any defect resulting from failures in process-control at SII after incoming inspection is found, good RESONATORS shall be supplied to (CUSTOMER) free of charge as a replacement .

In the event that any trouble or problems rising directly from RESONATORS occurs, it will be amicably settled between both parties, provided that warranty shall be done within the score of replacement of good RESONATORS.

8. Amendment or abolition of the specifications.

Amendment or abolition of the specifications shall be made upon mutual consent between Nansons and SII .If any problem arises , it shall be amicably settled between both parties.

9.Effectiveness of the specifications

These specifications are effective after receipt of returned copies with your approved sign.

10. Controls On Environmental Load Substances

Complete Pb-free Complies with EU RoHS directive [1] The maximum rating

	ltem	Symbol	Rating	Note
1	Storage temperature range	T_stg	−40 ~ +85°C	
2	Maximum drive level	DL max.	1.0 μW max.	

[2] Recommended Operating Condition

	Item	Symbol	Rating	Note
1	Operating temperature range	T_use	−40 ~ +85°C	
2	Drive level	DL	0.1 μW typ.	

[3] Electrical -Characteristics

Measurement temperature: 25±2°C

LO	DI Electrical -Characteristics Measurement temperature : 25±2 C			
	Item	Symbol	Specifications	Conditions
1	Nominal frequency	f_nom	32.768 kHz	
2	Frequency tolerance	f_tol	± 5 × 10 ⁻⁶	
3	Load capacitance	C_L	12.5 pF	
4	Motional resistance	R_1	50 kΩ max.	Measured with ATI 4192A Impedance analyzer. OSC LEVEL = 0.1V
5	Q-value	Ø	40 × 10 ³ min.	calculated with the following equation: Q=(2π·Fr·L ₁)/R ₁
6	Motional capacitance	C ₁	2.0 fF typ.	
7	Shunt capacitance	Co	0.9 pF typ.	Measured with ATI 4192A Impedance analyzer. OSC LEVEL = 0.1V
8	Turnover temperature	Ti	25 ± 5°C	Measure this coefficient at 3 points of 10°C, 25°C, and 40°C using
9	Parabolic coefficient	В	(-0.035±10%)×10 ⁻⁶ /°C ²	C-MOS circuit.
10	Frequency ageing	f_age	± 3 × 10 ⁻⁶ / year	25±3°C、 First year
11	Insulation resistance	IR	500 MΩ min.	Measured with ATI 4329A Insulation Resistance Meter. Apply DC100V.

[4] Environment-proof • Mechanical property

No	Item	Specifications	Conditions	*1
1	High temperature storage	$\triangle f/f = \pm 5 \times 10^{-6}$	After storage under 85°C for 500 hrs,	
			measure at room temperature.	
2	Low temperature storage	$\triangle f/f = \pm 5 \times 10^{-6}$	After storage under -40°C for 500	*1
			hrs, measure at room temperature.	
3	High temperature and	$\triangle f/f = \pm 5 \times 10^{-6}$	After storage under 60°C±2°C, 90 to	*1
	high humidity storage		95% RH for 500 hrs, measure at room	
			temperature.	
4	Temperature cycle	$\triangle f/f = \pm 5 \times 10^{-6}$	Measured at room temperature after	*1
			20 cycles.	
			-25°C⇔+80°C for 30 minutes.	
5	Mechanical shock resistance	$\triangle f/f = \pm 5 \times 10^{-6}$	Measure after free drop of the	*2
			RESONATOR three times from the	
			height of 75cm onto a wooden board.	
6	Vibration resistance	$\triangle f/f = \pm 5 \times 10^{-6}$	Amplitude 1.5mm and 10~60Hz with	*2
			cycle time 2~3 minutes in 3 direction	
			(X,Y,and Z axis)each for 2 hrs.	
7	Resistance to soldering heat	$\triangle f/f_0 = \pm 5 \times 10^{-6}$	Measured at room temperature after	
			immersing the lead wire in a	*1
			soldering bath of 300°C±10°C for 5	
			seconds up to a position where it is	
			2mm away from the root of the	
			plug.	
8	Tensile strength of lead wire	$\triangle f/f_0 = \pm 5 \times 10^{-6}$	Apply a load of 500g for 30 seconds	*2
			in the lead wire's axial direction.	
9	Bending strength of lead wire	$\triangle f/f_0 = \pm 5 \times 10^{-6}$	Bending cycle : 0° → 45° → 0° → 45°	*2
			→ 0°	
10	Solderability of lead wire	A minimum 95% of	Apply resin-flux contained-solder to	*2
. 0	Total mo	the area to be	a soldering iron of 280°C±5°C for 5	-
		coated with solder	seconds.	

Note:

- 1. The above tests no. 1 to 9 must be conducted independently (not series tests)
- 2. *1: Measure after 24 hours soak at room temperature .
- 3. *2: Measure after 2 hours soak at room temperature .
- 4. R1 is $60k\Omega$ max. after the each above tests.

[5] Precautions

(1) Temperature for soldering the lead wire shall not exceed 300°C and the soldering time shall be within 5 seconds.

This product can not be used for the reflow soldering or flow soldering.

(2) Position to be soldered: Solder only the position where the lead wire is

1.0mm away from the glass seal.

Do not solder the case.

(3) Cutting, bending and

correction of lead wire: The glass seal shall be free of any crack or other

damage which may deteriorate the characteristics

of RESONATORS.


[6] Outgoing inspection standard

•The outgoing inspection shall be conducted as per the following standard .

•The sampling shall be performed according to the ANSI/ASQCZ1.4-1996.

No	Item	Sampling level	AQL(%)
1	Frequency tolerance	I	1.0
2	Equivalent series resistance	I	1.0
3	Outer appearance	I	1.5
4	Others characteristics	Periodical quality inspection	


[7] Out Line Drawing



DESCRIPTION	Materials	Remarks	REMARKS
VT-200-F	Ni SnCu(2∼5%Cu)		UNIT:1=1mm

[8] Packaging specification


- Packaging specification
- 1) White ball case (the inner compartment) the packing structure



- 2. Outer case packing specification (the sectional plan) [Figure 3]
- 1) The number of Carton case (the outer case) size and white ball case (the inner compartment) [Table 1] [Figure 2]

Liable	1 1			
The outer case	B4	VT5	VT10	VT20
Size(mm)	345 x 235 x 141	315 x 240 x 290	450 x 295 x 290	570 x 440 x 290
Number of white ball case	2boxes	5boxes	10boxes	20boxes

Statement of delivery or designated slip to the envelope



3. Sample of the label display (display department, please refer to [Figure 1] [Figure 2])

	PART	VT-200-F
Product bar code	LOTNo.	
	Quantity	10, 000 pcs
Item bar code *	Calibre	32.768kHz 12.5pF /±5 × 10 ⁻⁶
		12.5pF /±5 × 10 ⁻⁶
Quantity	Remarks	3
Lot. No. bar code		Pb Free

PART : Our company product name

LOT No. : Lot No. display

Quantity: Quantity

Calibre : Frequency, CL value, F0 deviation

Remarks: Marking etc.

* : Item code

4. Storage environment

A product avoids the direct ray and please store with the normal temperature and humidity .

Temperature: +15 to 35 °C
 Humidity: 25 to 85%RH

5. Storage term

We recommend using within a year of shipment under the environment set in the specification (Temperature: 15-35°C, Humidity: 25-85%RH) regardless of opening the product or not. Crystal oscillator doesn't have a lifetime by reason of little performance change caused by secular variation. Nevertheless, please note that you should confirm the specification of our product whose storage period expires before use.