


Description

This synchronous decade counter features an internal carry look ahead for application in high-speed counting designs.

The XD74LS160 characterized for operation from 0 °c to 70 °c





Absolute Maximum Ratings (Note)

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

Supply Voltage 7V Inpul Vollage 7V

Operating Free Air Temperature Range 0° to 70°

Note: The "Absolute Maximum Ratings" are those values beyond which the salety of the device cannot be guaran. teed. The device should not be operated at these limits. The parametric values defined in the "Electical Characteristics" table are not guaranteed at the absolute maximum ratings. The "Recommended Operating Condtons" table will deline the conditions tor actual device operation.

Storage Temperature Range -65°C to +150°C Recommended Operating Conditions

| Item | | Symbol | Min | Тур | Max | Unit |
|-----------------------|-------------|------------------------|------|------|------|------|
| Supply voltage | | Vcc | 4.75 | 5.00 | 5.25 | ٧ |
| Output current | | l _{oн} | _ | _ | -400 | μA |
| | | lou | _ | _ | 8 | mA |
| Operating temperature | | Topr | -20 | 25 | 75 | °C |
| Clock frequency | | folock | 0 | _ | 25 | MHz |
| Clock pulse width | | t _{w (clock)} | 25 | _ | _ | ns |
| Clear pulse width | | t _{w (clear)} | 20 | _ | _ | ns |
| Setup time | A, B, C, D | | 20 | _ | _ | ns |
| | Enable P, T | tsu | 20 | | | ns |
| | Load | | 20 | | _ | ns |
| Hold time | | t _h | 3 | _ | _ | ns |

| Symbol | Parameter | Conditions | - a | Min | Typ (Note 1) | Max | Unit |
|-----------------|------------------------------|------------------------------------------------------------------------|------|-----|-----------------|------|------|
| VI | Input Clamp Voltage | V _{CC} = Min, I _I = -18 mA | | | | -1.5 | ٧ |
| V _{OH} | High Level Output Voltage | V _{CC} = Min, I _{OH} = Max, V _{IL} = Max | XD74 | 2.7 | | Bid | ٧ |
| V _{OL} | Low Level Output Voltage | V _{CC} = Min, I _{OL} = Max, V _{IH} = Min | XD74 | | | 0.5 | ٧ |
| | Voltage | I _{OL} = 4 mA, V _{CC} = Min | XD74 | | | 0.4 | ٧ |

Note 1: All typicals are at $V_{CC} = 5V$, $T_A = 25^{\circ}C$.

Note 2: Not more than one output should be shorted at a time, and the duration should not exceed one second.

Electrical Characteristics

over recommended operating free air temperature range (unless otherwise noted) (Continued)

| Symbol | Parameter | Conditions | | Min | Typ (Note 1) | Max | Units |
|-----------------|-------------------------------------|----------------------------------------------------------------|-------|-----|-----------------|------|-------|
| lı . | Input Current @ Max | $V_{CC} = Max, V_1 = 7V$ | Other | | = = | 0.1 | mA |
| | Input Voltage | put Voltage PE, CET Inputs | | | | 0.2 | |
| I _{IH} | High Level Input Current | $V_{CC} = Max, V_1 = 2.7V$ | Other | | | 20 | μА |
| | | PE, CET Inputs | | | | 40 | μ. |
| I _{IL} | Low Level Input Current | V _{CC} = Max, V _I = 0.4V inputs | XD74 | | | -1.6 | mA |
| | | PE, CET Inputs | | | | -0.8 | |
| IOS | Short Circuit Output Current | VCc = Max(Note 2) | XD74 | -20 | - | -100 | mA |
| Іссн | Supply Current with Outputs HIGH | V _{CC} = Max, PE = GND CP = ✓, Other Inputs = 4.5V | - | | | 31 | mA |
| ICCL | Supply Current with Outputs LOW | V _{CC} = Max, V _{IN} = GND CP = | = | =+1 | <u> </u> | 31 | mA |

Switching Characteristics V_{CC} - +5.0V, T_A - +25°C

| Symbol | Parameter | R _L = C _L = | Units | | |
|-----------------------------------------------------------------------------|-------------------------------|--------------------------------------|----------|-----|--|
| | | Min | Max |] | |
| f _{máx} | Maximum Clock Frequency | 25 | | MHz | |
| t _{PLH} t _{PHL} | Propagation Delay CP to TC | D O | 25 21 | ns | |
| t _{PLH} Propagation Delay t _{PHL} CP to Q _n | | P 0 | 24 27 | ns | |
| t _{PLH} Propagation Delay t _{PHL} CET to TC | | | 14 23 | ns | |
| t _{PHL} Propagation Delay MR to Q _n (*160) | | | 28 | ns | |



Ordering information

| PN: | Package |
|-----------|---------------------|
| XD74LS160 | DIP16 1,000Pcs/Tube |

