



Glass Passivated Three Phase Rectifier Bridge


VRRM 800 to 2400V
ID 100 A

Applications

- Three phase rectifiers for power supplies
- Rectifiers for DC motor field supplies
- Battery charger rectifiers
- Input rectifiers for variable frequency drives

Features

- Three phase bridge rectifier
- Blocking voltage:800 to 2400V
- Heat transfer through aluminum oxide DBC ceramic isolated metal baseplate
- Glass passivated chip



Module Type

TYPE	VRRM	VRSM
MD100S08M4	800V	900V
MD100S12M4	1200V	1300V
MD100S16M4	1600V	1700V
MD100S18M4	1800V	1900V
MD100S20M4	2000V	2100V
MD100S22M4	2200V	2300V
MD100S24M4	2400V	2500V

Maximum Ratings

Symbol	Conditions	Values	Units
ID	Three phase, full wave Tc=100°C	100	A
IFSM	t=10mS Tvj =45°C	1020	A
i ² t	t=10mS Tvj =45°C	5200	A ² s
V _{isol}	a.c.50HZ;r.m.s.;1min	3000	V
T _{vj}		-40 to +125	°C
T _{stg}		-40 to +125	°C
Mt	To terminals(M5)	5±15%	Nm
Ms	To heatsink(M5)	5±15%	Nm
Weight	Module (Approximately)	146	g

Thermal Characteristics

Symbol	Conditions	Values	Units
R _{th(j-c)}	Per diode	1.0	°C/W
R _{th(c-s)}	Module (Approximately)	0.07	°C/W



Electrical Characteristics

Symbol	Conditions	Values			Units
		Min.	Typ.	Max.	
V _{FM}	T=25°C I _F =300A	—	1.70	1.90	V
I _{RD}	T _{vj} =25°C V _{RD} =V _R RM T _{vj} =150°C V _{RD} =V _R RM	—	—	0.3 5	mA mA

Performance Curves




Fig1. Forward Characteristics




Fig2. Power dissipation




Fig3. Transient thermal impedance




Fig4. Max Non-Repetitive Forward Surge Current




Fig5.Forward Current Derating Curve

Package Outline Information

CASE: M4

