




型号: 12080  
尺寸:  $\varnothing 11.9$   
焦距: 8mm  
感应角度:  $30^\circ$   
感应距离: 17m



型号: 13250  
尺寸:  $\varnothing 13$   
焦距: 25mm  
感应角度:  $30^\circ$   
感应距离: 16m



型号: 20360  
尺寸:  $\varnothing 20$   
焦距: 36mm  
感应角度:  $30^\circ$   
感应距离: 18m



型号: 20200  
尺寸:  $\varnothing 19.9$   
焦距: 20mm  
感应角度:  $30^\circ$   
感应距离: 18m



型号: 22200  
尺寸:  $\varnothing 22$   
焦距: 20mm  
感应角度:  $30^\circ$   
感应距离: 18m




型号: 35202  
尺寸:  $\varnothing 34.7$   
焦距: 20mm  
感应角度:  $60^\circ$   
感应距离: 15m




型号: 22203  
尺寸:  $\varnothing 22$   
焦距: 20mm  
感应角度:  $45^\circ$   
感应距离: 15m




型号: 20280  
尺寸:  $\varnothing 20$   
焦距: 28mm  
感应角度:  $30^\circ$   
感应距离: 18m




型号: 1620  
尺寸:  $\varnothing 16.8$   
焦距: 20mm  
感应角度:  $30^\circ$   
感应距离: 25m



型号: 2220-251  
尺寸:  $\varnothing 22$   
焦距: 24mm  
感应角度:  $50^\circ$   
感应距离: 10m



型号: 2218  
尺寸:  $\varnothing 22$   
焦距: 18mm  
感应角度:  $45^\circ$   
感应距离: 30m



型号: 2224-03  
尺寸:  $\varnothing 21.9$   
焦距: 20mm  
感应角度:  $40^\circ$   
感应距离: 16m



型号: 008140  
尺寸:  $\varnothing 13.2 \times 5.3$   
焦距: 5.5mm  
感应角度:  $140^\circ$   
感应距离: 6m



型号: 008140-G  
尺寸:  $\varnothing 13 \times 10 \times 5.6$   
焦距: 5.5mm  
感应角度:  $110^\circ$   
感应距离: 4.5m



型号: 13120  
尺寸:  $\varnothing 13.5 \times 9.4$   
焦距: 6mm  
感应角度:  $120^\circ$   
感应距离: 4.5-8m



型号: 13120F-2  
尺寸:  $\varnothing 12.5 \times 10.6$   
焦距: 6mm  
感应角度:  $120^\circ$   
感应距离: 6-8m



型号: 13120F  
尺寸:  $\varnothing 13.9 \times 10.4$   
焦距: 6mm  
感应角度:  $120^\circ$   
感应距离: 6-8m



型号: 011050  
尺寸:  $\varnothing 11.8 \times 9.9$   
焦距: 5mm  
感应角度:  $120^\circ$   
感应距离: 6m



型号: 8120-1  
尺寸:  $\varnothing 13.2 \times 7.2$   
焦距: 6mm  
感应角度:  $120^\circ$   
感应距离: 2m



型号: N0803-32  
尺寸:  $\varnothing 15.5 \times 5.7$   
焦距: 6mm  
感应角度:  $120^\circ$   
感应距离: 5m




型号: 8006  
尺寸:  $11 \times 9.3 \times 7.1$   
焦距: 4mm  
感应角度:  $120^\circ$   
感应距离: 4m



型号: 8120-2  
尺寸:  $\varnothing 10.1 \times 9$   
焦距: 5.2mm  
感应角度:  $120^\circ$   
感应距离: 8m



型号: 011050-G  
尺寸:  $\varnothing 11.8 \times 9.9$   
焦距: 5mm  
感应角度:  $120^\circ$   
感应距离: 6m



型号: 8307-2  
尺寸:  $18.7 \times 18.7 \times 4$   
焦距: 12mm  
感应角度:  $70^\circ$   
感应距离: 4m




型号: 023101  
尺寸:  $\varnothing 22.6 \times 11.2$   
感应角度:  $100^\circ$   
感应距离: 10-11m



型号: 8003-2F  
尺寸:  $\varnothing 25.3 \times 12.5$   
焦距: 10.5mm  
感应角度:  $120^\circ$   
感应距离: 12m



型号: 8002-2W  
尺寸:  $23.1 \times 23.1 \times 19$   
焦距: 10.5mm  
感应角度:  $120^\circ$   
感应距离: 12m



型号: 8002-2  
尺寸:  $23.3 \times 23.3 \times 18$   
焦距: 10.5mm  
感应角度:  $110^\circ$   
感应距离: 11m



型号: 8002-1(孔)  
尺寸:  $23.4 \times 23.4 \times 18.9$   
焦距: 10.5mm  
感应角度:  $120^\circ$   
感应距离: 11m



型号: 023100  
尺寸:  $23.5 \times 23.5 \times 18.9$   
焦距: 10.5mm  
感应角度:  $100^\circ$   
感应距离: 10-11m



型号: 024120  
尺寸:  $23.7 \times 23.7 \times 19.2$   
焦距: 12mm  
感应角度:  $120^\circ$   
感应距离: 12m



型号: 028140  
尺寸:  $\varnothing 27.9 \times 14.8$   
焦距: 15mm  
感应角度:  $120^\circ$   
感应距离: 10m





型号: 023100 去腿  
尺寸: 23.5\*23.5\*18.9  
焦距: 10.5mm  
感应角度: 100°  
感应距离: 10-11m




型号: 024120 去腿  
尺寸: 23.7\*23.7\*19.2  
焦距: 12mm  
感应角度: 120°  
感应距离: 12m




型号: 9002-1.7  
尺寸:  $\varnothing 24*20$   
焦距: 12mm  
感应角度: 120°  
感应距离: 9-10m



型号: 8005-1  
尺寸:  $\varnothing 22.9*19.2$   
焦距: 11mm  
感应角度: 120°  
感应距离: 10m



型号: 9002-1  
尺寸:  $\varnothing 23.4*19.1$   
焦距: 12mm  
感应角度: 120°  
感应距离: 9m



型号: NL-02  
尺寸: 23.3\*19  
焦距: 11.6mm  
感应角度: 120°  
感应距离: 10-11m



型号: 8003-1  
尺寸:  $\varnothing 23 * 18.5$   
焦距: 10.5mm  
感应角度: 120°  
感应距离: 11-12m



型号: 8005-2  
尺寸:  $\varnothing 22.8 * 19.6$   
焦距: 11mm  
感应角度: 120°  
感应距离: 10m




型号: 7709-1W  
尺寸:  $\varnothing 20.9*17.4$   
焦距: 7.6mm  
感应角度: 110°  
感应距离: 12m



型号: 7709-2  
尺寸:  $\varnothing 17*9$   
焦距: 5mm  
感应角度: 100-110°  
感应距离: 6m



型号: 7709-1  
尺寸:  $\varnothing 20.7*16.8$   
焦距: 7.6mm  
感应角度: 125°  
感应距离: 8-9m



型号: 8308-7  
尺寸: 12.8\*14  
感应角度: 160°  
感应距离: 11m



型号: 2134-1  
尺寸: 268\*15\*17.1  
焦距: 7.5mm  
感应角度: 120°  
感应距离: 6m



型号: 2136-1  
尺寸: 23.8\*16.3\*13.1  
焦距: 7.5mm  
感应角度: 120°  
感应距离: 6m



型号: 2135-1  
尺寸: 25\*15\*17  
焦距: 7.5mm  
感应角度: 120°  
感应距离: 6m



型号: AL23  
尺寸: 34.5\*20\*10.5  
焦距: 25mm  
感应角度: 水平 120° ,  
垂直 40°  
感应距离: 水平 11m,  
垂直 9m



型号: 8308-6  
尺寸: 13.8\*15.1  
焦距: 9.6mm  
感应角度: 90°  
感应距离: 6-7m



型号: 8308-2  
尺寸:  $\varnothing 11 * 14.6$   
焦距: 6mm  
感应角度: 120°  
感应距离: 6m




型号: 018090  
尺寸:  $\varnothing 17.9 * 13.9$   
焦距: 9mm  
感应角度: 120°  
感应距离: 8m



型号: 023115  
尺寸:  $\varnothing 26 * 17.2$   
焦距: 11.5mm  
感应角度: 120°  
感应距离: 12m



型号: 4/1 球  
尺寸: 52.6\*31\*23.1\*29  
焦距: 30mm  
感应角度: 100°  
感应距离: 10m



型号: 8605-2  
尺寸:  $\varnothing 44.3 * 12.3$   
焦距: 15mm  
感应角度: 120°  
感应距离: 10m



型号: 8102-4  
尺寸:  $\varnothing 42.7 * 4.7$   
焦距: 15mm  
感应角度: 120°  
感应距离: 8m




型号: 8102-2  
尺寸:  $\varnothing 49 * 2.4$   
焦距: 15mm  
感应角度: 360°  
感应距离: 7m




型号: 8605-5  
尺寸:  $\varnothing 45.6 * 12.2$   
焦距: 15mm  
感应角度: 120°  
感应距离: 10m




型号: 8605-1  
尺寸:  $\varnothing 43.5 * 11.5$   
焦距: 15mm  
感应角度: 120°  
感应距离: 10m



型号: 8605-3  
尺寸:  $\varnothing 44.5 * 12.1$   
焦距: 15mm  
感应角度: 100°  
感应距离: 12m



型号: 8603-6  
尺寸:  $\varnothing 44.8 * 11.2$   
焦距: 17.5mm  
感应角度: 120°  
感应距离: 14m




型号: 8603-4  
尺寸:  $\varnothing 45 * 11$   
焦距: 17.5mm  
感应角度: 120°  
感应距离: 14m




型号: 8604-5  
尺寸:  $\varnothing 52.2 * 7.3$   
焦距: 18mm  
感应角度: 360°  
感应距离: 6m





型号: 8603-3  
尺寸:  $\varnothing 45.4 * 11.4$   
焦距: 17.5mm  
感应角度:  $180^\circ$   
感应距离: 10m



型号: 8605-3W  
尺寸:  $\varnothing 43.6 * 11.5$   
焦距: 15mm  
感应角度:  $100^\circ$   
感应距离: 10m



型号: 8605-2B  
尺寸:  $\varnothing 35.7 * 11.5$   
焦距: 15mm  
感应角度:  $115^\circ$   
感应距离: 10m



型号: 8603-4A  
尺寸:  $\varnothing 35 * 10.9$   
焦距: 17.5mm  
感应角度:  $115-120^\circ$   
感应距离: 14m




型号: Q10050  
尺寸:  $\varnothing 100 * 56$   
焦距: 50mm  
感应角度:  $110^\circ$   
感应距离: 12m




型号: 四联探头  
尺寸:  $76.6 * 76.6 * 33.8$   
焦距: 30mm  
感应角度:  $360^\circ$   
感应距离: 10m




型号: Q70  
尺寸:  $\varnothing 70 * 35$   
焦距: 35mm  
感应角度:  $^\circ$   
感应距离: m




型号: 0512H  
尺寸:  $60.3 * 51.5$   
焦距: 31mm  
感应角度:  $120^\circ$   
感应距离: 12m




型号: 7803-1  
尺寸:  $39 * 25$   
焦距: 20mm  
感应角度:  $89^\circ$   
感应距离: 7m



型号: 7805-1  
尺寸:  $56.7 * 35.8$   
焦距: 22mm  
感应角度:  $100^\circ$   
感应距离: 10m



型号: 7809-5  
尺寸:  $43.3 * 24.5$   
焦距: 25mm  
感应角度:  $100^\circ$   
感应距离: 12m




型号: 8719-A  
尺寸:  $53.5 * 31$   
焦距: 25mm  
感应角度:  $100^\circ$   
感应距离: 10-11m




型号: BV-100DP  
尺寸:  $43.2 * 19.7$   
焦距: 30mm  
感应角度:  $80^\circ$   
感应距离: 15m




型号: SIR 650  
尺寸:  $45.8 * 20$   
焦距: 30mm  
感应角度:  $80^\circ$   
感应距离: 15m




型号: 7703-1  
尺寸: 60.6\*42.4  
焦距: 30.5mm  
感应角度: 83 °  
感应距离: 24m




型号: 7809-2  
尺寸: 56.6\*44  
焦距: 25mm  
感应角度: 100°  
感应距离: 12m



型号: SIR-650  
尺寸: 59.5\*38.9  
焦距: 30mm  
感应角度: 120 °  
感应距离: 12m




型号: SIR 650P  
尺寸: 59.4\*38.9  
焦距: 30mm  
感应角度: 120°  
感应距离: 12m




型号: 7708-1  
尺寸: 57\*44.7  
焦距: 29.7mm  
感应角度: 120°  
感应距离: 10m




型号: 7708-3  
尺寸: 58.6\*45.1  
焦距: 29.7mm  
感应角度: 80 °  
感应距离: 14-15m




型号: 7704-3  
尺寸: 56.7\*35.7  
焦距: 23mm  
感应角度: 110°  
感应距离: 12m




型号: 8719  
尺寸: 53.5\*34  
焦距: 25mm  
感应角度: 100 °  
感应距离: 10-11m




型号: 8203-1  
尺寸: 56.4\*43.9  
焦距: 25mm  
感应角度: 110°  
感应距离: 12m



型号: 614230  
尺寸: 60.7\*42.4  
焦距: 30.5mm  
感应角度: 90 °  
感应距离: 12m




型号: 8501-2G  
尺寸: 76\*36  
焦距: 21mm  
感应角度: 120°  
感应距离: 15m



型号: 7707-1A  
尺寸: 91.4\*39.4  
焦距: 25mm  
感应角度: 180°  
感应距离: 16m



型号: 8202  
尺寸: 62.7\*25.1  
焦距: 16mm  
感应角度: 120°  
感应距离: 12m



型号: 7707-5A  
尺寸: 73.7\*26.2  
焦距: 25mm  
感应角度: 120 °  
感应距离: 16m