


REV	LOCAS	DESCRIPTION	DRAW	DATE
01	NEW	INITIAL RELEASE	Junly	2010.08.16
02	△02	ECN20100012	Junly	2010.10.11
03	△03	ECN20110037	Huang	2011.04.26
04	△04	ECN20120040	Huang	2012.09.26

NOTES:

- MATERIAL:
 - Housing:High Temperature Thermoplastic UL94V-0; Color Black.
 - Terminal:Copper Alloy.
 - Nail:Stainless Steel
- SPECIALITY:
 - Rated current:2.0A
 - Rated voltage:30V
 - Contact Resistance:50mΩ MAX
 - Insulation Resistance:100MΩ MIN 100V DC
 - Dielectric withstanding voltage: 100V AC.
 - Solder ability:245±5°C, 5±0.5s.
 - Durability:5000 Cycles Min.
 - Operating condition:Temperature: -30°C~+80°C; Humidity: 80% R.H MAX

Ordering Information



PART No.	DIM A	DIM B	PART No.	DIM A	DIM B
BA0306300450-25	4.50	3.00	BA0307300600-25	6.00	4.50
BA0306300500-25	5.00	3.50	BA0307300620-25	6.20	4.70
BA0306300550-25	5.50	4.00			

QUADRANT POINT (QP)	SHEN ZHEN D-CHAIN TECHNOLOGY CO.,LTD										
TANGENCY POINT (TP)											
INTERSECTION POINT (IP)											
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESING	Huang	DATE	2012.09.26	TITLE:	3PIN BATTERY PH:3.00mm SMT TYPE WITHOUT POST					
X. ±0.25	CHECKED	Andy.L	DATE	2012.09.26	REV:	04	SCALE:	5:1	UNIT:	mm	
X.x ±0.20	APPROVED	Andy.L	DATE	2012.09.26	PART NO:	BA0306300XXX-25		SIZE:	A4	SHEET:	1/1
X.xx ±0.15	DRAWING NO: DQBA0306300450-25										
ANGULAR ±3'											