


REV.	LOCAS.	DESCRIPTION	DRAW.	DATE.
01	NEW	INITIAL RELEASE.	Huang	2010.08.16
04	△04	ECN20120030	Huang	2012.07.13
05	△05	ECN20120035	Huang	2012.08.18
06	△06	ECN20120039	Huang	2012.09.12

NOTES:
 1. MATERIAL:
 1.1 Housing:High Temperature Thermoplastic UL94V-0; Color Black.
 1.2 Terminal:Phosphor Copper.
 1.3 Stator:SUS.
 2. SPECIALITY:
 2.1 Rated current:2.0A
 2.2 Rated voltage:30V
 2.3 Contact Resistance:50mΩ MAX
 2.4 Insulation Resistance:100MΩ MIN 100V DC
 2.5 Dielectric withstanding voltage: 100V AC.
 2.6 Solder ability:245±5℃, 5±0.5s.
 2.7 Durability:5000 Cycles Min.
 2.8 Operating condition:Temperature: -30℃~+80℃; Humidity: 80% R.H MAX

Ordering Information



PART NO	DIM A	DIM B	DIM C
BA0306300500-23	5.00	3.30	4.00
BA0306300600-23	6.00	4.30	5.00
BA0306300620-23	6.20	4.50	5.20
BA0306300650-23	6.50	4.80	5.50

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)	D-CHAIN DONG GUAN D-CHAIN TECHNOLOGY CO.,LTD			
	DESIGN	Huang	DATE	2012.09.12
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3'	CHECKED		DATE	
	APPROVED		DATE	
	PART NO: BA0306300XXX-23		REV: 06	SCALE: 5:1
	DRAWING NO:		SIZE: A4	SHEET: 1/1
			UNIT: mm	