





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



W= With Post

Ordering Information

F 3 P 2 16 3 5 01 1 1056
 产品类型 间距 塑胶高度 排数 单排PIN数 产品形态 塑胶材料 电镀厚度 包装方式 序列号
 F=排母 3=2.54 P=3.55 2=双排 1~40P 3=SMT 5=PA6T 00=常规 1=管装 2=卷装 3=盒装 4=袋装 5=盒装
 01="02-2u" 03="3u"

Dimension antitheses list					
ITEM	PB	PC	PW	H	W
001	3.9		6.6	3.5	5.0
002					

FH-01056

OPERATION

X.X	±0.30
X.XX	±0.20
X.XXX	±0.10
Angle	±3°
DIM	TOL

DRAW

CHECK

APPROVE

SCALE	FIT
UNIT	mm
SIZE	A4
SHEET	1/1
PROJ.	◆

深圳市连盛精密连接器有限公司

PART NO. F3P216350111056

TITLE: 2.54FH H=3.55 W=5.0 2*16P SMT=6.6 总高3.90 U型 AU1U 青铜 PA6T 带柱 ø1.6 H1.5

A0	2018.12.25	NEW DRAWING	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE