

General Description

The 75NF75 is N-Channel MOSFET, It has specifically been designed to minimize input capacitance and gate charge. The device is therefore suitable in advanced high-efficiency switching applications.

Features

- Minimize input capacitance and gate charge
- 100% avalanche tested
- Low On-Resistance


Product Summary

BVDSS	RDSON	ID
80V	9mΩ	80A

Applications

- Motor Control
- DC-DC converters
- Switching applications

TO-220/263 Pin Configuration



Type	Package	Marking
CMP75NF75	TO-220	CMP75NF75
CMB75NF75	TO-263	CMB75NF75

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	80	V
V_{GS}	Gate-Source Voltage	±20	V
$I_D@T_C=25^\circ C$	Continuous Drain Current	80	A
$I_D@T_C=100^\circ C$	Continuous Drain Current	64	A
I_{DM}	Pulsed Drain Current	320	A
EAS	Single Pulse Avalanche Energy ¹	338	mJ
$P_D@T_C=25^\circ C$	Total Power Dissipation	200	W
T_{STG}	Storage Temperature Range	-55 to 175	°C
T_J	Operating Junction Temperature Range	-55 to 175	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient	---	62	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-case	---	0.88	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	80	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V, I_D=30A$	---	---	9	m Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=80V, V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
gfs	Forward Transconductance	$V_{DS}=10V, I_D=15A$	---	19	---	S
R_g	Gate Resistance	$V_{DS}=0V, V_{GS}=0V, f=1\text{MHz}$	---	2.5	---	Ω
Q_g	Total Gate Charge	$I_D=50A$	---	92	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=40V$	---	25	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$	---	31	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=30V, I_D=2A$	---	19	---	ns
T_r	Rise Time	$R_L=15\Omega$	---	13	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=2.5\Omega$	---	55	---	
T_f	Fall Time	$V_{GS}=10V$	---	16	---	
C_{iss}	Input Capacitance	$V_{DS}=25V, V_{GS}=0V, f=1\text{MHz}$	---	5300	---	pF
C_{oss}	Output Capacitance		---	345	---	
C_{rss}	Reverse Transfer Capacitance		---	260	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V, \text{Force Current}$	---	---	80	A
I_{SM}	Pulsed Source Current		---	---	320	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_S=30A, T_J=25^{\circ}\text{C}$	---	0.9	1.4	V

Note :

1.The EAS data shows Max. rating . The test condition is $V_{DD}=30V, V_{GS}=10V, L=1\text{mH}, I_{AS}=26A$

This product has been designed and qualified for the consumer market.

Cmos assumes no liability for customers' product design or applications.

Cmos reserves the right to improve product design , functions and reliability without notice.