




**VOLTAGE RANGE:100 --- 600 V**

**CURRENT: 2.0 A**

**DO - 15**



Dimensions in millimeters

## Features

- ◇ Low cost
- ◇ Low leakage
- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ Easily cleaned with alcohol, Isopropanol and similar solvents
- ◇ The plastic material carries U/Lrecognition 94V-0

## Mechanical Data

- ◇ Case: JEDEC DO--15, molded plastic
- ◇ Terminals: Axial lead ,solderable per MIL- STD-202, Method 208
- ◇ Polarity: Color band denotes cathode
- ◇ Weight: 0.14 ounces, 0.39 grams
- ◇ Mounting position: Any

## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate by 20%.


		ER201	ER202	ER203	ER204	ER206	UNITS
Maximum recurrent peak reverse voltage	$V_{RRM}$	100	200	300	400	600	V
Maximum RMS voltage	$V_{RMS}$	70	140	210	280	420	V
Maximum DC blocking voltage	$V_{DC}$	100	200	300	400	600	V
Maximum average forward rectified current 9.5mm lead length, @ $T_A=75^\circ C$	$I_{F(AV)}$	2.0					A
Peak forward surge current 8.3ms single half-sine-wave superimposed on rated load @ $T_J=125^\circ C$	$I_{FSM}$	50.0					A
Maximum instantaneous forward voltage @ 2.0A	$V_F$	0.95		1.25		1.7	V
Maximum reverse current @ $T_A=25^\circ C$ at rated DC blocking voltage @ $T_A=100^\circ C$	$I_R$	5.0 200.0					$\mu A$
Maximum reverse recovery time (Note 1)	$t_{rr}$	35					ns
Typical junction capacitance (Note 2)	$C_J$	22					pF
Typical thermal resistance (Note 3)	$R_{\theta JA}$	40					$^\circ C/W$
Operating junction temperature range	$T_J$	- 55 ----- + 150					$^\circ C$
Storage temperature range	$T_{STG}$	- 55 ----- + 150					$^\circ C$

NOTE: 1. Measured with  $I_F=0.5A$ ,  $I_R=1A$ ,  $t_{rr}=0.25A$ .


2. Measured at 1.0MHz and applied reverse voltage of 4.0V DC.

3. Thermal resistance junction to ambient.






## Ratings AND Characteristic Curves

**FIG.1 – TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERISTIC**


NOTES:1.RISE TIME = 7ns MAX.INPUT IMPEDANCE = 1MΩ .22pF.  
2.RISE TIME =10ns MAX.SOURCE IMPEDANCE=50 Ω.



SET TIME BASE FOR 10/20 ns/cm

**FIG.2 – TYPICAL FORWARD CHARACTERISTIC**

**FIG.3 – FORWARD DERATING CURVE**

**FIG.4 – TYPICAL JUNCTION CAPACITANCE**

**FIG.5 – PEAK FORWARD SURGE CURRENT**

**FIG.6 – TYPICAL REVERSE CHARACTERISTICS**


PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
DO-15	3000/AMMO	30000	42X28X31	12.00	10.00