




## IGBT

### Features

- Low gate charge
- Trench FS Technology,
- saturation voltage:  $V_{CE(sat)}$ ,  
typ = 1.6V,  $I_C=20A$  and  $T_C = 25^\circ C$
- RoHS product

### Applications

- General purpose inverters
- UPS



### Absolute Ratings ( $T_C=25^\circ C$ )

Parameter	Symbol	Typ	Unit
Collector-Emmitter Voltage	$V_{ces}$	650	V
Collector Current-continuous	$I_C$ $T=25^\circ C$ $T=100^\circ C$	40	A
		20	A
Collector Current-pulse	$I_{CM}$	80	A
Diode RMS forward current	$I_F$ $T=25^\circ C$ $T=100^\circ C$	40	A
		20	A
Gate-Emmitter Voltage	$V_{GES}$	$\pm 20$	V
Turn-off safe area	-	180	A
Surge non repetitive forward current $t_p=10ms$ sinusoidal	$I_{FSM}$	80	A
Power Dissipation (TO-247/TO-263)	$P_D$ $T_C=25^\circ C$	162	W
		(TO-220F)	46
Diode Forward Current	$T_C=100^\circ C$	20	A
Operating and Storage Temperature Range	$T_J, T_{STG}$	-55~+150	$^\circ C$
Maximum Lead Temperature for Soldering Purposes	$T_L$	300	$^\circ C$

\*Collector current limited by maximum Junction temperature

### Thermal Characteristic

Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
Off-Characteristics						
Collector-Emmitter Voltage	$BV_{CES}$	$I_C=500\mu A, V_{GE}=0V$	650	-	-	V







Breakdown Voltage Temperature Coefficient	$\Delta BV_{CES}/\Delta T_J$	$I_C=1\text{mA}$ , reference d to $25^\circ\text{C}$	-	0.5	-	$\text{V}/^\circ\text{C}$
Zero Gate Voltage Collector Current	$I_{CES}$	$V_{CE}=650\text{V}$ , $V_{GE}=0\text{V}$ , $T_C=25^\circ\text{C}$	-		10	$\mu\text{A}$
Gate-body leakage current	$I_{GESF}$	$V_{CE}=0\text{V}$ , $V_{GE}=\pm 20\text{V}$	-	-	200	$\text{nA}$
<b>On-Characteristics</b>						
Gate-Emmitter Threshold Voltage	$V_{GE(th)}$	$V_{CE}=V_{GE}$ , $I_C=250\mu\text{A}$	4.5	-	6.5	V
Collector-Emmitter saturation Voltage	$V_{CESAT}$	$V_{GE}=15\text{V}$ , $I_C=20\text{A}$ , $T_C=25^\circ\text{C}$	-	1.6	2.0	V
		$T_C=125^\circ\text{C}$		1.75	2.15	
		$T_C=175^\circ\text{C}$		1.9	2.3	
Short Collector current	$I_C(sc)$	$V_{GE}=15\text{V}$ $V_{CE}=360\text{V}$ tsc< 10us $T_C=25^\circ\text{C}$		116.7		A
<b>Dynamic Characteristics</b>						
Input capacitance	$C_{ies}$	$V_{CE}=25\text{V}$ ,	-	1500	-	$\text{pF}$
Output capacitance	$C_{oes}$	$V_{GE}=0\text{V}$ ,	-	128	-	$\text{pF}$
Reverse transfer capacitance	$C_{res}$	$f=1.0\text{MHZ}$ , $T_C=25^\circ\text{C}$	-	28.7	-	$\text{pF}$
<b>Switching Characteristics</b>						
Turn-On delay time	$t_d(on)$	$V_{CE}=400\text{V}$ , $I_C=20\text{A}$ , $R_G=10\Omega$ , $V_{GE}=15\text{V}$ $T_C=25^\circ\text{C}$ Inductive Load	-	16	-	ns
Turn-On rise time	$t_r$		-	56	-	ns
Turn-off delay time	$t_d(off)$		-	52	-	ns
Turn-off Fall time	$t_f$		-	82	-	ns
Turn-on energy	$E_{on}$		-	0.79	-	mJ
Turn-off energy	$E_{off}$		-	0.3	-	mJ
Total switching Energy	$E_{total}$		-	1.09	-	mJ
Total Gate Charge	$Q_g$	$V_{CE}=400\text{V}$ , $I_C=20\text{A}$ , $R_G=10\Omega$ , $V_{GE}=15\text{V}$	-	43.9	-	nC
<b>Anti-Paraller Diode Characteristics and Maximum Ratings</b>						
Diode Forward Voltage	$V_F$	$V_{GE}=0\text{V}$ , $I_F=20\text{A}$ , $T_C=25^\circ\text{C}$	-	1.4	-	V
		$V_{GE}=0\text{V}$ , $I_F=20\text{A}$ , $T_C=175^\circ\text{C}$	-	1.0	-	V
Diode Reverse recovery time	$t_{rr}$	$V_{GE}=0\text{V}$ , $I_F=20\text{A}$ $di/dt=100\text{A}/\mu\text{s}$	-	254	-	ns
Reverse recovery	$Q_{rr}$		-	347	-	$\mu\text{C}$







charge					
Diode Reverse recovery Current	Irrm		-	2.7	- A
Parameter	Symbol	Typ		Unit	
		TO-263/TO-247	TO-220F		
IGBT Thermal Resistance, Junction to Case	$R_{th(j-c)}$	0.77		°C/W	
FRD Thermal Resistance, Junction to Case	$R_{th(j-c)}$	2.05		°C/W	
Thermal Resistance, Junction to Ambient	$R_{th(j-A)}$	33.8		°C/W	







### Order information







type	Package
SL20T65FL1	TO-247
SL20T65K1	TO-263
SL20T65F1	TO-220F





## Electrical Characteristics (curves)












### Normalized Maximum Transient Thermal Impedance for IGBT(TO-247)





## Package Mechanical DATA

