



E-NETTR 100/1000Base-T Transformer Module

P/N: H2415G

- * Designed to meet IEEE802.3bt requirement
- * Designed to meet IR255°C peak requirement
- * Power over Ethernet (POE) Magnetics, 1.5A current capability
- * Primary inductance 350uH Min with 25mA DC Bias
- * Operating temperature range: -40°C to +85°C
- * Storage temperature range: -40°C to +85°C




Electrical Specifications @ 25° C

Part Number	Turn Ratio (±3%)	OCL(uH Min) @ 100KHz/0.1V with 25mA DC Bias	OCL(uH Min) @ 100KHz/0.1V/ with 35mA DC Bias	L.L (uH Max)	C _{w/w} (pF Max)	DCR (Ω Max)	Hi-Pot (Vrms MIN)
H2415G	1CT:1CT	350	135	0.35	28	1.1	AC 1500/1mA/1S


Continue

Part Number	Insertion Loss 0.3~100MHZ (dB Max)	Return Loss (dB Min)					Cross Talk (dB Min)			DCMR (dB Min)		
		0.3-30MH	40MHz	50MHz	60-80MHz	100MHz	30MHz	60MHz	100MHz	30MHz	60MHz	100MHz
H2415G	-1.1	-14.5	-12.5	-10.5	-7	-5	-33	-28	-25	-35	-30	-27

Mechanical



Schematics



东莞市祥星电子有限公司

地址: 东莞市石碣镇横滘科技中路第三工业区 Miss yang: 13694998066 Mr Li: 15013501940

TEL: 0769-86384669

FAX: 0769-81813600

Http://www.e-nettr.com

xingguang@e-nettr.com