


Pin strip

971-SLR

Soldering area \varnothing 1 mm; plug-in area \varnothing 1,3 mm



$$L1 = (\text{number of poles} - 1) \times \text{pitch}$$

Part Numbers

No. of poles	971-SLR	Length	Pcs
2	12.893.811	9,50	1.000
3	13.893.811	14,50	500
4	14.893.811	19,50	500
5	15.893.811	24,50	250
6	16.893.811	29,50	250
7	17.893.811	34,50	250
8	18.893.811	39,50	250
9	19.893.811	44,50	250
10	20.893.811	49,50	100
11	21.893.811	54,50	100
12	22.893.811	59,50	100

further number of poles on request

General Information

Pitch	5 mm
No. of poles	2 - 12
Usable with	plug connector of series 115-F, 950-FL-DS, 950-TFL-DS, 950-NAF-DS, 950-GFL-DS, 950-NLFL-DS, 950-RFL-DS
Additional Information	Pin strip is suitable for reflow soldering



Technical Data

Overvoltage Category	III	III	II
Pollution Severity Level	3	2	2
Rated Voltage	250 V	320 V	630 V
Rated Impulse Voltage	4 kV	4 kV	4 kV
Rated Insulation Voltage	250 V acc. to EN 60998-1		
Rated Current	10 A		
Soldering process	Wave solder & reflow solder		
Hole in PCB	\varnothing 1,3 mm		
PCB thickness	Wave solder max. 1,6 mm; reflow solder 1,6 - 3,2 mm		

Material

Moulding	PA HT, black, V-0
Comparative Tracking Index	CTI \geq 600
Insulating Group	I
Temperature Range	-40°C up to 150°C; reflow solder temperature (Peak) max. 260°C (15-30 s)
Solder pin	\varnothing 1,3 mm (plug-in area) / \varnothing 1,0 mm (soldering area); tin plated brass

Approvals

	Current	Voltage	Group	AWG	Nm
	10 [1]	300	B		
	10 [1]	300	B		

[1] By using 115-F current of 12 A possible

Options / Accessories

- Other plug pin lengths on request
- Other P.C. pin surfaces on request