

1.8V to 7.0V, 5MHz, RRIO **Low Power Operational Amplifiers**

Features

Operates on 1.8V ~ 7V Supplies

Input Offset voltage: $\pm 2mV(max)$

Low Quiescent Current: 280µA

Gain Bandwidth Product: 5MHz

Slew Rate: 4.5V/µs

Rail-to-Rail Input and Output (RRIO)

Unity Gain Stable

No Phase Reversal

Extended Temperature Ranges From -40°C to +125°C

Small Packaging COS9051 available in SOT23-5 COS9051S available in SOT23-6 COS9052 available in SOP8/MSOP8 COS9052S available in MSOP10 COS9054 available in SOP14/TSSOP14

Applications

- Battery or Solar Powered Systems
- Portable Equipment
- Sensor Conditioning
- **Analog Active Filters**
- White Goods
- Smoke/Gas/Environment Sensors

Rev1.0 Copyright@2018 Cosine Nanoelectronics Inc. All rights reserved The information provided here is believed to be accurate and reliable. Cosine Nanoelectronics assumes no reliability for inaccuracies and omissions. Specifications described and contained here are subjected to change without notice on the purpose of improving the design and performance. All of this information described herein should not be implied or granted for any third party.

General Description

The COS9051 (single), COS9052 (dual) and COS9054 (quad) are micro-power, rail-to-rail input and output amplifiers operated on 1.8V to 7V supplies. Despite their low quiescent current, the COS905x family provides excellent overall performance and versatility. They have both rail-to-rail input and output range. The output voltage swing extends to within 10mV of each rail, providing the maximum output dynamic range with excellent overdrive recovery.


COS905x family is unity gain stable and has a gain bandwidth product of 1.5MHz (typical). They provide high CMRR and PRSS performance and can operate from a single supply voltage as low as 1.8V.

The COS905xS devices include a shutdown mode (COS9051S, and COS9052S) that allow the amplifiers to switch off into standby mode with typical current consumption less than 5 μA. These features make the COS905x family well suited for single-supply, battery-powered applications. They can be used as plus-in replacements for many commercially available op-amps to reduce power and improve input/output range and performance.

1



1. Pin Configuration and Functions



Pin Functions

Name	Description	Note
+Vs	Positive power supply	A bypass capacitor of 0.1µF as close to the part as possible should be placed between power supply pins or between supply pins and ground.
-Vs	Negative power supply or ground	If it is not connected to ground, bypass it with a capacitor of 0.1µF as close to the part as possible.
-IN	Negative input	Inverting input of the amplifier. Voltage range of this pin can go from -Vs -0.3V to +Vs + 0.3V.
+IN	Positive input	Non-inverting input of the amplifier. This pin has the same voltage range as –IN.
OUT	Output	The output voltage range extends to within millivolts of each supply rail.
SHDN	Shutdown	High: enable op-amp; Low: disable op-amp



2. Product Specification

2.1 Absolute Maximum Ratings (1)

Parameter	Rating	Units
Power Supply: +Vs to -Vs	7.5	\ \
Input Voltage	-Vs -0.5V to +Vs + 0.5V	\ \
Input Current (2)	10	mA
Storage Temperature Range	-65 to 150	°C
Junction Temperature	150	°C
Operating Temperature Range	-40 to 125	°C
ESD Susceptibility, HBM	2000	V

⁽¹⁾ Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

2.2 Thermal Data

Parameter	Rating	Unit
Package Thermal Resistance	190 (SOT23-5) 206 (MSOP8) 155 (SOP8) 105 (TSSOP14) 82 (SOP14)	°C/W

2.3 Recommended Operating Conditions

Parameter	Rating	Unit
DC Supply Voltage	1.8V ~ 7V	V
Input common-mode voltage range	-Vs ~ +Vs	V
Operating ambient temperature	-40 to +85	°C

⁽²⁾ Input terminals are diode-clamped to the power-supply rails. Input signals that can swing more than 0.5V beyond the supply rails should be current-limited to 10mA or less.



2.4 Electrical Characteristics

(+Vs=+5V, -Vs=0, VcM=Vs/2, TA=+25°C, RL=10k Ω to Vs/2, unless otherwise noted)

$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	±2 ±5 μV/°0
Input Offset Voltage Vos COS905xB : Input Offset Voltage Drift $\Delta Vos/\Delta T$ -40 to 125°C ±0.6 Input Bias Current IB ±2.5 Input Offset Current Ios ±2.5 Common-Mode Voltage Range V _{CM} V _S = 5.5V -0.1 5 Common-Mode Rejection Ratio CMRR V _{CM} = 0.1V to 4.9V 125 Open-Loop Voltage Gain AOL V _O =0.2V to 4.8V 120 Output Characteristics Output Voltage Swing from Rail R _L =100kΩ 1 R _L =2kΩ 40 Short-Circuit Current I _{SR} Sourcing 21 I _{SK} Sinking 22 Power Supply Operating Voltage Range I _S 7 Power Supply Rejection Ratio PSRR V _S = +1.8V to +5.5V 80 100	mV ±5 μV/°C
Input Offset Voltage Drift ΔVos/ΔT -40 to 125°C ±0.6 Input Bias Current IB ±2.5 Input Offset Current Ios ±2.5 Common-Mode Voltage Range V _{CM} V _S = 5.5V -0.1 5 Common-Mode Rejection Ratio CMRR V _{CM} =0.1V to 4.9V 125 120 Open-Loop Voltage Gain AOL V _O =0.2V to 4.8V 120 120 Output Characteristics R _L =100kΩ 1	±5 µV/°(
	+ -
$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	А
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	pA
	pA
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	5.6 V
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	dB
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	dB
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	
$R_L = 2k\Omega \qquad \qquad 40$ $Short-Circuit Current \qquad I_{SR} \qquad Sourcing \qquad \qquad 21$ $I_{SK} \qquad Sinking \qquad \qquad 22$ $Power Supply$ $Operating Voltage Range \qquad \qquad 1.8 \qquad \qquad 7$ $Power Supply Rejection Ratio \qquad PSRR \qquad V_S = +1.8V \text{ to } +5.5V \qquad 80 \qquad 100$ $I_O = 0 \text{ mA} \qquad \qquad 280$	mV
Isr Sourcing 21	mV
Short-Circuit Current Isk Sinking 22 Power Supply Operating Voltage Range 1.8 7 Power Supply Rejection Ratio PSRR Vs = +1.8V to +5.5V 80 100 Io = 0 mA 280	mV
IskSinking22Power SupplyOperating Voltage Range1.87Power Supply Rejection RatioPSRR $V_S = +1.8V$ to $+5.5V$ 80100 $I_O = 0$ mA280	mA
Operating Voltage Range 1.8 7 Power Supply Rejection Ratio PSRR $V_S = +1.8V$ to $+5.5V$ 80 100 $I_O = 0$ mA 280	mA
Power Supply Rejection Ratio PSRR $V_S = +1.8V$ to $+5.5V$ 80 100 $I_O = 0$ mA 280	
I _O = 0 mA 280	7.0 V
	dB
Quiescent Current / Ampliner IQ	μА
	5 μΑ
Dynamic Performance	
Gain Bandwidth Product GBWP G=+1 5	MHz
Slew Rate SR G = +1, 2V Output Step 4.5	V/µs
Noise Performance	•
Voltage Noise Density e _n f=1kHz 25	nV/√ŀ



3.0 Application Notes

Driving Capacitive Loads

Driving large capacitive loads can cause stability problems for voltage feedback op amps. As the load capacitance increases, the feedback loop's phase margin decreases, and the closed loop bandwidth is reduced. This produces gain peaking in the frequency response, with overshoot and ringing in the step response. A unity gain buffer (G = +1) is the most sensitive to capacitive loads, but all gains show the same general behavior.

When driving large capacitive loads with these op amps (e.g., > 100 pF when G = +1), a small series resistor at the output (R_{ISO} in Figure 1) improves the feedback loop's phase margin (stability) by making the output load resistive at higher frequencies. It does not, however, improve the bandwidth.

To select R_{ISO} , check the frequency response peaking (or step response overshoot) on the bench. If the response is reasonable, you do not need R_{ISO} . Otherwise, start R_{ISO} at 1 k Ω and modify its value until the response is reasonable.




Figure 1. Indirectly Driving Heavy Capacitive Load

An improvement circuit is shown in Figure 2. It provides DC accuracy as well as AC stability. R_F provides the DC accuracy by connecting the inverting signal with the output, C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving phase margin in the overall feedback loop.




Figure 2. Indirectly Driving Heavy Capacitive Load with DC Accuracy



For noninverting configuration, there are two others ways to increase the phase margin: (a) by increasing the amplifier's gain or (b) by placing a capacitor in parallel with the feedback resistor to counteract the parasitic capacitance associated with inverting node, as shown in Figure 3.




Figure 3. Adding a Feedback Capacitor in the Noninverting Configuration

Power-Supply Bypassing and Layout

The COS9051/2/4 operates from a single +1.8V to +5.5V supply or dual $\pm 0.9V$ to $\pm 2.75V$ supplies. For single-supply operation, bypass the power supply +Vs with a $0.1\mu F$ ceramic capacitor which should be placed close to the +Vs pin. For dual-supply operation, both the +Vs and the -Vs supplies should be bypassed to ground with separate $0.1\mu F$ ceramic capacitors. $2.2\mu F$ tantalum capacitor can be added for better performance.

The length of the current path is directly proportional to the magnitude of parasitic inductances and thus the high frequency impedance of the path. High speed currents in an inductive ground return create an unwanted voltage noise. Broad ground plane areas will reduce the parasitic inductance. Thus a ground plane layer is important for high speed circuit design.

Typical Application Circuits

Differential Amplifier

The circuit shown in Figure 4 performs the differential function. If the resistors ratios are equal $(R_4 / R_3 = R_2 / R_1)$, then $V_{OUT} = (V_{IP} - V_{IN}) \times R_2 / R_1 + V_{REF}$.






Figure 4. Differential Amplifier

Low Pass Active Filter

When receiving low-level signals, limiting the bandwidth of the incoming signals into the system is often required. The simplest way to establish this limited bandwidth is to place an RC filter at the noninverting terminal of the amplifier. If even more attenuation is needed, a multiple pole filter is required. The Sallen-Key filter can be used for this task, as Figure 5. For best results, the amplifier should have a bandwidth that is 8 to 10 times the filter frequency bandwidth. Failure to follow this guideline can result in reduction of phase margin. The large values of feedback resistors can couple with parasitic capacitance and cause undesired effects such as ringing or oscillation in high-speed amplifiers. Keep resistors value as low as possible and consistent with output loading consideration.





Figure 5. Two-Pole Low-Pass Sallen-Key Active Filter




4. Package Information

4.1 SOT23-5 (Package Outline Dimensions)



Symbol	100000000000000000000000000000000000000	nsions imeters	Dimensions In Inches	
	Min	Max	Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.400	0.012	0.016
С	0.100	0.200	0.004 0.008	
D	2.820	3.020	0.111 0.119	
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
Ŀ	0.700REF		0.028	BREF
L1	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°


4.2 SOP8 (Package Outline Dimensions)



Symbol		nsions meters	Dimensions In Inches	
	Min	Max	Min	Max
Α	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
В	0.330	0.510	0.013	0.020
С	0.190	0.250	0.007	0.010
D	4.780	5.000	0.188	0.197
E	3.800	4.000	0.150	0.157
E1	5.800	6.300	0.228	0.248
е	1.270TYP		0.050	TYP
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°





4.3 MSOP8 (Package Outline Dimensions)



Symbol		nsions meters	Dimensions In Inches		
-	Min	Max	Min	Max	
Α	0.800	1.200	0.031	0.047	
A1	0.000	0.200	0.000	0.008	
A2	0.760	0.970	0.030	0.038	
b	0.30 TYP		0.012 TYP		
С	0.15	0.15 TYP		TYP	
D	2.900	3.100	0.114	0.122	
е	0.65	TYP	0.026	TYP	
E	2.900	3.100	0.114	0.122	
E1	4.700	5.100	0.185	0.201	
L	0.410	0.650	0.016	0.026	
θ	0° 6°		0°	6°	

4.4 SOP14 (Package Outline Dimensions)






Symbol	Dimensions In Millimeters				
	MIN	NOM	MAX		
Α	1.35	1.60	1.75		
A1	0.10	0.15	0.25		
A2	1.25	1.45	1.65		
A3	0.55	0.65	0.75		
b	0.36		0.49		
b1	0.35	0.40	0.45		
С	0.16		0.25		
c1	0.15	0.20	0.25		
D	8.53	8.63	8.73		
E	5.80	6.00	6.20		
E1	3.80	3.90	4.00		
е		1.27 BS0	2		
L	0.45	0.60	0.80		
L1		1.04 REI			
L2		0.25 BS0	0		
R	0.07				
R1	0.07				
h	0.30	0.40	0.50		
θ	0°		8°		
θ1	6°	8°	10°		
θ2	6°	8°	10°		
θ3	5°	7°	9°		
θ4	5°	7°	9°		



4.5 TSSOP14 (Package Outline Dimensions)



Symbol	Dimensions In Millimeters			
	MIN	NOM	MAX	
Α		_	1.20	
A1	0.05	1 1	0.15	
A2	0.90	1.00	1.05	
A3	0.34	0.44	0.54	
b	0.20	_	0.28	
b1	0.20	0.22	0.24	
С	0.10	i .	0.19	
c1	0.10	0.13	0.15	
D	4.86	4.96	5.06	
E	6.20	6.40	6.60	
E1	4.30	4.40	4.50	
е		0.65 BSC		
L	0.45	0.60	0.75	
L1		1.00 REF		
L2		0.25 BSC		
R	0.09 —		_	
R1	0.09	-		
S	0.20	<u> </u>		
01	0°		8°	
θ2	10°	12°	14°	
θ3	10° 12° 14°			

5. Order Information

Model	Channel	Order Number	Package	Package Option	Marking Information
0000054		COS9051TR	SOT23-5	Tape and Reel, 3000	C9051
COS9051	1	COS9051TRU	SOT23-5	Tape and Reel, 3000	C9051U
COC0051C	l I	COS9051STR	SOT23-6	Tape and Reel, 3000	C9051S
COS9051S		COS9051STRU	SOT23-6	Tape and Reel, 3000	C9051SU
COS9052	0	COS9052SR	SOP-8	Tape and Reel, 3000	COS9052
		COS9052MR	MSOP-8	Tape and Reel, 3000	COS9052
COS9052S	2	COS9052SMRA	MSOP-10	Tape and Reel, 3000	COS9052S
		COS9052SMRB	MSOP-10	Tape and Reel, 3000	COS9052S
COS9054	4	COS9054SR	SOP-14	Tape and Reel, 3000	COS9054
		COS9054TR	TSSOP-14	Tape and Reel, 3000	COS9054