

# 1553C6

# OSCILLATOR UNIT WITH HCSL OUTPUT IN SMD 5.0x3.2MM CERAMIC SEAM SEAL PACKAGE.


#### PRODUCT FEATURES

- Small dimensions 5.0x3.2x1.3 with 6 solder pads.
- Highly reliable seam sealed ceramic package.
- Wide frequency range.
- Low jitter and phase noise.
- ROHS compliant, LEAD-FREE and HALOGEN-FREE.

#### **APPLICATIONS**

- High speed communication
- Telecom equipment
- Handheld equipment

#### PRODUCT PHOTO (NOT IN SCALE)




#### PRODUCT SPECIFICATIONS

PARAMETER	1553C6	CONDITIONS / REMARKS
Nominal frequency range	10 ~ 220MHz	Fund., Overtone or PLL
Supply voltage	2.5V <sub>DC</sub> / 3.3V <sub>DC</sub>	Other option possible
Supply current	40mA	Maximum, Fund mode lower Icc
Frequency stability	±25ppm / ±50ppm / ±100ppm	See note below.
Operating temperature range	-10 to +70°C or -40 to 85°C	Other options available.
Output waveform and load	HCSL / 50Ω	RL to Ground on each output
Output voltage level HIGH	0.74V	Typical
Output voltage level LOW	0v	Typical
Rise and Fall times	0.5ns	@ 20~80~20%V <sub>cc</sub>
Symmetry (duty cycle)	45~55%	@ outputs cross point
Phase Jitter RMS	<1ps	Integrated 12kHz≤F <sub>j</sub> ≤20MHz

Note: Stability includes frequency deviations at  $+25^{\circ}$ C, over temperature range, due to supply voltage changes, output load changes, shock and vibration.

### PACKAGE OUTLINE / DIMENSIONS



## PACKAGING INFORMATION

- Tape & Reel compliant to EIA-481.
- Embossed carrier width 12mm.
- Component pitch in carrier 8mm.
- Reel diameter 180mm.
- QTY per reel: 1,000pcs

#### RECOMMENDED REFLOW PROFILE

