
ALMD-EL3D, ALMD-EG3D, ALMD-CM3D, ALMD-CB3D

High Brightness SMT Round LED Lamps Amber, Red, Green and Blue Tinted LEDs



Data Sheet





Description


The new Avago ALMD-xx3D LED series has the same or just slightly less luminous intensity than conventional high brightness, through-hole LEDs.

The new LED lamps can be assembled using common SMT assembly processes and are compatible with industrial reflow soldering processes.

The LEDs are made with an advanced optical grade epoxy for superior performance in outdoor sign applications.

For easy pick and place assembly, the LEDs are shipped in EIA-compliant tape and reel. Every reel is shipped from a single intensity and color bin– except the red color–for better uniformity.

Package Dimensions





Features

- Compact form factor
- High brightness material
- Available in Red, Amber, Green and Blue color
- Red AllnGaP 626 nm
- Amber AllnGaP 590 nm
- Green InGaN 525 nm
- Blue InGaN 470 nm
- JEDEC MSL 2A
- Compatible with industrial reflow soldering process
- Typical Viewing angle: 30°
- Tinted, non-diffused

Applications

Variable Message Signs





Notes:

- 1. All dimensions in millimeters (inches).
- 2. Tolerance is \pm 0.20 mm unless other specified.

CAUTION: In GaN devices are Class 1C HBM ESD sensitive, All nGaP devices are Class 1B ESD sensitive per JEDEC Standard. Please observe appropriate precautions during handling and processing. Refer to Application Note AN-1142 for additional details.

CAUTION: Customer is advised to keep the LED in the MBB when not in use as prolonged exposure to environment might cause the silver plated leads to tarnish, which might cause difficulties in soldering.


Device Selection Guide

Part Number	Color and Dominant Wavelength	Luminous Into	Viewing Angle	
	$\lambda_{ m d}$ (nm) Typ $^{[3]}$	Min	Max	Typ (°) ^[4]
ALMD-EG3D-VX002	Red 626	4200	9300	30°
ALMD-EL3D-VX002	Amber 590	4200	9300	
ALMD-CM3D-XZ002	Green 525	7200	16000	
ALMD-CB3D-SU002	Blue 470	1900	4200	

Notes:

- 1. The luminous intensity is measured on the mechanical axis of the lamp package and it is tested with pulsing condition.
- 2. The optical axis is closely aligned with the package mechanical axis.
- 3. Dominant wavelength, $\hat{\lambda}d$, is derived from the CIE Chromaticity Diagram and represents the color of the lamp.
- 4. θ ½ is the off-axis angle where the luminous intensity is half the on-axis intensity.
- 5. Tolerance for each bin limit is \pm 15%

Part Numbering System



Absolute Maximum Rating, $T_J = 25$ °C

Parameter	Red and Amber	Blue and Green	Unit
DC Forward Current [1]	50	50 30	
Peak Forward Current	100 [2]	100 [3]	mA
Power Dissipation	120	120 114	
Reverse Voltage	5 (I _R = 100 μA) ^[4]	5 ($I_R = 100 \mu\text{A}$) [4] 5 ($I_R = 10 \mu\text{A}$) [4]	
LED Junction Temperature	11	110	
Operating Temperature Range	-40 to	°C	
Storage Temperature Range	-40 to	-40 to +100	

Notes:

- 1. Derate linearly as shown in Figure 4 and Figure 9.
- 2. Duty Factor 30%, frequency 1 kHz.
- 3. Duty Factor 10%, frequency 1 kHz.
- 4. Indicates product final testing; long-term reverse bias is not recommended.

Electrical / Optical Characteristics, $T_J = 25$ °C

Parameter	Symbol	Min.	Тур.	Max.	Units	Test Conditions
Forward Voltage	V _F				V	I _F = 20 mA
Red		1.8	2.1	2.4		
Amber		1.8	2.1	2.4		
Green		2.8	3.2	3.8		
Blue		2.8	3.2	3.8		
Reverse Voltage	V _R					
Red & Amber		5			V	$I_F = 100 \mu A$
Green & Blue		5				$I_F = 10 \mu\text{A}$
Dominant Wavelength [1]	$\lambda_{\sf d}$					I _F = 20 mA
Red	-	618.0	626.0	630.0		
Amber		584.5	590.0	594.5		
Green		519.0	525.0	539.0		
Blue		460.0	470.0	480.0		
Peak Wavelength						
Red	λ_{PEAK}		634		nm	Peak of Wavelength of Spectral
Amber	,		594			Distribution at $I_F = 20 \text{ mA}$
Green			516			
Blue			464			
Thermal Resistance	Rθ _{J-PIN}		130		°C/W	LED Junction-to-Pin
Luminous Efficacy [2]						
Red	ηγ		200		lm/W	Emitted Luminous Power/Emitted
Amber	-14		520		,	Radiant Power
Green			530			
Blue			65			
Thermal coefficient of λ _d					nm/°C	$I_F = 20 \text{ mA}$; $+25 ^{\circ}\text{C} \le T_J \le +100 ^{\circ}\text{C}$
Red			0.059			-
Amber			0.103			
Green			0.028			
Blue			0.024			

Notes:

- 1. The dominant wavelength is derived from the chromaticity diagram and represents the color of the lamp.
- 2. The radiant intensity, l_e in watts per steradian, may be found from the equation $l_e = l_V/\eta_V$ where l_V is the luminous intensity in candelas and η_V is the luminous efficacy in lumens/watt.

AllnGaP




Figure 1. Relative Intensity vs Wavelength




Figure 3. Relative Intensity vs Forward Current




Figure 5. Relative Dominant Wavelength Shift vs Forward Current





Figure 2. Forward Current vs Forward Voltage



Note: $R\theta_{J-A} = 460 \, ^{\circ}\text{C/W}$

Figure 4. Maximum Forward Current vs Ambient Temperature

InGaN




Figure 6. Relative Intensity vs Wavelength




Figure 7. Forward Current vs Forward Voltage

100




Figure 8. Relative Intensity vs Forward Current




Figure 9. Maximum Forward Current vs Ambient Temperature




Figure 10. Dominant Wavelength Shift vs Forward Current




Figure 11a. Radiation Pattern for X axis




Figure 12. Relative Intensity Shift vs Junction Temperature

10

T_J - JUNCTION TEMPERATURE

35

60

85

-15




Figure 11b. Component Axis for Radiation Pattern




Figure 13. Forward Voltage Shift vs Junction Temperature

0.1

-40






Figure 14. Recommended Soldering Land Pattern



Note:

- 1. Nozzle depth should be touching LED flange during pick and place.
- 2. Nozzle width should be able to fit into LED carrier tape

Figure 15. Recommended Pick and Place Nozzle Tip (Urethane PAD Tip)








Figure 17. Recommended Pb- Free Reflow Soldering Profile

Note: For detailed information on reflow soldering of Avago Surface Mount LED, refer to Avago Application Note AN1060 Surface Mounting SMT LED Indicator Components.




Figure 18. Carrier Tape Dimension




Figure 19. Reel Dimension




Figure 20. Unit Orientation from reel

Intensity Bin Limit Table (1.3:1 lv bin ratio)

	Intensity (mcd) at 20 mA				
Bin	Min	Max			
S	1900	2500			
Т	2500	3200			
U	3200	4200			
V	4200	5500			
W	5500	7200			
Χ	7200	9300			
Υ	9300	12000			
Z	12000	16000			

Tolerance for each bin limit is \pm 15%

VF Bin Table (V at 20 mA) for Red&Amber

Bin ID	Min	Max	
VD	1.8	2.0	
VA	2.0	2.2	
VB	2.2	2.4	

Tolerance for each bin limit is ± 0.05 V

Red Color Range

Min Dom	Max Dom	X min	Y Min	X max	Y max	
618.0	630.0	0.6872	0.3126	0.6890	0.2943	
		0.6690	0.3149	0.7080	0.2920	

Tolerance for each bin limit is ± 0.5 nm

Amber Color Range

Bin	Min Dom	Max Dom	Xmin	Ymin	Xmax	Ymax
1	584.5	587.0	0.5420	0.4580	0.5530	0.4400
			0.5370	0.4550	0.5570	0.4420
2	587.0	589.5	0.5570	0.4420	0.5670	0.4250
			0.5530	0.4400	0.5720	0.4270
4	589.5	592.0	0.5720	0.4270	0.5820	0.4110
			0.5670	0.4250	0.5870	0.4130
6	592.0	594.5	0.5870	0.4130	0.5950	0.3980
			0.5820	0.4110	0.6000	0.3990

Tolerance for each bin limit is ± 0.5 nm

Green Color Range

Bin	Min Dom	Max Dom	Xmin	Ymin	Хтах	Ymax
1	519.0	523.0	0.0667	0.8323	0.1450	0.7319
			0.1200	0.7375	0.0979	0.8316
2	523.0	527.0	0.0979	0.8316	0.1711	0.7218
			0.1450	0.7319	0.1305	0.8189
3	527.0	531.0	0.1305	0.8189	0.1967	0.7077
			0.1711	0.7218	0.1625	0.8012
4	531.0	535.0	0.1625	0.8012	0.2210	0.6920
			0.1967	0.7077	0.1929	0.7816
5	535.0	539.0	0.1929	0.7816	0.2445	0.6747
			0.2210	0.6920	0.2233	0.7600

Tolerance for each bin limit is $\pm 0.5 \text{nm}$

Blue Color Range

Bin	Min Dom	Max Dom	Xmin	Ymin	Xmax	Ymax
1	460.0	464.0	0.1440	0.0297	0.1766	0.0966
			0.1818	0.0904	0.1374	0.0374
2	464.0	468.0	0.1374	0.0374	0.1699	0.1062
			0.1766	0.0966	0.1291	0.0495
3	468.0	472.0	0.1291	0.0495	0.1616	0.1209
			0.1699	0.1062	0.1187	0.0671
4	472.0	476.0	0.1187	0.0671	0.1517	0.1423
			0.1616	0.1209	0.1063	0.0945
5	476.0	480.0	0.1063	0.0945	0.1397	0.1728
			0.1517	0.1423	0.0913	0.1327

Tolerance for each bin limit is \pm 0.5nm

Moisture Sensitivity and Handling

The ALMD-xx3D series oval package has a Moisture Sensitive Level 2a rating per JEDEC J-STD-020. Refer to Avago Application Note AN5305, Handling of Moisture Sensitive Surface Mount Devices, for additional details and a review of proper handling procedures.

A. Storage before use

- An unopened moisture barrier bag (MBB) can be stored at < 40° C/90% RH for 12 months. If the actual shelf life has exceeded 12 months and the humidity indicator card (HIC) indicates that baking is not required then it is safe to reflow solder the LEDs per the original MSL rating.
- It is recommended that the MBB not be opened prior to assembly (e.g. for IQC).

B. Control after opening the MBB

- The humidity indicator card (HIC) shall be read immediately upon opening of the MBB.
- The LEDs must be kept at < 30° C/60% RH at all times, and all high temperature related processes including soldering, curing or rework need to be completed within 672 hours.

C. Control for unfinished tape and reel parts

 Unused LEDs must be stored in a sealed MBB with a desiccant or desiccator at < 5% RH.

D. Control of assembled boards

 If the PCB soldered with the LEDs is to be subjected to other high temperature processes, the PCB needs to be stored in a sealed MBB with desiccant or desiccator at < 5% RH to ensure that all LEDs have not exceeded their floor life of 672 hours

E. Baking is required if:

- The HIC indicator is not BROWN at 10% and is AZURE at 5%
- The LEDs are exposed to a condition of > 30° C/60% RH at any time.
- The LED floor life exceeded 672 hours.

The recommended baking condition is: $60 \pm 5^{\circ}$ C for 20 hours.

DISCLAIMER: Avago's products and software are not specifically designed, manufactured or authorized for sale as parts, components or assemblies for the planning, construction, maintenenace or direct operation of a nuclear facility or for use in medical devices or applications. Customer is solely responsible, and waives all rights to make claims against avago or its suppliers, for all loss, damage, expense or liability in connection with such use.

