

NOTES:

1.MATERIAL:




- 1.1 HOUSING: HIGH TEMPERATURE RESISTANT PLASTIC, UL94 V-0.
- 1.2 CONTACTS: COPPER ALLOY
- 1.3 SHELL: STAINLESS STEEL

2.SPECIALITY:




- 2.1 RATED CURRENT: 5A
- 2.2 RATED VOLTAGE: 10V
- 2.3 CONTACT RESISTANCE: 50m OHMS MAX.
- 2.4 INSULATION RESISTANCE: 100M OHMS MIN 100V DC
- 2.5 DURABILITY: 3000 CYCLES.
- 2.8 OPERATING CONDITION: TEMPERATURE -30°C~+80°C.
HUMIDITY 80% R.H MAX

3.IR REFLOW:

THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.



061N-4BVS33-WX



1:L=6.8
2:L=6.5

L	L = 6.8
L	L = 6.5

—		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	061N-4BVS33-WX	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.2
			MODEL NAME	061N-4BVS33-WX		X.x ±0.21
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.11
					ANGULAIR	±3
					FILE NO.	