


Features

- Low gate charge
- Trench FS Technology,
- saturation voltage: $V_{CE(sat)}$,
type = 1.6V, $I_C=50A$ and $T_C = 25^\circ C$
- RoHS product



Applications

- General purpose inverters
- UPS



Absolute Ratings ($T_c=25^\circ C$)

Parameter	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CES}	650	V
*Collector Current-continuous	$I_C \quad T=25^\circ C$	100	A
	$T=100^\circ C$	50	A
Collector Current-pulse(note 1)	I_{CM}	200	A
Diode RMS forward current	$I_F \quad T=25^\circ C$	50	A
	$T=100^\circ C$	25	A
Gate-Emitter Voltage	V_{GES}	± 30	V
Power Dissipation	$P_D \quad T_c=25^\circ C$	368	W
Operating Temperature Range	T_J	-55~175	°C
Storage Temperature Range	T_{STG}	-55~+175	°C
Maximum Lead Temperature for Soldering Purposes	T_L	300	°C

*Collector current limited by maximum Junction temperature

Thermal Characteristic

Parameter	Symbol	Tests conditions	Min	Typ	Max	Units
Off-Characteristics						
Collector-Emitter Voltage	BV_{CES}	$I_C=250\mu A, V_{GE}=0V$	650	-	-	V
Breakdown Voltage Temperature Coefficient	$\Delta BV_{CES}/\Delta T_J$	$I_C=0.5mA$, referenced to $25^\circ C$	-	0.6	-	V/°C
Zero Gate Voltage Collector Current	I_{CES}	$V_{CE}=650V, V_{GE}=0V, T_c = 25^\circ C$	-	-	0.2	mA

Gate-body leakage current	I_{GES}	$V_{CE}=0V, V_{GE}=\pm 30V$	-	-	± 200	nA
On-Characteristics						
Gate-Emitter Threshold Voltage	$V_{GE(th)}$	$V_{CE}=V_{GE}, I_c=250\mu A$	4.0	-	6.5	V
Collector-Emitter saturation Voltage	V_{CESAT}	$V_{GE}=15V, I_c=50A, T_c=25^\circ C$	-	1.6	2.2	V
Dynamic Characteristics						
Input capacitance	C_{IES}	$V_{CE}=25V, V_{GE}=0V, f=1.0MHz, T_c=25^\circ C$	-	3330	-	pF
Output capacitance	C_{OES}		-	270	-	pF
Reverse transfer capacitance	C_{RES}		-	78	-	pF
Total Gate Charge	Q_g	$V_{CC}=520V, I_C=50A, V_{GE}=15V, T_c=25^\circ C$	-	118	-	nC
Gate to emitter charge	Q_{ge}		-	33	-	
Gate to collector charge	Q_{gc}		-	48	-	
Short current	I_{SC}	$V_{GE}=15V, V_{CE}=300V, T_{Jstart}\leq 150^\circ C, t\leq 10\mu s$	-	295	-	A
Switching Characteristics						
Turn-On delay time	$t_d(on)$	$V_{CC}=400V, I_C=50A, R_G=10\Omega, V_{GE}=15V, T_c=25^\circ C$	-	33	-	ns
Turn-On rise time	t_r		-	105	-	ns
Turn-off delay time	$t_d(off)$		-	140	-	ns
Turn-off Fall time	t_f		-	72	-	ns
Turn-on energy	E_{on}		-	0.65	-	mJ
Turn-off energy	E_{off}		-	1.53	-	mJ
Total switching Energy	E_{tot}		-	2.20	-	mJ
Anti-Paralle Diode Characteristics and Maximum Ratings						
Diode Forward Voltage	V_F	$V_{GE}=0V, I_F=20A.$	-	1.7	2.4	V
Diode Reverse recovery time	t_{rr}	$V_{GE}=0V, VR=400V, IF=50A, dI/dt=200A/us$	-	25	-	ns
Reverse recovery charge	Q_{rr}		-	15	-	uC
Diode Reverse recovery Current	I_{rrm}		-	1.2	-	A







Electrical Characteristics

Parameter	Symbol	Value	Unit
Thermal Resistance,Junction to Case	$R_{th(j-c)}$	0.34	°C/W
Thermal Resistance,Junction to Ambitent	$R_{th(j-A)}$	34	°C/W


Notes:

- 1: Pulse width limited by maximum junction temperature
- 2: Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 2\%$
- 3: Essentially independent of operating temperature


Electrical Characteristics (curves)



Diode Characteristic




Collector current vs. case temperature




Gate Charge Characteristics

VGE=15V, IC=50A




Capacitance Characteristic

Vce=25V, VGE =0V, f=1.0MHZ




Switching Time vs. IC(25°C)

VCE=400V, VGE=15V, RG=10Ω




Switching Time vs. IC(175°C)

VCE=400V, VGE=15V, RG=10Ω




Switching Time vs. Rg (25°C)

VGE=15V, VCE=400V, IC=50A




Switching Time vs. Rg (175°C)

VGE=15V, VCE=400V, IC=50A




Switching Time vs. T_j

VGE=15V, VCE=400V, IC=50A, Rg=10Ω




Switching Loss vs. T_j

VGE=15V, VCE=400V, IC=50A, Rg=10Ω




Switching Loss vs. IC (25°C)







VGE=15V, VCE=400V, Rg=10Ω




Switching Loss vs. IC (175°C)

VGE=15V, VCE=400V, Rg=10Ω





Normalized Maximum Thermal Impedance for IGBT (RJC)



Package Mechanical DATA

